

## Product information

# 77 12 115 ESD

## Electronics Diagonal Cutter ESD

DIN ISO 9654 DIN EN 61 340-5



- Round head, with bevel and lead catcher - no uncontrolled loss of cut wire ends
- Cutting edge hardness approx. 62 HRC
- For fine cutting work, e.g. in electronics and fine mechanics
- Electrically discharging handles - dissipative
- Sturdy, zero-backlash box joint
- Low-friction double spring for gentle and even opening
- The mirror polish together with a fine film of oil offer effective rust protection - no circuit faults caused by peeling chrome from plated tools
- Cutting edges additionally induction-hardened, cutting edge hardness approx. 62 HRC
- Handles with two-colour multi-component grips black/grey
- Ball bearing chrome steel, oil hardened




### General

Article No.	77 12 115 ESD
EAN	4003773025108
Head	mirror polished
Handles	with multi-component grips
weight	70 g
Dimensions	115 x 66 x 17 mm
Standard	DIN ISO 9654 DIN EN 61 340-5
Reach	no
RohS	no

### Technical details

Style	1
Cutting capacities medium hard wire (diameter)	Ø 1.2 mm
Cutting capacities hard wire (diameter)	Ø 0.6 mm
Cutting capacities soft wire (diameter)	Ø 0.3 – 1.6 mm
	14 mm
	7.5 mm
Head width (A)	11 mm
ESD	yes

## Technical details



## Classification

eCl@ss 5.1.4	21040302
ETIM 5.0	EC000165
ETIM 6.0	EC000165
proficl@ss 6.0	AAA949c004
UNSPSC 13.1	27112149

*technical change and errors excepted*

