


## Product information

# 79 22 125

## Precision Electronics Diagonal Cutter

DIN ISO 9654



- Round head
- Precision pliers for ultra fine cutting work, e. g. in electronics and fine mechanics
- Very precisely ground and sharp cutting edges with very small bevels for exact cutting on delicate electronic components; also available without bevel for flush cutting
- Cutting edges additionally induction-hardened, cutting edge hardness approx. 64 HRC
- Approx. 20% lighter than conventional electronics pliers
- Bolted joint with carefully manufactured joint surfaces for even, low-friction movement throughout the entire opening range
- Smooth-running double spring for a gentle and even opening
- Ergonomically optimised multi-component handles
- Ball bearing chrome steel, forged, multi stage oil-hardened




### General

|             |                            |
|-------------|----------------------------|
| Article No. | 79 22 125                  |
| EAN         | 4003773061342              |
| Pliers      | burnished                  |
| Head        | polished                   |
| Handles     | with multi-component grips |
| weight      | 60 g                       |
| Dimensions  | 125 x 60 x 19 mm           |
| Standard    | DIN ISO 9654               |
| Reach       | yes                        |
| RohS        | no                         |

### Technical details

|  |                |
|--|----------------|
| Style  | 2              |
| Cutting capacities medium hard wire (diameter) | Ø 1.0 mm       |
| Cutting capacities soft wire (diameter)        | Ø 0.1 – 1.7 mm |
|  | 10 mm          |
|  | 6.5 mm         |
| Head width (A)                                 | 11 mm          |





| <b>Classification</b> |  |
|-----------------------|--|
| eCl@ss 5.1.4          | 21040302                                   |
| ETIM 5.0              | EC000165                                   |
| ETIM 6.0              | EC000165                                   |
| proficl@ss 6.0        | AAA949c004                                 |
| UNSPSC 13.1           | 27112114                                   |
| <b>Accessories</b>    |  |
| 00 11 V79             | Material catcher<br>for 79 02 / 22 125 ESD |

*technical change and errors excepted*