

## Product information

# 64 62 120 ESD

## Electronics End Cutting Nippers ESD

DIN ISO 9654 DIN EN 61 340-5



- Precision pliers for ultra fine cutting work, e. g. in electronics and fine mechanics
- Electrically discharging handles - dissipative
- Sturdy, zero backlash box joint
- Low-friction double spring for gentle and even opening
- The mirror polish together with a fine film of oil offer effective rust protection - no circuit faults caused by peeling chrome from plated tools
- Cutters additionally laser hardened, cutter hardness at least 56 HRC
- Handles with two-colour multi-component grips black/grey
- Oblique End Cutter, mini-blade with small bevel,  $\alpha = 65^\circ$
- Ball bearing chrome steel, oil hardened

MM     $\alpha 65^\circ$

### General

Article No.	64 62 120 ESD
EAN	4003773025085
Head	mirror polished
Handles	with multi-component grips
weight	70 g
Dimensions	120 x 66 x 17 mm
Standard	DIN ISO 9654 DIN EN 61 340-5
Reach	no
RohS	no

### Technical details

Cutting capacities soft wire (diameter)	$\varnothing 0.6$ mm
Head width (A)	11 mm
	20 mm
	7 mm
Cutting edge length mm (C)	7 mm
ESD	yes

### Classification

eCl@ss 5.1.4	21040302
ETIM 5.0	EC002222
ETIM 6.0	EC002222
proficl@ss 6.0	AAA947c004
UNSPSC 13.1	27112117

*technical change and errors excepted*