

## Product information

# 64 02 115

## Electronics End Cutting Nipper

DIN ISO 9654




- Precision pliers for ultra fine cutting work, e. g. in electronics and fine mechanics
- Sturdy, zero backlash box joint
- Low-friction double spring for gentle and even opening
- The polish or mirror polish together with a fine film of oil offer effective rust protection - no circuit faults caused by peeling chrome from plated tools
- Cutters additionally laser hardened, cutter hardness at least 56 HRC
- End Cutter, with small bevel
- Ball bearing chrome steel, oil hardened



| General     |                            |
|-------------|----------------------------|
| Article No. | 64 02 115                  |
| EAN         | 4003773035343              |
| Head        | mirror polished            |
| Handles     | with multi-component grips |
| weight      | 70 g                       |
| Dimensions  | 115 x 62 x 17 mm           |
| Standard    | DIN ISO 9654               |
| Reach       | no                         |
| RohS        | no                         |

| Technical details                              |          |
|--|----------|
| Cutting capacities soft wire (diameter)        | Ø 2.0 mm |
| Cutting capacities medium hard wire (diameter) | Ø 1.0 mm |
| Cutting capacities hard wire (diameter)        | Ø 0.6 mm |
| Head width (A)                                 | 11 mm    |
|  | 6 mm     |
|  | 7.5 mm   |
| Cutting edge length mm (C)                     | 16 mm    |



| Classification |            |
|----------------|------------|
| eCl@ss 5.1.4   | 21040302   |
| ETIM 5.0       | EC002222   |
| ETIM 6.0       | EC002222   |
| proficl@ss 6.0 | AAA947c004 |
| UNSPSC 13.1    | 27112117   |

*technical change and errors excepted*

