

## Product information

# 99 11 250

## High Leverage Concreters' Nipper

High lever transmission

DIN ISO 9242



- 25 % less effort required compared to conventional concreters' nippers of the same size
- Extra-slim form for tying deep mounted steel rods
- To lace concrete reinforcing steel with binding wire from a roll
- Wire is twisted and cut in a single pass
- High-leverage joint, minimising strain, even when thick binding wires are used
- The high damping of the cutting stroke on cutting through the binding wire reduces the strain on tendons and muscles
- Cutting edges additionally hardened; cutting edge hardness approx. 61 HRC
- High-grade special tool steel, forged, multi stage oil-hardened

### General

Article No.	99 11 250
EAN	4003773071402
Pliers	black atramentized
Head	polished
Handles	plastic coated
weight	350 g
Dimensions	250 x 47 x 23 mm
Standard	DIN ISO 9242
Reach	no
RohS	no

### Technical details

	Ø 1.8 mm
	Ø 3.3 mm
Head width (W3)	25.0 mm

### Classification

eCl@ss 5.1.4	21040301
proficl@ss 6.0	AAC483c003

technical change and errors excepted