



2-conductor ground terminal block

Item No.: 285-157



2-conductor ground terminal block

Marking

RoHS ✓
Compliant

Business data

| | |
|------------|---------------|
| Supplier | WAGO |
| Item no. | 285-157 |
| GTIN / EAN | 4045454507435 |
| Content | 1 |
| | |
| | |

Notes

Technical data



Miscellaneous

| | |
|-----------------------------------|--|
| Safety information 1 | sively on DIN-35 x 15 rail; 2.3 mm thick, copper |
| Ratings per | IEC/EN 60947-7-2 |
| Type of wiring | Side-entry wiring |
| Total number of connection points | 2 |
| Total number of potentials | 1 |

| Technical data | |
|--|---|
| <i>Number of levels</i> | <i>1</i> |
| <i>Connection technology</i> | <i>POWER CAGE CLAMP</i> |
| <i>Actuation type</i> | <i>Operating tool</i> |
| <i>Connectable conductor materials</i> | <i>Copper</i> |
| <i>Solid conductor</i> | <i>10 ... 50 mm² / 8 ... 1/0 AWG</i> |
| <i>Fine-stranded conductor</i> | <i>10 ... 70 mm² / 8 ... 2/0 AWG</i> |
| <i>Strip length</i> | <i>30 mm / 1.18 Inch</i> |
| <i>Width</i> | <i>20 mm / 0.787 Inch</i> |
| <i>Height from upper-edge of DIN-35 rail</i> | <i>87 mm / 3.425 Inch</i> |
| <i>Depth</i> | <i>94 mm / 3.701 Inch</i> |
| <i>Design</i> | <i>horizontal</i> |
| <i>Type of mounting</i> | <i>Carrier rail 35 x 15</i> |
| <i>Marking level</i> | <i>Side marking</i> |
| <i>Color</i> | <i>green-yellow</i> |
| <i>Insulating material</i> | <i>Polyamide 66 (PA 66)</i> |
| <i>Fire load [MJ]</i> | <i>1.98 [MJ]</i> |
| <i>Weight [g]</i> | <i>186.522 [g]</i> |
| <i>Product Family</i> | <i>POWER CAGE CLAMP</i> |
| <i>Main product function</i> | <i>GND cond. term. block</i> |
| <i>Product type</i> | <i>High-current terminal blocks</i> |

Images & drawings





Address

WAGO Kontakttechnik GmbH & Co. KG

Hansastr. 27

32423 Minden

Telefon: 0571/887-0

Fax: 0571/887-169

<http://www.wago.com>

© WAGO Kontakttechnik GmbH & Co. KG

Technische Änderungen und Irrtümer vorbehalten.