

## Product information

# 77 01 130

## Electronics Diagonal Cutter

DIN ISO 9654



- Round head, with bevel
- Cutting edge hardness approx. 62 HRC
- For fine cutting work, e.g. in electronics and fine mechanics
- Load-optimised for a more direct feel when working
- Low-friction double spring for gentle and even opening
- The polish or mirror polish together with a fine film of oil offer effective rust protection - no circuit faults caused by peeling chrome from plated tools
- Cutters additionally laser hardened, cutter hardness at least 60 HRC
- Narrow sleeves pulled up to the head of the pliers enable the tool to be guided securely and comfortably, also between thumb and index finger
- Ball bearing chrome steel, oil hardened




### General

Article No.	77 01 130
EAN	4003773018575
Head	mirror polished
Handles	plastic coated
weight	108 g
Dimensions	130 x 59 x 14 mm
Standard	DIN ISO 9654
Reach	no
RohS	no

### Technical details

Style	0
Cutting capacities medium hard wire (diameter)	Ø 1.5 mm
Cutting capacities hard wire (diameter)	Ø 0.8 mm
Cutting capacities soft wire (diameter)	Ø 0.3 – 2 mm
	18 mm
	9.5 mm
Head width (A)	15 mm





<b>Classification</b>	
eCl@ss 5.1.4	21040302
ETIM 5.0	EC000165
ETIM 6.0	EC000165
proficl@ss 6.0	AAA949c004
UNSPSC 13.1	27112114

*technical change and errors excepted*