

**Trade name:** edding Permanent Marker Refill Ink T25, T100, T1000, MTK25 (black), contained in: edding 800

**Current version :** 5.1.0, issued: 14.03.2012

**Replaced version:** 5.0.0, issued: 14.12.2011

**Region:** GB

## SECTION 1: Identification of the substance/mixture and of the company/undertaking

### 1.1 Product identifier

**Trade name**

**edding Permanent Marker Refill Ink T25, T100, T1000, MTK25 (black), contained in: edding 800**

### 1.2 Relevant identified uses of the substance or mixture and uses advised against

**Relevant identified uses of the substance or mixture**

Refilling ink

### 1.3 Details of the supplier of the safety data sheet

**Address**

edding Aktiengesellschaft  
Bookkoppel 7  
D-22926 Ahrensburg

Telephone no. +49 (0) 41 02 / 80 8-0

**Information provided by / telephone**

+49 (0)4102 - 808-0

**Advice on Safety Data Sheet**

sdb\_info@umco.de

### 1.4 Emergency telephone number

For medical advice (in German and English):

+49 (0)30 30686 790 (Giftnotruf Berlin)

## SECTION 2: Hazards identification

### 2.1 Classification of the substance or mixture

**Classification in accordance with Directive 67/548/EEC or 1999/45/EC**

F; R11

R67

### 2.2 Label elements

**Labelling according to Directive 1999/45/EC**

**Hazard symbols**



Highly flammable

**R phrases**

11

Highly flammable.

67

Vapours may cause drowsiness and dizziness.

**S phrases**

2

Keep out of the reach of children.

29

Do not empty into drains.

46

If swallowed, seek medical advice immediately and show this container or label.

51

Use only in well-ventilated areas.

### 2.3 Other hazards

No data available.

**Trade name:** edding Permanent Marker Refill Ink T25, T100, T1000, MTK25 (black), contained in: edding 800

**Current version :** 5.1.0, issued: 14.03.2012

**Replaced version:** 5.0.0, issued: 14.12.2011

**Region:** GB

### SECTION 3: Composition/information on ingredients

#### 3.1 Substances

Not applicable. The product is not a substance.

#### 3.2 Mixtures

##### Chemical characterization

Mixture (preparation)

##### Hazardous ingredients

| No | Substance name   |                           | Additional information |        |
|----|--|---------------------------|------------------------|--------|
|    | CAS / EC / Index / REACH no  | Classification 67/548/EEC | Concentration          | %-b.w. |
| 1  | <b>1-METHOXY-2-PROPANOL</b>  |                           |                        |        |
|    | 107-98-2<br>203-539-1<br>603-064-00-3<br>-                                 | R10<br>R67                | > 40,00 - < 45,00      | %-b.w. |
| 2  | <b>ethanol</b>   |                           |                        |        |
|    | 64-17-5<br>200-578-6<br>603-002-00-5<br>-                                  | F; R11                    | > 10,00 - < 30,00      | %-b.w. |
| 3  | <b>Poly(oxy-1,2-ethanediyl), .alpha.-decyl-.omega.-hydroxy-, phosphate</b> |                           |                        |        |
|    | 52019-36-0<br>-<br>-<br>-  | Xi; R38<br>Xi; R41        | > 1,00 - < 5,00        | %-b.w. |

Full Text for all R-phrases: pls. see section 16

#### 3.3 Other information

The data subject of this Material Safety Data sheet refer to the ink contained in this product (marker).

### SECTION 4: First aid measures

#### 4.1 Description of first aid measures

##### General information

In case of persisting adverse effects, consult a physician. Remove contaminated clothing and shoes immediately, and launder thoroughly before reusing.

##### After inhalation

Remove affected person from the immediate area. Ensure supply of fresh air.

##### After skin contact

Wash off immediately with soap and water. Do NOT use solvents or thinners !

##### After eye contact

Separate eyelids, wash the eyes thoroughly with water (15 min.).

##### After ingestion

Rinse mouth thoroughly with water. Summon a doctor immediately. Never give anything by mouth to an unconscious person.

#### 4.2 Most important symptoms and effects, both acute and delayed

No data available.

#### 4.3 Indication of any immediate medical attention and special treatment needed

No data available.

**Trade name:** edding Permanent Marker Refill Ink T25, T100, T1000, MTK25 (black), contained in: edding 800

**Current version :** 5.1.0, issued: 14.03.2012

**Replaced version:** 5.0.0, issued: 14.12.2011

**Region:** GB

## SECTION 5: Firefighting measures

### 5.1 Extinguishing media

#### **Suitable extinguishing media**

Alcohol-resistant foam; extinguishing powder; Carbon dioxide; Water spray jet

#### **Unsuitable extinguishing media**

Full water jet

### 5.2 Special hazards arising from the substance or mixture

In the event of fire, the following can be released: Carbon dioxide (CO<sub>2</sub>); Carbon monoxide (CO)

### 5.3 Advice for firefighters

Use self-contained breathing apparatus. Wear protective clothing. Cool endangered containers with water spray jet. Suppress gases/vapours/mists with water spray jet.

## SECTION 6: Accidental release measures

### 6.1 Personal precautions, protective equipment and emergency procedures

#### **For non-emergency personnel**

Refer to protective measures listed in sections 7 and 8. Avoid contact with skin, eyes and clothing. Ensure adequate ventilation. Keep away sources of ignition.

#### **For emergency responders**

No data available. Personal protective equipment (PPE) - see Section 8.

### 6.2 Environmental precautions

Do not discharge into the drains/surface waters/groundwater.

### 6.3 Methods and material for containment and cleaning up

Take up with absorbent material (e.g., sand, kieselguhr, universal binder). Send in suitable containers for recovery or disposal.

### 6.4 Reference to other sections

No data available.

## SECTION 7: Handling and storage

### 7.1 Precautions for safe handling

#### **Advice on safe handling**

Provide good ventilation of working area (local exhaust ventilation, if necessary). If workplace exposure limits are exceeded, respiratory protection approved for this particular job must be worn. Product inherent handling risks must be minimised taking the appropriate measures for protection and preventive actions. The working process should be designed to rule out the release of hazardous substances or skin contact as far as possible by the state of the art.

#### **General protective and hygiene measures**

Do not eat, drink or smoke during work time. Keep away from foodstuffs and beverages. Avoid contact with eyes and skin. Remove soiled or soaked clothing immediately. Do not inhale vapours. Clean skin thoroughly after work; apply skin cream.

#### **Advice on protection against fire and explosion**

Vapours can form an explosive mixture with air. Take precautionary measures against static charges. Keep away from sources of heat and ignition. Use explosion-proof equipment/fittings and non-sparking tools.

### 7.2 Conditions for safe storage, including any incompatibilities

#### **Technical measures and storage conditions**

Keep container tightly closed and dry in a cool, well-ventilated place. Protect from heat and direct sunlight.

#### **Requirements for storage rooms and vessels**

Containers which are opened must be carefully resealed and kept upright to prevent leakage. Always keep in containers of same material as the original one.

#### **Advice on storage assembly**

Do not store together with: Acids; Alkalies; Oxidizing agents

Trade name: edding Permanent Marker Refill Ink T25, T100, T1000, MTK25 (black), contained in: edding 800

Current version : 5.1.0, issued: 14.03.2012

Replaced version: 5.0.0, issued: 14.12.2011

Region: GB

**7.3 Specific end use(s)**

No data available.

**SECTION 8: Exposure controls/personal protection**

**8.1 Control parameters**

**Occupational exposure limit values**

| No | Substance name  | CAS no.  | EC no.                                   |
|----|---|----------|--|
| 1  | 1-METHOXY-2-PROPANOL  | 107-98-2 | 203-539-1                                |
|    | 2000/39/EWG   |          |  |
|    | 1-Methoxypropanol-2   |          |  |
|    | STEL  | 568      | mg/m <sup>3</sup> 150 ml/m <sup>3</sup>  |
|    | TWA   | 375      | mg/m <sup>3</sup> 100 ml/m <sup>3</sup>  |
|    | Skin resorption / sensibilisation                               |          |  |
|    | Skin  |          |  |
|    | <b>List of approved workplace exposure limits (WELs) / EH40</b> |          |  |
|    | 1-Methoxypropan-2-ol  |          |  |
|    | STEL  | 560      | mg/m <sup>3</sup> 150 ml/m <sup>3</sup>  |
|    | TWA   | 375      | mg/m <sup>3</sup> 100 ml/m <sup>3</sup>  |
|    | Skin resorption / sensibilisation                               |          |  |
|    | Sk  |          |  |
| 2  | ethanol   | 64-17-5  | 200-578-6                                |
|    | <b>List of approved workplace exposure limits (WELs) / EH40</b> |          |  |
|    | Ethanol   |          |  |
|    | TWA   | 1920     | mg/m <sup>3</sup> 1000 ml/m <sup>3</sup> |

**8.2 Exposure controls**

**Appropriate engineering controls**

No data available.

**Personal protective equipment**

**Respiratory protection**

If workplace exposure limits are exceeded, a respiration protection approved for this particular job must be worn. In case of aerosol and mist formation, take appropriate measures for breathing protection in the event workplace threshold values are not specified.

**Eye / face protection**

Safety glasses with side protection shield (EN 166)

**Hand protection**

Sufficient protection is given wearing suitable protective gloves checked according to i.e. EN 374, in the event of risk of skin contact with the product . Before use, the protective gloves should be tested in any case for its specific work-station suitability (i.e. mechanical resistance, product compatibility and antistatic properties). Adhere to the manufacturer's instructions and information relating to the use, storage, care and replacement of protective gloves. Protective gloves shall be replaced immediately when physically damaged or worn. Design operations thus to avoid permanent use of protective gloves.

Appropriate Material butyl rubber

**Other**

Normal chemical work clothing.

**Environmental exposure controls**

No data available.

**SECTION 9: Physical and chemical properties**

**9.1 Information on basic physical and chemical properties**

|                    |
|--------------------|
| <b>Form/Colour</b> |
| liquid             |
| black              |
| <b>Odour</b>       |
| characteristic     |

**Trade name:** edding Permanent Marker Refill Ink T25, T100, T1000, MTK25 (black), contained in: edding 800

**Current version :** 5.1.0, issued: 14.03.2012

**Replaced version:** 5.0.0, issued: 14.12.2011

**Region:** GB

|  |              |             |                   |
|--|--------------|-------------|-------------------|
| <b>Odour threshold</b>                           |              |             |                   |
| No data available                                |              |             |                   |
| <b>pH value</b>                                  |              |             |                   |
| No data available                                |              |             |                   |
| <b>Boiling point / boiling range</b>             |              |             |                   |
| Value  | >            | 70          | °C                |
| Reference pressure                               |              | 1013        | hPa               |
| <b>Melting point / melting range</b>             |              |             |                   |
| No data available                                |              |             |                   |
| <b>Decomposition point / decomposition range</b> |              |             |                   |
| No data available                                |              |             |                   |
| <b>Flash point</b>                               |              |             |                   |
| Value  |              | 18 - 21     | °C                |
| <b>Auto-ignition temperature</b>                 |              |             |                   |
| No data available                                |              |             |                   |
| <b>Oxidising properties</b>                      |              |             |                   |
| No data available                                |              |             |                   |
| <b>Explosive properties</b>                      |              |             |                   |
| No data available                                |              |             |                   |
| <b>Flammability (solid, gas)</b>                 |              |             |                   |
| No data available                                |              |             |                   |
| <b>Lower flammability or explosive limits</b>    |              |             |                   |
| No data available                                |              |             |                   |
| <b>Upper flammability or explosive limits</b>    |              |             |                   |
| No data available                                |              |             |                   |
| <b>Vapour pressure</b>                           |              |             |                   |
| Value  | <            | 110         | kPa               |
| Reference temperature                            |              | 50          | °C                |
| <b>Vapour density</b>                            |              |             |                   |
| No data available                                |              |             |                   |
| <b>Evaporation rate</b>                          |              |             |                   |
| No data available                                |              |             |                   |
| <b>Relative density</b>                          |              |             |                   |
| No data available                                |              |             |                   |
| <b>Density</b>                                   |              |             |                   |
| Value  |              | 0,80 - 1,20 | g/cm <sup>3</sup> |
| Reference temperature                            |              | 20          | °C                |
| <b>Solubility in water</b>                       |              |             |                   |
| No data available                                |              |             |                   |
| <b>Solubility(ies)</b>                           |              |             |                   |
| No data available                                |              |             |                   |
| <b>Partition coefficient: n-octanol/water</b>    |              |             |                   |
| No data available                                |              |             |                   |
| <b>Viscosity</b>                                 |              |             |                   |
| Value  |              | 12 - 80     | sec               |
| Reference temperature                            |              | 20          | °C                |
| Type   | Efflux time  |             |                   |
| Method   | DIN cup 4 mm |             |                   |

**Trade name:** edding Permanent Marker Refill Ink T25, T100, T1000, MTK25 (black), contained in: edding 800

**Current version :** 5.1.0, issued: 14.03.2012

**Replaced version:** 5.0.0, issued: 14.12.2011

**Region:** GB

| Solvent separation test |   |     |
|-------------------------|---|-----|
| Value                   | < | 3 % |

## 9.2 Other information

| Other information                                  |
|--|
| The physical data is that of the main component/s. |

## SECTION 10: Stability and reactivity

### 10.1 Reactivity

No data available.

### 10.2 Chemical stability

No data available.

### 10.3 Possibility of hazardous reactions

No data available.

### 10.4 Conditions to avoid

No data available.

### 10.5 Incompatible materials

Acids; Alcalis; Oxidizing agents

### 10.6 Hazardous decomposition products

No hazardous decomposition products known.

## SECTION 11: Toxicological information

### 11.1 Information on toxicological effects

| Acute oral toxicity         |                    |
|-----------------------------|--------------------|
| LD50                        | 5660 mg/kg         |
| Species                     | rat                |
| Reference substance         | CAS 107-98-2       |
| Acute dermal toxicity       |                    |
| LD50                        | 9999,9 mg/kg       |
| Species                     | rabbit             |
| Reference substance         | CAS 107-98-2       |
| Acute inhalational toxicity |                    |
| Remarks                     | No data available. |

Trade name: edding Permanent Marker Refill Ink T25, T100, T1000, MTK25 (black), contained in: edding 800

Current version : 5.1.0, issued: 14.03.2012

Replaced version: 5.0.0, issued: 14.12.2011

Region: GB

|   |
|---|
| <b>Skin corrosion/irritation</b>  |
| No data available   |
| <b>Serious eye damage/irritation</b>  |
| No data available   |
| <b>Respiratory or skin sensitisation</b>  |
| No data available   |
| <b>Germ cell mutagenicity</b>   |
| No data available   |
| <b>Reproduction toxicity</b>  |
| No data available   |
| <b>Carcinogenicity</b>  |
| No data available   |
| <b>STOT-single exposure</b>   |
| No data available   |
| <b>STOT-repeated exposure</b>   |
| No data available   |
| <b>Aspiration hazard</b>  |
| No data available   |
| <b>Delayed and immediate effects as well as chronic effects from short and long-term exposure</b>   |
| Inhalation of solvent vapours in higher concentration may lead to nausea, headache, drowsiness and dizziness.<br>Repeated and prolonged skin contact may cause removal of natural fat from the skin and irritation of the skin. |

**SECTION 12: Ecological information**

**12.1 Toxicity**

|                          |
|--------------------------|
| <b>Fish toxicity</b>     |
| No data available        |
| <b>Daphnia toxicity</b>  |
| No data available        |
| <b>Algae toxicity</b>    |
| No data available        |
| <b>Bacteria toxicity</b> |
| No data available        |

**12.2 Persistence and degradability**

No data available.

**12.3 Bioaccumulative potential**

No data available.

**12.4 Mobility in soil**

No data available.

**12.5 Results of PBT and vPvB assessment**

No data available.

**12.6 Other adverse effects**

No data available.

**12.7 Other information**

|  |
|--|
| <b>Other information</b>                                   |
| Ecological data are not available.                         |
| Do not discharge product unmonitored into the environment. |

**Trade name:** edding Permanent Marker Refill Ink T25, T100, T1000, MTK25 (black), contained in: edding 800

**Current version :** 5.1.0, issued: 14.03.2012

**Replaced version:** 5.0.0, issued: 14.12.2011

**Region:** GB

## SECTION 13: Disposal considerations

### 13.1 Waste treatment methods

#### Product

Allocation of a waste code number, according to the European Waste Catalogue, should be carried out in agreement with the regional waste disposal company.

#### Packaging

Residuals must be removed from packaging and when emptied completely disposed of in accordance with the regulations for waste removal. Incompletely emptied packaging must be disposed of in the form of disposal specified by the regional disposer.

## SECTION 14: Transport information

### 14.1 Transport ADR/RID/ADN

|                           |                        |
|---------------------------|------------------------|
| Class                     | 3                      |
| Classification code       | F1                     |
| Packing group             | II                     |
| Hazard identification no. | 33                     |
| UN number                 | UN1263                 |
| Technical name            | PAINT RELATED MATERIAL |
| Special Provision 640     | 640D                   |
| Tunnel restriction code   | D/E                    |
| Label                     | 3                      |

### 14.2 Transport IMDG

|                      |                        |
|----------------------|------------------------|
| Class                | 3                      |
| Packing group        | II                     |
| UN number            | UN1263                 |
| Proper shipping name | PAINT RELATED MATERIAL |
| EmS                  | F-E+S-E                |
| Label                | 3                      |

### 14.3 Transport ICAO-TI / IATA

|                      |                        |
|----------------------|------------------------|
| Class                | 3                      |
| Packing group        | II                     |
| UN number            | UN1263                 |
| Proper shipping name | Paint related material |
| Label                | 3                      |

### 14.4 Other information

No data available.

### 14.6 Special precautions for user

No data available.

### 14.7 Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code

Not relevant

## SECTION 15: Regulatory information

### 15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

#### EU regulations

**Council Directive 96/82/EC on the control of major-accident hazards involving dangerous substances**

Remarks Annex I, part 2, category 7 b

### 15.2 Chemical safety assessment

No data available.



**Trade name:** edding Permanent Marker Refill Ink T25, T100, T1000, MTK25 (black), contained in: edding 800

**Current version :** 5.1.0, issued: 14.03.2012

**Replaced version:** 5.0.0, issued: 14.12.2011

**Region:** GB

## SECTION 16: Other information

### Sources of key data used to compile the data sheet:

EC Directive 67/548/EC resp. 99/45/EC as amended in each case.

Regulation (EC) No 1907/2006 (REACH), 1272/2008 (CLP) as amended in each case.

EC Directives 2000/39/EC, 2006/15/EC, 2009/161/EC

National Threshold Limit Values of the corresponding countries as amended in each case.

Transport regulations according to ADR, RID, IMDG, IATA as amended in each case.

The data sources used to determine physical, toxic and ecotoxic data, are indicated directly in the corresponding chapter.

### Full text of the R-, H- and EUH- phrases drawn up in sections 2 and 3 (provided not already drawn up in these sections)

|     |   |
|-----|---|
| R10 | Flammable.                                  |
| R11 | Highly flammable.                           |
| R38 | Irritating to skin.                         |
| R41 | Risk of serious damage to eyes.             |
| R67 | Vapours may cause drowsiness and dizziness. |

### Department issuing safety data sheet

UMCO Umwelt Consult GmbH

Georg-Wilhelm-Str. 183 , D-21107 Hamburg

Tel.: +49 40 / 79 02 36 300 Fax: +49 40 / 79 02 36 357 e-mail: umco@umco.de

This information is based on our present state of knowledge. However, it should not constitute a guarantee for any specific product properties and shall not establish a legally valid relationship.