

Product information

79 12 125

Precision Electronics Diagonal Cutter

DIN ISO 9654



- Specially for cutting through hard wire and piano wire
- Precision pliers for ultra fine cutting work, e. g. in electronics and fine mechanics
- Very precisely ground and sharp cutting edges with very small bevels for exact cutting on delicate electronic components; also available without bevel for flush cutting
- Cutting edges additionally induction-hardened, cutting edge hardness approx. 64 HRC
- Approx. 20% lighter than conventional electronics pliers
- Bolted joint with carefully manufactured joint surfaces for even, low-friction movement throughout the entire opening range
- Smooth-running double spring for a gentle and even opening
- Ergonomically optimised multi-component handles
- Ball bearing chrome steel, forged, multi stage oil-hardened




General

Article No.	79 12 125
EAN	4003773071365
Pliers	burnished
Head	polished
Handles	with multi-component grips
weight	59 g
Dimensions	125 x 59 x 16 mm
Standard	DIN ISO 9654
Reach	yes
RohS	no

Technical details

Cutting capacities medium hard wire (diameter)	Ø 1.3 mm
Cutting capacities hard wire (diameter)	Ø 1.0 mm
Cutting capacities soft wire (diameter)	Ø 0.3 – 1.7 mm
	10 mm
	6.5 mm
Head width (A)	11 mm



Classification	
eCl@ss 5.1.4	21040302
ETIM 5.0	EC000165
ETIM 6.0	EC000165
proficl@ss 6.0	AAA949c004
UNSPSC 13.1	27112114

technical change and errors excepted

