



- ◆ High MTBF up to 700 000 hours
- ◆ Superior operating temperature performance up to 70 °C
- ◆ Very High efficiency up to 87%
- ◆ Very Low Cost
- ◆ Compact
- ◆ Withstands 300VAC surges (5s)
- ◆ Three Year Warranty

## LS Series Single Output General Purpose Power Supplies

### Key Market Segments & Applications

- Test & Measurement
- Automated Service
- Factory Automation
- General Purpose
- LED Lighting & Displays

### LS Features and Benefits

#### Features

- ◆ High MTBF
- ◆ High Efficiency
- ◆ -25 to +70 deg C Operating Temperature
- ◆ Low Derating above 50 degs C (up to 70% load available at 70° C)
- ◆ Curve B emc

#### Benefits

- ◆ Superior Reliability
- ◆ Easier System Cooling
- ◆ Suitable for Indoor & Outdoor Enclosures
- ◆ Improved System Power Optimisation
- ◆ Assists System Compliance

### Specifications


		LS50	LS75	LS100	LS150
Items					
AC Input Voltage (300VAC for 5s)	VAC	88 - 264VAC		88-132/176-264VAC(1)	
Input Frequency	Hz	47 - 63Hz			
DC Input Voltage	VDC	125 - 373VDC		258 - 273VDC	
Inrush Current (230VAC, cold start)	A	40	40	40	40
Power Factor	-	Meets EN61000-3-2, -3			
Input Current (115/230VAC)	A	1.3 / 0.8	1.6 / 1.0	2.5 / 1.5	3 / 2
Temperature Coefficient	-	<0.03%/°C (0 - 50°C)			
Overcurrent Protection	-	> 110%			
Overvoltage Protection	V	3.3V: 3.8-4.45V, 5V: 5.75-6.75V, 12V: 13.8-16.2V, 15V: 17.25-20.25V, 24V: 27.6-32.4V, 36V: 41.4-48.6V, 48V: 55.2-64.8V			
Hold Up Time (115 / 230V input)	ms	14 / 60	14 / 60	18 / 100	20 / 28
Leakage Current (230VAC 60Hz)	mA	<1mA		TBA	
Remote Sense	-	No			
LED Indicator	-	Green LED = On			
Operating Temperature	--	25 to +70°C. Derate linearly to 50% load from +50 to +70°C (2)			
Storage Temperature	-	-40 to +85°C			
Operating Humidity	-	20 - 90% RH (non condensing)			
Storage Humidity	-	10 - 95% RH (non condensing)			
Cooling	-	Convection			
Withstand Voltage	-	Input to Ground 1.5kVAC, Input to Output 3kVAC, Output to Ground 500VAC for 1 min.			
Isolation Resistance	-	>100M at 25C & 70%RH, Output to Ground 500VDC			
Vibration (non operating)	-	10 - 55Hz: 19.6m/s <sup>2</sup> constant sweep 1 min X, Y, Z for 1 hour			
Shock	-	< 196.1 m/s <sup>2</sup> (20G)			
Immunity	-	IEC61000-4-2, -3, -4, -5, -6, -8, -11			
Safety Agency Approvals	-	UL60950-1, EN60950-1, IEC60950-1, CE Mark			
Conducted & Radiated EMI	-	EN55011/EN55022-B, FCC-B			
MTBF (MIL-HDBK-217F)		712,890	648,786	545375	505393
Weight (Typ)	g	350	410	600	700
Size (LxWxH)	in	3.9 x 3.8 x 1.4	5.1 x 3.8 x 1.5	6.3 x 3.8 x 1.5	7.8 x 3.9 x 1.5
Warranty	yrs	Three Years			

Model Selector							
Model	Voltage	Adjust Range (V)	Max Current (A)	Load Reg (mV)	Line Reg (mV)	Ripple Noise (mV)	Efficiency (typ) %
LS50-3	3.3V	3.0 - 3.6	10	40	20	80	75
LS50-5	5V	4.75 - 5.5	10	40	20	80	80
LS50-12	12V	10.8 - 13.2	4.2	96	48	120	84
LS50-15	15V	13.5 - 16.5	3.4	120	60	120	85
LS50-24	24V	22 - 27.2	2.2	192	96	120	86
LS50-36	36V	32 - 40	1.4	288	144	150	86
LS50-48	48V	42 - 54	1.1	384	192	200	86
LS75-3	3.3V	3.0 - 3.6	15	40	20	80	75
LS75-5	5V	4.75 - 5.5	12	40	20	80	79
LS75-12	12V	10.8 - 13.2	6	96	48	120	84
LS75-15	15V	13.5 - 16.5	5	120	60	120	85
LS75-24	24V	22 - 27.2	3.2	192	96	120	86
LS75-36	36V	32 - 40	2.1	288	144	150	86
LS75-48	48V	42 - 54	1.6	384	192	200	87
LS100-3	3.3V	3.0 - 3.3	20	66	16.5	80	74
LS100-5	5V	4.75 - 5.5	16	50	25	80	77
LS100-12	12V	10.8 - 13.2	8.5	60	60	120	81
LS100-15	15V	13.5 - 16.5	7	75	75	120	82
LS100-24	24V	22 - 27.2	4.5	120	120	120	84
LS100-36	36V	32 - 40	3	150	150	150	84
LS100-48	48V	42 - 54	2.3	180	180	200	84
LS150-3	3.3V	3.0 - 3.3	30	66	16.5	80	74
LS150-5	5V	4.75 - 5.5	26	50	25	80	78
LS150-12	12V	10.8 - 13.2	12.5	60	60	120	83
LS150-15	15V	13.5 - 16.5	10	75	75	120	84
LS150-24	24V	22 - 27.2	6.5	120	120	120	86
LS150-36	36V	32 - 40	4.3	150	150	150	86
LS150-48	48V	42 - 54	3.3	180	180	200	87

Notes: Preliminary models shaded in blue

- (1) Switch selectable for 115 or 230VAC
- (2) LS50, LS75-3 & -5: Derate linearly to 70% load from +50 to +70°C.  
 LS75-12, -15, -24, -36, -48 Derate linearly to 60% load from +50 to +70°C.

## LS50 Outline Drawing



**NOTES**  
 A. MODEL NAME, INPUT VOLTAGE RANGE, NOMINAL OUTPUT VOLTAGE, MAXIMUM OUTPUT CURRENT & COUNTRY OF MANUFACTURE ARE SHOWN IN ACCORDANCE WITH THE SPECIFICATION.  
 B. M3 TAPPED, EMBOSSED & COUNTERSINK HOLES (Ø) FOR CUSTOMER CHASSIS MOUNTING. SCREWS MUST NOT PROTRUDE INTO POWER SUPPLY BY MORE THAN 5mm.



## LAMBDA EUROPE

<b>AUSTRIA</b> LAMBDA ELECTRONICS GmbH Aredstraße 22 A-2544 Leobersdorf	Telephone: +43 (0) 2256 655 84 Facsimile: +43 (0) 2256 645 12 www.lambda-austria.com
<b>FRANCE</b> LAMBDA SAS ZAC des Delaches, BP1077 - Gometz le Chatel 91940 Les Ulis	Telephone: +33 (0) 1 60 12 71 65 Facsimile: +33 (0) 1 60 12 71 66 Web: www.lambda-f.com
<b>GERMANY</b> LAMBDA GmbH Karl-Bold-Straße 40 D-77855 Achern	Telephone: +49 (0) 78 41 666 0 Facsimile: +49 (0) 78 41 5000 Web: www.lambda-germany.com
<b>ISRAEL</b> NEMIC LAMBDA LTD Kibbutz Givat Hashlosha 48800	Telephone: +972 (0) 3 902 4333 Facsimile: +972 (0) 3 902 4777 Web: www.nemic.co.il
<b>ITALY</b> LAMBDA s.r.l. Via dei Laboratori 128/130, 20092, Cinisello Balsamo (Mi)	Telephone: +39 (0) 02 61 29 38 63 Facsimile: +39 (0) 02 61 29 09 00 Web: www.lambda-italy.com
<b>SWEDEN</b> LAMBDA SCANDINAVIA PO Box 546, Rallarvägen 41 SE-184 25. Akersberga	Telephone: +46 (0) 8 598 94 090 Facsimile: +46 (0) 8 540 66 096 Web: www.lambda-scandinavia.com
<b>UK</b> LAMBDA UK Kingsley Avenue Ilfracombe Devon EX34 8ES	Telephone: +44 (0) 1271 856666 Facsimile: +44 (0) 1271 864894 Web: www.lambda-gb.com

## LAMBDA NORTH AMERICA

visit [www.lambda-power.com](http://www.lambda-power.com) for a list of Lambda offices and distributors

## LAMBDA ASIA

visit [www.dense-lambda.com](http://www.dense-lambda.com) for a list of Lambda offices and distributors

## LOCAL DISTRIBUTION

