


# PX0695/10/63 Datasheet

**Product Name // IEC Connector Snap Fit To Panel Outlet**  
**PX0695 Series 1mm Panel Black 6.3mm Tab Termination**  
**EN60 320-2-2 Standard Sheet F Class I**

 [View Product Page](#)





| List No      | DIM A |
|--------------|-------|
| PX0695/10/28 | 33.1  |
| PX0695/10/48 | 33.1  |
| PX0695/10/63 | 35.4  |

**// Product Description:**

- Snap Fit Panel Mount IEC Outlets
  - EN60 320-2-2 Standard Sheet F Class I
  - Choice of panel thickness depending on part code: /10 - 1mm, /15 - 1.5mm, /20 - 2mm, /30 - 3mm
  - Choice of Termination depending on part code: /28 - 2.8mm Solder Tag, /63 - 6.3mm Tab, /PC - PCB Spills
- Choice of colour depending on part code: /WH - White, /GY - Grey, no suffix - Black (some approvals apply to specific colours only - see data for details)
  - Insulation Boot for rear of connector available separately (part code 12075) for all versions except PCB Mount
  - Blanking Cover for front of connector available separately (part code 14228)
  - Mate with PX0685, PX0686, PX0686/SE

**// General Information:**

|                            |                                       |
|----------------------------|---------------------------------------|
| Product Display Title:     | Snap Fit Panel Mount IEC Outlets      |
| Product Family:            | IEC Connectors                        |
| Product Series:            | IEC60320 Main Inlets and Outlets      |
| Approvals:                 | CSA, ENEC, UL, VDE                    |
| Body Material:             | Nylon 66                              |
| Current Max:               | 10A, 15A                              |
| Flamability Rating:        | UL94V-0                               |
| Function:                  | Panel Mount Connector                 |
| Iec Connector Colour:      | Black                                 |
| Iec Connector Mates With:  | PX0685,PX0686,PX0686/SE               |
| Iec En60620 Type:          | EN60 320-2-2 Standard Sheet F Class I |
| Max Operating Temperature: | +70°C                                 |
| Min Operating Temperature: | -40°C                                 |
| Max Panel Thickness:       | 1mm                                   |
| Min Panel Thickness:       | 1mm                                   |
| Number Of Contacts:        | 3 Contacts                            |
| Voltage Max:               | 250V                                  |

**// Product PDF Links**

 [IEC Connectors product data](#)

**// Product 3D CAD Model Links**

 [PX0695/10/633D CAD Model](#)