

Product information

99 11 300

High Leverage Concreters' Nipper

High lever transmission

DIN ISO 9242



- 25 % less effort required compared to conventional concreters' nippers of the same size
- Extra-slim form for tying deep mounted steel rods
- To lace concrete reinforcing steel with binding wire from a roll
- Wire is twisted and cut in a single pass
- High-leverage joint, minimising strain, even when thick binding wires are used
- The high damping of the cutting stroke on cutting through the binding wire reduces the strain on tendons and muscles
- Cutting edges additionally hardened; cutting edge hardness approx. 61 HRC
- High-grade special tool steel, forged, multi stage oil-hardened



General	
Article No.	99 11 300
EAN	4003773042365
Pliers	black atramentized
Head	polished
Handles	plastic coated
weight	537 g
Dimensions	300 x 51 x 17 mm
Standard	DIN ISO 9242
Reach	no
RohS	no
Technical details	
	Ø 2.0 mm
	Ø 3.8 mm
Head width (W3)	25.0 mm
Classification	
eCl@ss 5.1.4	21040301
proficl@ss 6.0	AAC483c003

technical change and errors excepted