

D-SUB bus connector - SUBCON 15/M-SH - 2761606

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




D-SUB connector, 15-pos, male connector, one cable entry < 35°, universal type for all systems, pin assignment: 1, 2, 3, ..., 14, 15 to screw connection terminal block

Your advantages

- Easy assembly thanks to knurled screws
- High level of EMC
- Assembly under field conditions
- Flexibility in terms of cable entry selection
- For universal use
- Change to the D-SUB orientation through a reversible connection block

Key Commercial Data

| | |
|--------------------------------------|---|
| Packing unit | 1 pc |
| GTIN |  4 017918 101671 |
| GTIN | 4017918101671 |
| Weight per Piece (excluding packing) | 15.900 g |
| Custom tariff number | 85366990 |
| Country of origin | Germany |

Technical data

Dimensions

| | |
|---------------------|-------|
| Max. cable diameter | 10 mm |
| Min. cable diameter | 4 mm |
| Width | 16 mm |
| Height | 55 mm |
| Length | 65 mm |

Ambient conditions

| | |
|---------------------------------|------------------|
| Ambient temperature (operation) | -20 °C ... 75 °C |
|---------------------------------|------------------|

D-SUB bus connector - SUBCON 15/M-SH - 2761606

Technical data

Ambient conditions

| | |
|---|--|
| Ambient temperature (storage/transport) | -25 °C ... 80 °C |
| Altitude | 5000 m (For restrictions see manufacturer's declaration) |
| Degree of protection | IP20 |
| | IP20 |

General

| | |
|-----------------------------|--|
| Nominal voltage U_N | 50 V |
| Nominal current I_N | 100 mA |
| Signal | Modbus |
| Insertion/withdrawal cycles | > 200 |
| SUBCON fixing screws | 4-40 UNC |
| Tightening torque | 0.4 Nm |
| Housing material | ABS, metal-plated |
| Pin assignment | All connections are 1:1 on the screw terminal block |
| MTTF | 6706 Years (SN 29500 standard, temperature 25 °C, operating cycle 21 % (5 days a week, 8 hours a day)) |
| | 1817 Years (SN 29500 standard, temperature 40 °C, operating cycle 34.25 % (5 days a week, 12 hours a day)) |
| | 155 Years (SN 29500 standard, temperature 40 °C, operating cycle 100 % (7 days a week, 24 hours a day)) |

Connection data

| | |
|--|----------------------|
| Connection | D-SUB connection |
| Number of positions | 15 |
| Connection method | D-SUB connector |
| Connection | PCB connection |
| Connection method | Screw connection |
| Conductor cross section flexible min. | 0.14 mm ² |
| Conductor cross section flexible max. | 1 mm ² |
| Conductor cross section solid min. | 0.14 mm ² |
| Conductor cross section solid max. | 1.5 mm ² |
| Min. AWG conductor cross section, flexible | 26 |
| Max. AWG conductor cross section, flexible | 18 |
| Conductor cross section AWG min. | 26 |
| Conductor cross section AWG max. | 16 |
| Stripping length | 5 mm |
| Tightening torque | 0.4 Nm |

Standards and Regulations

| | |
|---|--|
| Free from substances that could impair the application of coating | according to P-VW 3.10.7 57 65 0 VW-AUDI-Seat central standard |
| Connection in acc. with standard | CUL |
| ATEX | # II 3 G Ex nA IIC T4 Gc X |
| Noxious gas test | ISA-S71.04-1985 G3 Harsh Group A |

D-SUB bus connector - SUBCON 15/M-SH - 2761606


Technical data

Environmental Product Compliance


| | |
|------------|---|
| REACH SVHC | Lead 7439-92-1 |
| China RoHS | Environmentally Friendly Use Period = 50 |
| | For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration" |

Drawings

Schematic diagram



Dimensional drawing



Stripping specifications

Classifications

eCl@ss

| | |
|------------|----------|
| eCl@ss 4.0 | 27140816 |
| eCl@ss 4.1 | 27140816 |
| eCl@ss 5.0 | 27143424 |
| eCl@ss 5.1 | 27143400 |
| eCl@ss 6.0 | 27143400 |
| eCl@ss 7.0 | 27440302 |
| eCl@ss 8.0 | 27440302 |
| eCl@ss 9.0 | 27440302 |

ETIM

| | |
|----------|----------|
| ETIM 2.0 | EC001132 |
| ETIM 3.0 | EC001132 |
| ETIM 4.0 | EC001132 |
| ETIM 5.0 | EC001132 |
| ETIM 6.0 | EC001132 |

UNSPSC

| | |
|---------------|----------|
| UNSPSC 6.01 | 30211802 |
| UNSPSC 7.0901 | 39121402 |
| UNSPSC 11 | 39121402 |
| UNSPSC 12.01 | 39121402 |
| UNSPSC 13.2 | 39121522 |

D-SUB bus connector - SUBCON 15/M-SH - 2761606

Approvals

Approvals






Approvals

CSA / UL Recognized / cUL Recognized / EAC / cULus Recognized

Ex Approvals

ATEX

Approval details

| | | | |
|------------------|---|---|---------------|
| CSA |  | http://www.csagroup.org/services-industries/product-listing/ | 2437602 |
| UL Recognized |  | http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm | FILE E 238705 |
| cUL Recognized |  | http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm | FILE E 238705 |
| EAC |  | | EAC-Zulassung |
| cULus Recognized |  | | |
