

D-SUB contact insert - VS-09-BU-DSUB/9-MPT-0,5 - 1688395

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




D-SUB contact insert, shell size 1, with 9 signal contacts, female type of contact, screw connection, straight, for panel mounting frame and sleeve housing with IP67 protection

Your advantages

- ✓ Easy connection with screw terminal technology



Key Commercial Data

Packing unit	10 pc
Minimum order quantity	10 pc
GTIN	 4 017918 817534
GTIN	4017918817534
Weight per Piece (excluding packing)	13.980 g
Custom tariff number	85366990
Country of origin	Germany

Technical data

Mechanical characteristics

Number of positions	9
Connection profile	D-SUB 9
Insertion/withdrawal cycles	≥ 200
Connection method	Screw connection
Conductor cross section	0.14 mm ² ... 0.5 mm ²
Connection cross section AWG	26 ... 20
Insertion force per signal contact	≤ 3.30 N
Extraction force per signal contact	≤ 2.2 N
Mounting type	Hole
Insulation resistance	≥ 5000 MΩ
Degree of protection	IP20

D-SUB contact insert - VS-09-BU-DSUB/9-MPT-0,5 - 1688395

Technical data

Mechanical characteristics

Type	09
Size of housing	1

Ambient conditions

Ambient temperature (operation)	-20 °C ... 80 °C
---------------------------------	------------------

Material data

Flammability rating according to UL 94	V0
Housing material	Steel
Housing surface material	tin-plated
Contact carrier material	PBTP
Contact material	Cu
Contact surface material	Au/Ni
Height	12.6 mm

Electrical characteristics

Number of positions	9
Rated current	5 A
Overvoltage category	II
Degree of pollution	2
Rated voltage (III/3)	60 V

Standards and Regulations

Flammability rating according to UL 94	V0
--	----


Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values


Drawings

D-SUB contact insert - VS-09-BU-DSUB/9-MPT-0,5 - 1688395

Dimensional drawing



Schematic diagram



D-SUB contact insert

Classifications

eCl@ss

eCl@ss 4.0	27140816
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27261200
eCl@ss 6.0	27261200
eCl@ss 7.0	27440302
eCl@ss 8.0	27440302
eCl@ss 9.0	27440205

ETIM

ETIM 2.0	EC000437
ETIM 3.0	EC000437
ETIM 4.0	EC000438
ETIM 5.0	EC001132
ETIM 6.0	EC000438

UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	39121522

Approvals

Approvals

D-SUB contact insert - VS-09-BU-DSUB/9-MPT-0,5 - 1688395


Approvals

Approvals

EAC

Ex Approvals

Approval details

EAC		B.01742
-----	---	---------
