


PCB TERMINAL BLOCKS

5.08mm Pitch Low Profile 90° Rising Clamp Terminal Blocks

- 2 & 3 pole double interlocking mechanism for increased strength
- 4-12 solid block end stackable
- Moulded in green UL94-V0 flame retardant PA66
- Professional rising clamp terminals
- 0.2-2.5mm² (30-14AWG) solid cable
- 0.2-1.5mm² (30-14AWG) stranded cable
- Guided pin alignment
- Captive screw
-  approved


CTB0558



TYPE NO.	POLES	LENGTH
CTB0558/2	2	10.16mm
CTB0558/3	3	15.24mm
CTB0558/4	4	20.32mm
CTB0558/5	5	25.4mm
CTB0558/6	6	30.48mm
CTB0558/7	7	35.56mm
CTB0558/8	8	40.64mm
CTB0558/9	9	45.72mm
CTB0558/10	10	50.8mm
CTB0558/11	11	55.88mm
CTB0558/12	12	60.96mm

SPECIFICATION

Rating	14A/250V UL=14A/300V, VDE&IMQ=14A/250V
Dielectric strength	≥2kV
Impulse withstand voltage	4kV
Working temperature	110°C
Moulding	UL94-V0 flame retardant PA66
Pin/terminal	Tinned, nickel plated brass
Rising clamp	Tinned, nickel plated brass
Screw/torque	M3 steel zinc plated, 0.5Nm
Recommended PCB hole size	ø1.3mm



For other dimensions see CTB0508