



## Data Sheet | Item Number: 787-1211

Switched-mode power supply; Compact; 1-phase; 12 VDC output voltage; 5 A output current; DC-OK LED

<https://www.wago.com/787-1211>



### Features:

- Switched-mode power supply
- Stepped profile for installation in standard distribution boards
- Removable front panel and screw mounts for alternative installation in distribution boxes or devices
- Pluggable *picoMAX*® Connection Technology (tool-free)
- Suitable for both parallel and series operation
- Electrically isolated output voltage (SELV) per EN 60335-1 and UL 60950-1; PELV per EN 60204

### Technical data

Input		Output	
Phases	1	Nominal output voltage $U_{o, nom}$	DC 12 V (SELV)
Nominal input voltage $U_{i, nom}$	1 x AC 100 ... 240 V; DC 140 ... 340 V	Output voltage range	DC 10 ... 14 V (adjustable)
Input voltage range	1 x AC 85 ... 264 V; DC 125 ... 375 V	Default setting	DC 12 V
Input voltage derating	-2 %/V (< 100 VAC); -1.33 %/V (< 140 VDC)	Nominal output current $I_{o, nom}$	5 A
Nominal mains frequency range	47 ... 63 Hz; 0 Hz	Nominal output power	60 W
Input current $I_i$	≤ 0.6 A	Deviation	≤ 1 %
Discharge current	≤ 0.25 mA	Deviation, dynamic load change 10 ... 90 %	≤ 1 %
Inrush current	≤ 30 A (NTC)	Residual ripple	≤ 100 mV (Peak-to-peak)
Power factor	≥ 0.5	Overload behavior	Constant power (in overload range: 1.22 ... 1.7 x $I_{o, nom}$ ); Hiccup in the event of a short circuit or permanent overload
Power factor correction (PFC)	passive		
Mains failure hold-up time	≥ 600 ms (230 VAC); ≥ 12 ms (110 VAC)		

### Signaling and Communication

Signaling	1 x LED DC OK (green)
Operation status indicator	Green LED ( $U_o$ )

### Efficiency/power losses

Power loss $P_I$	$\leq 0.6$ W
Power loss (max.) $P_{I(max)}$	9 W (100 VAC / 12 VDC; 2.5 A)
Efficiency (typ.)	88.5 % (230 VAC; nominal load); 87.5 % (110 VAC; nominal load)

### Circuit protection

Internal fuse	T 3.15 A / 250 VAC
Backup fusing (required)	An external DC fuse is required for the DC input voltage.
Backup fusing (recommended)	Circuit breaker: 6 A, 10 A or higher; Tripping characteristic: B

### Safety and protection

Isolation voltage (pri.-sec.)	DC 4.242 kV
Isolation voltage (pri.-PE)	DC 2.12 kV
Protection class	I
Protection type	IP20; per EN 60529
Reverse voltage protection	Yes
Resistance to reverse feed	$\leq$ DC 16 V
Overvoltage category	II
Pollution degree	2
Transient suppression (primary)	Varistor
Overvoltage protection; secondary	$\leq 20$ VDC (in the event of a fault)
Short-circuit-protected	Yes
Open-circuit-proof	Yes
Parallel operation	Yes, for devices of the same type
Series operation	Yes, for 2 devices of the same type
MTBF	$> 500,000$ h (per IEC 61709)

### Connection data

Connection type 1	Input/output
Connection technology	Push-in CAGE CLAMP®
WAGO connector	<i>picoMAX</i> ® 5.0, WAGO 2092 Series
Solid conductor	0.2 ... 2.5 mm <sup>2</sup> / 24 ... 12 AWG
Fine-stranded conductor	0.2 ... 2.5 mm <sup>2</sup> / 24 ... 12 AWG
Strip length	9 ... 10 mm / 0.35 ... 0.39 inches
Cable length (max.)	30 m

### Physical data

Width	72 mm / 2.835 inches
Height	90 mm / 3.543 inches
Depth	56 mm / 2.205 inches
Depth from upper-edge of DIN-rail	52.5 mm / 2.067 inches
Note (dimensions)	Depth: 48 mm (without cover)

### Mechanical Data

Mounting type	DIN-35 rail Screw mount (back/side)
---------------	--

### Material Data

Flammability class per UL94	V0
Fire load	0 MJ
Weight	63 g

### Environmental requirements

Ambient temperature (operation at $U_n$ )	-25 ... +70 °C
Surrounding air temperature (storage)	-40 ... +85 °C
Relative humidity	20 ... 90 % (no condensation permissible)
Derating	-3 %/K (> +45 °C and $U_g = 90$ VAC); -2.3 %/K (> +50 °C and $U_g = 230$ VAC)

### Standards and specifications

Conformity marking	CE
Standards/specifications	EN 61204-3 EN 60335-1 EN 62368-1 UL 60950-1 UL 508

### Commercial data

ETIM 8.0	EC002540
ETIM 7.0	EC002540
PU (SPU)	1 pcs
Packaging type	Box
Country of origin	CN
GTIN	4055143804226
Customs tariff number	85044083900

### Approvals / Certificates

#### General approvals



Approval	Standard	Certificate Name
EAC Brjansker Zertifizierungs- stelle	TP TC 004/2011,TP TC 020/2011	EAC RU C-DE.AM02. B.00089_19
UL Underwriters Laboratories Inc.	UL 508	E255817
UR Underwriters Laboratories Inc.	UL 62368-1	E255815

### Downloads

### Environmental Product Compliance

Compliance Search

Environmental Product  
Compliance 787-1211



Documentation

Manual

Product Manual DC Power Supply, 12 V	V 1.1.0 29.06.2020	pdf 3916.69 KB	
--------------------------------------	-----------------------	-------------------	--

Bid Text

787-1211	04.07.2019	xml 7.48 KB	
----------	------------	----------------	--

787-1211	12.06.2019	docx 20.96 KB	
----------	------------	------------------	--

Instruction Leaflet

Stromversorgung COMPACT	V 1.2.0 18.08.2020	pdf 2661.69 KB	
-------------------------	-----------------------	-------------------	--

CAD/CAE-Data

CAD data

2D/3D Models 787-1211	
--------------------------	--

CAE data

EPLAN Data Portal 787-1211	
-------------------------------	--

1 Compatible Products

1.1 Optional Accessories

1.1.1 Strain relief

1.1.1.1 Strain relief plate



[Item No.: 2092-1601](#)

Gripping plate; light gray

1.1.2 Tool

1.1.2.1 Operating tool



[Item No.: 210-720](#)

Operating tool; Blade: 3.5 x 0.5 mm; with a partially insulated shaft; multicoloured

[Item No.: 210-769](#)

SCREWDRIVER; green

Subject to changes. Please also observe the further product documentation!

Current addresses can be found at: [www.wago.com](http://www.wago.com)