



## Data Sheet | Item Number: 787-1701

Switched-mode power supply; Eco; 1-phase; 12 VDC output voltage; 2 A output current; DC-OK LED

<https://www.wago.com/787-1701>



Similar to illustration



### Features:

- Switched-mode power supply
- Natural convection cooling when horizontally mounted
- Encapsulated for use in control cabinets
- Suitable for both parallel and series operation
- Electrically isolated output voltage (SELV) per EN 60335-1; PELV per EN 60204
- DIN-35 rail mountable in different positions
- Direct installation on mounting plate via cable grip

### Technical data

#### Input

Phases	1
Nominal input voltage $U_{i, \text{nom}}$	1 x AC 100 ... 240 V
Input voltage range	1 x AC 90 ... 264 V; DC 125 ... 375 V
Nominal mains frequency range	47 ... 63 Hz; 0 Hz
Input current $I_i$	$\leq 0.7$ A (100 VAC)
Discharge current	$\leq 3.5$ mA
Inrush current	$\leq 18$ A
Power factor correction (PFC)	passive
Mains failure hold-up time	$\geq 10$ ms (230 VAC)

#### Output

Nominal output voltage $U_{o, \text{nom}}$	DC 12 V (SELV)
Output voltage range	DC 10 ... 14 V (adjustable)
Default setting	DC 12 V
Nominal output current $I_{o, \text{nom}}$	2 A (12 VDC; 110 ... 240 VAC); 1.6 A (12 VDC; 100 ... 240 VAC)
Nominal output power	24 W
Deviation	$\leq 1$ %
Residual ripple	$\leq 150$ mV (Peak-to-peak)
Overload behavior	Constant power (in overload range: 1.05 ... 1.4 x $I_{o, \text{nom}}$ ); Shutdown and automatic restart in the event of a short circuit

### Signaling and Communication

Signaling	1 x LED DC OK (green)
Operation status indicator	Green LED (U <sub>o</sub> )

### Efficiency/power losses

Power loss P <sub>I</sub>	≤ 6 W (230 VAC; 12 VDC; 2 A)
Efficiency (typ.)	80 % (230 VAC; 2 ADC)

### Circuit protection

Internal fuse	F 1 A / 250 VAC
Backup fusing (required)	An external DC fuse is required for the DC input voltage.
Backup fusing (recommended)	Circuit breaker: B6, B10

### Safety and protection

Isolation voltage (pri.-sec.)	DC 4.242 kV
Isolation voltage (pri.-PE)	DC 2.2 kV
Isolation voltage (sec.-PE)	DC 0.7 kV
Protection class	I
Protection type	IP20; per EN 60529
Resistance to reverse feed	≤ DC 14 V
Overvoltage category	II
Pollution degree	2
Transient suppression (primary)	Varistor
Short-circuit-protected	Yes
Open-circuit-proof	Yes
Parallel operation	Yes
Series operation	Yes, for 2 devices of the same type
MTBF	> 300,000 h (per IEC 61709)

### Connection data

Connection type 1	Input/output
Connection technology	CAGE CLAMP®
WAGO connector	WAGO 236 Series
Solid conductor	0.08 ... 2.5 mm <sup>2</sup> / 28 ... 12 AWG
Fine-stranded conductor	0.08 ... 2.5 mm <sup>2</sup> / 28 ... 12 AWG
Strip length	6 ... 7 mm / 0.24 ... 0.28 inches
Note (conductor cross-section)	12 AWG: THHN, THWN

### Physical data

Width	30 mm / 1.181 inches
Height	90 mm / 3.543 inches
Depth from upper-edge of DIN-rail	99 mm / 3.898 inches

### Mechanical Data

Mounting type	DIN-35 rail Screw mount
---------------	----------------------------

### Material Data

Fire load	0.129 MJ
Weight	250 g

### Environmental requirements

Ambient temperature (operation at U <sub>N</sub> )	-20 ... +60 °C
Surrounding air temperature (storage)	-25 ... +75 °C
Relative humidity	10 ... 95 % (no condensation permissible)
Derating	-4 %/K (> 45 °C)

### Standards and specifications

Conformity marking	CE
Standards/specifications	EN 61204-3 EN 60335-1 EN 61558-2-6 EN 62368-1

### Commercial data

eCl@ss 10.0	27-04-07-01
eCl@ss 9.0	27-04-07-01
ETIM 8.0	EC002540
ETIM 7.0	EC002540
PU (SPU)	1 pcs
Packaging type	Box
Country of origin	CN
GTIN	4055143656023
Customs tariff number	85044083900

### Approvals / Certificates

#### General approvals



Approval	Standard	Certificate Name
EAC Brjansker Zertifizierungs- stelle	TP TC 004/2011,TP TC 020/2011	EAC RU C-DE.AM02. B.00089_19

### Downloads

#### Environmental Product Compliance

Compliance Search

Environmental Product  
Compliance 787-1701



Documentation

Bid Text

787-1701 01.10.2019 xml 6.73 KB

787-1701 01.10.2019 docx 20.12 KB

Instruction Leaflet

ECO Power Switched- V 1.2 pdf  
Mode Power Supplies 21.12.2020 249.88 KB

CAD/CAE-Data

CAD data

2D/3D Models  
787-1701

CAE data

EPLAN Data Portal  
787-1701

ZUKEN Portal  
787-1701

1 Compatible Products

1.1 Optional Accessories

1.1.1 Marking

1.1.1.1 Marking strip



[Item No.: 210-831](#)

Marking strips; on reel; 2.3 mm wide; plain;  
Self-adhesive; white

[Item No.: 210-832](#)

Marking strips; on reel; 3 mm wide; plain;  
Self-adhesive; white

1.1.2 Tool

1.1.2.1 Operating tool



[Item No.: 210-720](#)

Operating tool; Blade: 3.5 x 0.5 mm; with a  
partially insulated shaft; multicoloured

[Item No.: 210-769](#)

SCREWDRIVER; green

Subject to changes. Please also observe the further product documentation!

Current addresses can be found at: [www.wago.com](http://www.wago.com)