


PX0675/63 Datasheet

Product Name // IEC Connector Flange Mount Outlet
PX0675 Series Black 6.3mm Tab Termination EN60 320-2-2
Standard Sheet F Class I

 [View Product Page](#)





49.6
40.00 CRS
28.8
2.6
A
23.8
Fixing Details
40.00 CRS
32.26
Ø3.4
R6.5 MAX
24.77

List No	DIM A
PX0675/28	33.1
PX0675/63	35.4

// Product Description:

- Flange Mount IEC Outlets
 - EN60 320-2-2 Standard Sheet F Class I
 - Choice of Termination depending on part code: /28 - 2.8mm Solder Tag, /48 - 4.8mm Tab, /63 - 6.3mm Tab, /PC - PCB Spills
 - Choice of colour depending on part code: /WH - White, /GY - Grey, no suffix - Black (some approvals apply to specific colour and/or Termination choices only - see data for details)
- PCB Mount version (part codes containing /PC) available with rear cover (part codes suffixed /12599), for all other versions Insulation Boot for rear of connector available separately (part code 12075)
 - Retaining Clip KT0006 available separately to prevent accidental removal of mating connector (for use with PX0686 Female Connector only)
 - Blanking Cover for front of connector available separately (part code 14228)
 - Mate with PX0685, PX0686, PX0686/SE

// General Information:

Product Display Title:	Flange Mount IEC Outlets
Product Family:	IEC Connectors
Product Series:	IEC60320 Main Inlets and Outlets
Approvals:	CSA, ENEC, UL, VDE
Body Material:	Nylon 66
Current Max:	10A, 15A
Flamability Rating:	UL94V-0
Function:	Flange Mount Connector
Iec Connector Colour:	Black
Iec Connector Mates With:	PX0685,PX0686,PX0686/SE
Iec En60620 Type:	EN60 320-2-2 Standard Sheet F Class I
Max Operating Temperature:	+70°C
Min Operating Temperature:	-40°C
Number Of Contacts:	3 Contacts
Voltage Max:	250V

// Product PDF Links

 [IEC Connectors product data](#)

// Product 3D CAD Model Links

 [PX0675/633D CAD Model](#)

// Product Certificate Links

 [VDE Certificate - IEC P675](#)

 [UL & CSA Certificate E93288](#)

 [CE Certificate - P675](#)