


PCB TERMINAL BLOCKS

5mm Pitch Low Profile 90° Rising Clamp Terminal Blocks

- 2 & 3 pole double Interlocking mechanism for increased strength
- 4-12 pole solid block and end stackable
- Moulded in green UL94-V0 flame retardant PA
- Professional rising clamp terminals
- 0.2-2.5mm² (30-14AWG) solid cable
- 0.2-1.5mm² (30-14AWG) stranded cable
- Guided pin alignment
- Captive screw
-  approved


CTB0550



| TYPE NO. | POLES | LENGTH |
|------------|-------|--------|
| CTB0550/2 | 2 | 10mm |
| CTB0550/3 | 3 | 15mm |
| CTB0550/4 | 4 | 20mm |
| CTB0550/5 | 5 | 25mm |
| CTB0550/6 | 6 | 30mm |
| CTB0550/7 | 7 | 35mm |
| CTB0550/8 | 8 | 40mm |
| CTB0550/9 | 9 | 45mm |
| CTB0550/10 | 10 | 50mm |
| CTB0550/11 | 11 | 55mm |

SPECIFICATION

| | |
|---------------------------|---|
| Rating | 14A/250V UL=14A/300V, VDE&IMQ=14A/250V |
| Dielectric strength | ≥2.kV |
| Impulse withstand voltage | 4kV |
| Working temperature | 110°C |
| Moulding | UL94-V0 flame retardant PA |
| Pin/terminal | Tinned, nickel plated brass |
| Rising clamp | Tinned, nickel plated brass |
| Screw/torque | M3 steel zinc plated, 0.5Nm |
| Recommended PCB hole size | ø1.3mm |



For other dimensions see CTB0500

PCB
TERMINAL
BLOCKS

INTER-
CONNECTION

FUSES &
FUSE-
HOLDERS

LEDs &
INDICATORS

MINIATURE
SWITCHES

LIMIT &
SAFETY
SWITCHES

CONTROL
PRODUCTS

INTERFACE
MODULES &
SUPPORTS

RELAY
BASES

DIN RAIL
ENCLOSURES

BATTERIES

SOLAR
PANELS

TRANS-
FORMERS