


PX0580/PC Datasheet

Product Name // IEC Connector PCB Mount Flange Rear
Mount Inlet PX0580 Series Black No Cover PCB Spills
Termination EN60 320-1 Standard Sheet C14 Class I

 [View Product Page](#)



// Product Description:

- Flange Mount IEC Inlets
 - EN60 320-1 Standard Sheet C14 Class I
 - Cold Condition
 - Choice of Termination depending on part code: /28 - 2.8mm Solder Tag, /48 - 4.8mm Tab, /63 - 6.3mm Tab, /TERM - Screw Terminal, /PC - PCB Spills
 - PCB Mount version also available with additional 4.8mm Tab Earth connection at top of connector (part codes containing /PC/7)
- Choice of colour depending on part code: /WH - White, /GY - Grey, no suffix - Black (some approvals apply to specific colours only - see data for details)
 - PCB Mount version without additional Earth Tab (part codes containing /PC) available with rear cover (part codes suffixed /12132), for all other versions Insulation Boot for rear of connector available separately (part code 11328)
 - Retaining Clip KT0006 available separately to prevent accidental removal of mating connector (for use with PX0587 Female Connector only)
 - Mate with PX0587, PX0587/SE, PX0588
 - Also available as Vertical Flange Mount (PX0579 Series)

// General Information:

Product Display Title:	Flange Mount IEC Inlets
Product Family:	IEC Connectors
Product Series:	IEC60320 Main Inlets and Outlets
Approvals:	CSA, ENEC, UL, VDE
Body Material:	Nylon 66
Current Max:	10A, 15A
Flamability Rating:	UL94V-0
Function:	Flange Mount Connector
Iec Connector Colour:	Black
Iec Connector Mates With:	PX0587,PX0587/SE,PX0588
Iec En60620 Type:	EN60 320-1 Standard Sheet C14 Class I
Iec Pcb Rear Cover:	No Cover
Max Operating Temperature:	+70°C
Min Operating Temperature:	-40°C
Number Of Contacts:	3 Contacts
Rohs Compliant:	Yes
Voltage Max:	250V

// Product PDF Links

 [IEC Connectors product data](#)

// Product 3D CAD Model Links

 [PX0580/PC3D CAD Model](#)

// Product Certificate Links

 [VDE Certificate - PX0580](#)

 [UL E70394 Certificate - PX0580](#)

 [CSA Certificate - IEC](#)

 [CE Certificate - PX0580](#)



Have a question or project enquiry
you'd like to talk to us about?



[Click Here To Contact Us](#)