

## SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006 Version 5.0 Revision Date 22.03.2013

---

### SECTION 1: Identification of the substance/mixture and of the company/undertaking

#### 1.1 Product identifiers

Product name : Buffer solution pH 6

Product Number : 52-7422

Brand : Rapid

REACH No. : A registration number is not available for this substance as the substance or its uses are exempted from registration, the annual tonnage does not require a registration or the registration is envisaged for a later registration deadline.

#### 1.2 Relevant identified uses of the substance or mixture and uses advised against

Identified uses : Laboratory chemicals, Manufacture of substances

#### 1.3 Details of the supplier of the safety data sheet

Company : Rapid Electronics,  
Severalls Lane,  
Colchester,  
Essex,  
CO4 5JS, United Kingdom

Telephone : +44 (0) 1206 751166

Fax : +44 (0) 1206 751188

E-mail address : sales@rapidelec.co.uk

#### 1.4 Emergency telephone number

Emergency Phone # : +44 (0) 1206 751166

---

### SECTION 2: Hazards identification

#### 2.1 Classification of the substance or mixture

Not a hazardous substance or mixture according to Regulation (EC) No. 1272/2008.  
Not a hazardous substance or mixture according to EC-directives 67/548/EEC or 1999/45/EC.

#### 2.2 Label elements

The product does not need to be labelled in accordance with EC directives or respective national laws.

#### 2.3 Other hazards - none

---

### SECTION 3: Composition/information on ingredients

#### 3.2 Mixtures

No components need to be disclosed according to the applicable regulations.

---

### SECTION 4: First aid measures

#### 4.1 Description of first aid measures

##### If inhaled

If breathed in, move person into fresh air. If not breathing, give artificial respiration.

##### In case of skin contact

Wash off with soap and plenty of water.

**In case of eye contact**

Flush eyes with water as a precaution.

**If swallowed**

Never give anything by mouth to an unconscious person. Rinse mouth with water.

**4.2 Most important symptoms and effects, both acute and delayed**

The most important known symptoms and effects are described in the labelling (see section 2.2) and/or in section 11

**4.3 Indication of any immediate medical attention and special treatment needed**

no data available

---

**SECTION 5: Firefighting measures****5.1 Extinguishing media****Suitable extinguishing media**

Use water spray, alcohol-resistant foam, dry chemical or carbon dioxide.

**5.2 Special hazards arising from the substance or mixture**

Nature of decomposition products not known.

**5.3 Advice for firefighters**

Wear self contained breathing apparatus for fire fighting if necessary.

**5.4 Further information**

no data available

---

**SECTION 6: Accidental release measures****6.1 Personal precautions, protective equipment and emergency procedures**

Avoid breathing vapours, mist or gas.

For personal protection see section 8.

**6.2 Environmental precautions**

Do not let product enter drains.

**6.3 Methods and materials for containment and cleaning up**

Keep in suitable, closed containers for disposal.

**6.4 Reference to other sections**

For disposal see section 13.

---

**SECTION 7: Handling and storage****7.1 Precautions for safe handling**

For precautions see section 2.2.

**7.2 Conditions for safe storage, including any incompatibilities**

Store in cool place. Keep container tightly closed in a dry and well-ventilated place.

**7.3 Specific end use(s)**

A part from the uses mentioned in section 1.2 no other specific uses are stipulated

---

**SECTION 8: Exposure controls/personal protection****8.1 Control parameters****Components with workplace control parameters**

Contains no substances with occupational exposure limit values.

**8.2 Exposure controls****Appropriate engineering controls**

General industrial hygiene practice.

## Personal protective equipment

### Eye/face protection

Use equipment for eye protection tested and approved under appropriate government standards such as NIOSH (US) or EN 166(EU).

### Skin protection

Handle with gloves. Gloves must be inspected prior to use. Use proper glove removal technique (without touching glove's outer surface) to avoid skin contact with this product. Dispose of contaminated gloves after use in accordance with applicable laws and good laboratory practices. Wash and dry hands.

The selected protective gloves have to satisfy the specifications of EU Directive 89/686/EEC and the standard EN 374 derived from it.

### Body Protection

Impervious clothing, The type of protective equipment must be selected according to the concentration and amount of the dangerous substance at the specific workplace.

### Respiratory protection

Respiratory protection not required. For nuisance exposures use type OV/AG (US) or type ABEK (EU EN 14387) respirator cartridges. Use respirators and components tested and approved under appropriate government standards such as NIOSH (US) or CEN (EU).

### Control of environmental exposure

Do not let product enter drains.

---

## SECTION 9: Physical and chemical properties

### 9.1 Information on basic physical and chemical properties

a) Appearance	Form: clear Colour: colourless
b) Odour	no data available
c) Odour Threshold	no data available
d) pH	6 at 25 °C
e) Melting point/freezing point	no data available
f) Initial boiling point and boiling range	no data available
g) Flash point	no data available
h) Evaporation rate	no data available
i) Flammability (solid, gas)	no data available
j) Upper/lower flammability or explosive limits	no data available
k) Vapour pressure	no data available
l) Vapour density	no data available
m) Relative density	1.000 - 1.020 g/cm <sup>3</sup>
n) Water solubility	no data available
o) Partition coefficient: n-octanol/water	no data available
p) Auto-ignition temperature	no data available
q) Decomposition temperature	no data available
r) Viscosity	no data available

s) Explosive properties no data available

t) Oxidizing properties no data available

## 9.2 Other safety information

no data available

---

## SECTION 10: Stability and reactivity

### 10.1 Reactivity

no data available

### 10.2 Chemical stability

Stable under recommended storage conditions.

### 10.3 Possibility of hazardous reactions

no data available

### 10.4 Conditions to avoid

no data available

### 10.5 Incompatible materials

Strong acids and strong bases

### 10.6 Hazardous decomposition products

Other decomposition products - no data available

In the event of fire: see section 5

---

## SECTION 11: Toxicological information

### 11.1 Information on toxicological effects

#### Acute toxicity

no data available

#### Skin corrosion/irritation

no data available

#### Serious eye damage/eye irritation

no data available

#### Respiratory or skin sensitisation

no data available

#### Germ cell mutagenicity

no data available

#### Carcinogenicity

IARC: No component of this product present at levels greater than or equal to 0.1% is identified as probable, possible or confirmed human carcinogen by IARC.

#### Reproductive toxicity

no data available

#### Specific target organ toxicity - single exposure

no data available

#### Specific target organ toxicity - repeated exposure

no data available

#### Aspiration hazard

no data available

#### Additional Information

RTECS: Not available

To the best of our knowledge, the chemical, physical, and toxicological properties have not been thoroughly investigated.

---

**SECTION 12: Ecological information**

- 12.1 Toxicity**  
no data available
- 12.2 Persistence and degradability**  
no data available
- 12.3 Bioaccumulative potential**  
no data available
- 12.4 Mobility in soil**  
no data available
- 12.5 Results of PBT and vPvB assessment**  
PBT/vPvB assessment not available as chemical safety assessment not required/not conducted
- 12.6 Other adverse effects**  
no data available

---

**SECTION 13: Disposal considerations****13.1 Waste treatment methods****Product**

Offer surplus and non-recyclable solutions to a licensed disposal company.

**Contaminated packaging**

Dispose of as unused product.

---

**SECTION 14: Transport information****14.1 UN number**

ADR/RID: -

IMDG: -

IATA: -

**14.2 UN proper shipping name**

ADR/RID: Not dangerous goods

IMDG: Not dangerous goods

IATA: Not dangerous goods

**14.3 Transport hazard class(es)**

ADR/RID: -

IMDG: -

IATA: -

**14.4 Packaging group**

ADR/RID: -

IMDG: -

IATA: -

**14.5 Environmental hazards**

ADR/RID: no

IMDG Marine pollutant: no

IATA: no

**14.6 Special precautions for user**

no data available

---

**SECTION 15: Regulatory information**

This safety datasheet complies with the requirements of Regulation (EC) No. 1907/2006.

**15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture**

no data available

**15.2 Chemical Safety Assessment**

For this product a chemical safety assessment was not carried out

---

**SECTION 16: Other information****Further information**

The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. The information in this document is based on the present state of our knowledge and is applicable to the product with regard to appropriate safety precautions. It does not represent any guarantee of the properties of the product.