

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006 Version 5.0 Revision Date 24.04.2012

1. IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

1.1 Product identifiers

Product name : 1,6-Diaminohexane

Product Number : 52-7454
 Brand : Rapid
 Index-No. : 612-104-00-9
 CAS-No. : 124-09-4

1.2 Relevant identified uses of the substance or mixture and uses advised against

Identified uses : Laboratory chemicals, Manufacture of substances

1.3 Details of the supplier of the safety data sheet

Company : Rapid Electronics,
 Severalls Lane,
 Colchester,
 Essex,
 CO4 5JS, United Kingdom

Telephone : +44 (0)1206 751166
 Fax : +44 (0) 1206 751188
 E-mail address : sales@rapidelec.co.uk

1.4 Emergency telephone number

Emergency Phone # : +44 (0)1206 751166

2. HAZARDS IDENTIFICATION

2.1 Classification of the substance or mixture

Classification according to Regulation (EC) No 1272/2008 [EU-GHS/CLP]


Acute toxicity, Dermal (Category 4)
 Acute toxicity, Oral (Category 4)
 Specific target organ toxicity - single exposure (Category 3)
 Skin corrosion (Category 1B)

Classification according to EU Directives 67/548/EEC or 1999/45/EC

Causes burns. Harmful in contact with skin and if swallowed. Irritating to respiratory system.


2.2 Label elements

Labelling according Regulation (EC) No 1272/2008 [CLP]

Pictogram	
Signal word	Danger
Hazard statement(s)	
H302	Harmful if swallowed.
H312	Harmful in contact with skin.
H314	Causes severe skin burns and eye damage.
H335	May cause respiratory irritation.
Precautionary statement(s)	
P261	Avoid breathing dust/ fume/ gas/ mist/ vapours/ spray.

P280 Wear protective gloves/ protective clothing/ eye protection/ face protection.
 P305 + P351 + P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
 P310 Immediately call a POISON CENTER or doctor/ physician.
 Supplemental Hazard Statements none

According to European Directive 67/548/EEC as amended.

Hazard symbol(s) 

R-phrase(s)
 R21/22 Harmful in contact with skin and if swallowed.
 R34 Causes burns.
 R36/37 Irritating to respiratory system.

S-phrase(s)
 S22 Do not breathe dust.
 S26 In case of contact with eyes, rinse immediately with plenty of water and seek medical advice.
 S36/37/39 Wear suitable protective clothing, gloves and eye/face protection.
 S45 In case of accident or if you feel unwell, seek medical advice immediately (show the label where possible).

2.3 Other hazards - none

3. COMPOSITION/INFORMATION ON INGREDIENTS

3.1 Substances

Synonyms :Hexamethylenediamine
 1,6-Hexanediamine

Formula : C₆H₁₆N₂
 Molecular Weight : 116.20 g/mol

Component		Concentration
Hexamethylenediamine		
CAS-No.	124-09-4	-
EC-No.	204-679-6	
Index-No.	612-104-00-9	

4. FIRST AID MEASURES

4.1 Description of first aid measures

General advice

Consult a physician. Show this safety data sheet to the doctor in attendance.

If inhaled

If breathed in, move person into fresh air. If not breathing, give artificial respiration. Consult a physician.

In case of skin contact

Take off contaminated clothing and shoes immediately. Wash off with soap and plenty of water. Consult a physician.

In case of eye contact

Rinse thoroughly with plenty of water for at least 15 minutes and consult a physician.

If swallowed

Do NOT induce vomiting. Never give anything by mouth to an unconscious person. Rinse mouth with water. Consult a physician.

- 4.2 Most important symptoms and effects, both acute and delayed**
burning sensation, Cough, wheezing, laryngitis, Shortness of breath, spasm, inflammation and edema of the larynx, spasm, inflammation and edema of the bronchi, pneumonitis, pulmonary edema, Material is extremely destructive to tissue of the mucous membranes and upper respiratory tract, eyes, and skin.
- 4.3 Indication of any immediate medical attention and special treatment needed**
no data available
-

5. FIREFIGHTING MEASURES

- 5.1 Extinguishing media**
Suitable extinguishing media
Use water spray, alcohol-resistant foam, dry chemical or carbon dioxide.
- 5.2 Special hazards arising from the substance or mixture**
Carbon oxides, nitrogen oxides (NOx)
- 5.3 Advice for firefighters**
Wear self contained breathing apparatus for fire fighting if necessary.
- 5.4 Further information**
no data available
-

6. ACCIDENTAL RELEASE MEASURES

- 6.1 Personal precautions, protective equipment and emergency procedures**
Use personal protective equipment. Avoid dust formation. Avoid breathing vapors, mist or gas. Ensure adequate ventilation. Evacuate personnel to safe areas. Avoid breathing dust.
- 6.2 Environmental precautions**
Prevent further leakage or spillage if safe to do so. Do not let product enter drains. Discharge into the environment must be avoided.
- 6.3 Methods and materials for containment and cleaning up**
Pick up and arrange disposal without creating dust. Sweep up and shovel. Keep in suitable, closed containers for disposal.
- 6.4 Reference to other sections**
For disposal see section 13.
-

7. HANDLING AND STORAGE

- 7.1 Precautions for safe handling**
Avoid contact with skin and eyes. Avoid formation of dust and aerosols. Provide appropriate exhaust ventilation at places where dust is formed.
- 7.2 Conditions for safe storage, including any incompatibilities**
Store in cool place. Keep container tightly closed in a dry and well-ventilated place.

Hygroscopic. Store under inert gas.
- 7.3 Specific end uses**
no data available
-

8. EXPOSURE CONTROLS/PERSONAL PROTECTION

- 8.1 Control parameters**
Components with workplace control parameters
Contains no substances with occupational exposure limit values.
- 8.2 Exposure controls**
Appropriate engineering controls
Handle in accordance with good industrial hygiene and safety practice. Wash hands before breaks and at the end of workday.

Personal protective equipment

Eye/face protection

Face shield and safety glasses Use equipment for eye protection tested and approved under appropriate government standards such as NIOSH (US) or EN 166(EU).

Skin protection

Handle with gloves. Gloves must be inspected prior to use. Use proper glove removal technique (without touching glove's outer surface) to avoid skin contact with this product. Dispose of contaminated gloves after use in accordance with applicable laws and good laboratory practices. Wash and dry hands.

The selected protective gloves have to satisfy the specifications of EU Directive 89/686/EEC and the standard EN 374 derived from it.

Immersion protection

Material: Nitrile rubber

Minimum layer thickness: 0.4 mm

Break through time: > 480 min

Material tested:Camatril® (Aldrich Z677442, Size M)

Splash protection

Material: Nitrile rubber

Minimum layer thickness: 0.11 mm

Break through time: > 30 min

Material tested:Dermatril® (Aldrich Z677272, Size M)

data source: KCL GmbH, D-36124 Eichenzell, phone +49 (0)6659 873000, e-mail sales@kcl.de, test method: EN374

If used in solution, or mixed with other substances, and under conditions which differ from EN 374, contact the supplier of the CE approved gloves. This recommendation is advisory only and must be evaluated by an Industrial Hygienist familiar with the specific situation of anticipated use by our customers. It should not be construed as offering an approval for any specific use scenario.

Body Protection

Complete suit protecting against chemicals, The type of protective equipment must be selected according to the concentration and amount of the dangerous substance at the specific workplace.

Respiratory protection

Where risk assessment shows air-purifying respirators are appropriate use a full-face particle respirator type N100 (US) or type P3 (EN 143) respirator cartridges as a backup to engineering controls. If the respirator is the sole means of protection, use a full-face supplied air respirator. Use respirators and components tested and approved under appropriate government standards such as NIOSH (US) or CEN (EU).

9. PHYSICAL AND CHEMICAL PROPERTIES

9.1 Information on basic physical and chemical properties

- | | |
|--|--|
| a) Appearance | Form: solid
Colour:
colourless |
| b) Odour | no data available |
| c) Odour Threshold | no data available |
| d) pH | 12.4 at 100 g/l at 25 °C |
| e) Melting point/freezing point | Melting point/range: 42 - 45 °C - lit. |
| f) Initial boiling point and boiling range | 204 - 205 °C |
| g) Flash point | 80 °C - closed cup |
| h) Evaporation rate | no data available |
| i) Flammability (solid, gas) | no data available |

j) Upper/lower flammability or explosive limits	Upper explosion limit: 6.3 %(V) Lower explosion limit: 0.7 %(V)
k) Vapour pressure	no data available
l) Vapour density	4.01 - (Air = 1.0)
m) Relative density	0.89 g/cm ³ at 25 °C
n) Water solubility	no data available
o) Partition coefficient: n-octanol/water	log Pow: 0.02
p) Autoignition temperature	no data available
q) Decomposition temperature	no data available
r) Viscosity	no data available
s) Explosive properties	no data available
t) Oxidizing properties	no data available

9.2 Other safety information

no data available

10. STABILITY AND REACTIVITY

10.1 Reactivity

no data available

10.2 Chemical stability

no data available

10.3 Possibility of hazardous reactions

no data available

10.4 Conditions to avoid

no data available

10.5 Incompatible materials

acids, Acid chlorides, Acid anhydrides, Strong oxidizing agents, Carbon dioxide (CO₂)

10.6 Hazardous decomposition products

Other decomposition products - no data available

11. TOXICOLOGICAL INFORMATION

11.1 Information on toxicological effects

Acute toxicity

LD50 Oral - rat - 750 mg/kg

LD50 Dermal - rabbit - 1,110 mg/kg

Skin corrosion/irritation

no data available

Serious eye damage/eye irritation

no data available

Respiratory or skin sensitization

no data available

Germ cell mutagenicity

no data available

Carcinogenicity

IARC: No component of this product present at levels greater than or equal to 0.1% is identified as probable, possible or confirmed human carcinogen by IARC.

Reproductive toxicity

no data available

Specific target organ toxicity - single exposure

May cause respiratory irritation.

Specific target organ toxicity - repeated exposure

no data available

Aspiration hazard

no data available

Potential health effects

Inhalation	May be harmful if inhaled. Material is extremely destructive to the tissue of the mucous membranes and upper respiratory tract. Causes respiratory tract irritation.
Ingestion	Harmful if swallowed. Causes burns.
Skin	Harmful if absorbed through skin. Causes skin burns.
Eyes	Causes eye burns.

Signs and Symptoms of Exposure

burning sensation, Cough, wheezing, laryngitis, Shortness of breath, spasm, inflammation and edema of the larynx, spasm, inflammation and edema of the bronchi, pneumonitis, pulmonary edema, Material is extremely destructive to tissue of the mucous membranes and upper respiratory tract, eyes, and skin.

Additional Information

RTECS: MO1180000

12. ECOLOGICAL INFORMATION

12.1 Toxicity

Toxicity to fish	LC50 - Leuciscus idus (Golden orfe) - 62 mg/l - 96 h
Toxicity to daphnia and other aquatic invertebrates	EC50 - Daphnia magna (Water flea) - 23.4 mg/l - 48 h

12.2 Persistence and degradability

Biodegradability Result: 56 % - Partially biodegradable.

12.3 Bioaccumulative potential

no data available

12.4 Mobility in soil

no data available

12.5 Results of PBT and vPvB assessment

no data available

12.6 Other adverse effects

Harmful to aquatic life.

13. DISPOSAL CONSIDERATIONS

13.1 Waste treatment methods

Product

Offer surplus and non-recyclable solutions to a licensed disposal company. Dissolve or mix the material with a combustible solvent and burn in a chemical incinerator equipped with an afterburner and scrubber.

Contaminated packaging

Dispose of as unused product.

14. TRANSPORT INFORMATION**14.1 UN number**

ADR/RID: 2280

IMDG: 2280

IATA: 2280

14.2 UN proper shipping name

ADR/RID: HEXAMETHYLENEDIAMINE, SOLID

IMDG: HEXAMETHYLENEDIAMINE, SOLID

IATA: Hexamethylenediamine, solid

14.3 Transport hazard class(es)

ADR/RID: 8

IMDG: 8

IATA: 8

14.4 Packaging group

ADR/RID: III

IMDG: III

IATA: III

14.5 Environmental hazards

ADR/RID: no

IMDG Marine pollutant: no

IATA: no

14.6 Special precautions for user

no data available

15. REGULATORY INFORMATION

This safety datasheet complies with the requirements of Regulation (EC) No. 1907/2006.

15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

no data available

15.2 Chemical Safety Assessment

no data available

16. OTHER INFORMATION**Further information**

The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. The information in this document is based on the present state of our knowledge and is applicable to the product with regard to appropriate safety precautions. It does not represent any guarantee of the properties of the product.
