

## SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006 Version 5.3 Revision Date 09.04.2013

### SECTION 1: Identification of the substance/mixture and of the company/undertaking

#### 1.1 Product identifiers

Product name : Acetone

Product Number : 52-7402

Brand : Rapid

Index-No. : 606-001-00-8

REACH No. : A registration number is not available for this substance as the substance or its uses are exempted from registration, the annual tonnage does not require a registration or the registration is envisaged for a later registration deadline.

CAS-No. : 67-64-1

#### 1.2 Relevant identified uses of the substance or mixture and uses advised against

Identified uses : Laboratory chemicals, Manufacture of substances

#### 1.3 Details of the supplier of the safety data sheet

Company : Rapid Electronics,  
Severalls Lane,  
Colchester,  
Essex,  
CO4 5JS, United Kingdom

Telephone : +44 (0) 1206 751166

Fax : +44 (0) 1206 751188

- E-mail address : sales@rapidelec.co.uk

#### 1.4 Emergency telephone number

Emergency Phone # : +44 (0) 1206 751166

### SECTION 2: Hazards identification

#### 2.1 Classification of the substance or mixture

##### Classification according to Regulation (EC) No 1272/2008

Flammable liquids (Category 2), H225

Eye irritation (Category 2), H319

Specific target organ toxicity - single exposure (Category 3), Central nervous system, H336

For the full text of the H-Statements mentioned in this Section, see Section 16.

##### Classification according to EU Directives 67/548/EEC or 1999/45/EC

F	Highly flammable	R11
Xi	Irritant	R36
		R66
		R67

For the full text of the R-phrases mentioned in this Section, see Section 16.

#### 2.2 Label elements

##### Labelling according Regulation (EC) No 1272/2008

Pictogram



Signal word	Danger
Hazard statement(s)	
H225	Highly flammable liquid and vapour.
H319	Causes serious eye irritation.
H336	May cause drowsiness or dizziness.
Precautionary statement(s)	
P210	Keep away from heat/sparks/open flames/hot surfaces. - No smoking.
P261	Avoid breathing vapours.
P305 + P351 + P338	IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
Supplemental Hazard information (EU)	
EUH066	Repeated exposure may cause skin dryness or cracking.

### 2.3 Other hazards - none

## SECTION 3: Composition/information on ingredients

### 3.1 Substances

Formula	:	C <sub>3</sub> H <sub>6</sub> O
Molecular Weight	:	58.08 g/mol
CAS-No.	:	67-64-1
EC-No.	:	200-662-2
Index-No.	:	606-001-00-8

#### Hazardous ingredients according to Regulation (EC) No 1272/2008

Component	Classification	Concentration
<b>Acetone</b>		
	Flam. Liq. 2; Eye Irrit. 2; STOT SE 3; H225, H319, H336, EUH066	-

#### Hazardous ingredients according to Directive 1999/45/EC

Component	Classification	Concentration
<b>Acetone</b>		
	F, Xi, R11 - R36 - R66 - R67	-

For the full text of the H-Statements and R-Phrases mentioned in this Section, see Section 16

## SECTION 4: First aid measures

### 4.1 Description of first aid measures

#### General advice

Consult a physician. Show this safety data sheet to the doctor in attendance.

#### If inhaled

If breathed in, move person into fresh air. If not breathing, give artificial respiration. Consult a physician.

#### In case of skin contact

Wash off with soap and plenty of water. Consult a physician.

#### In case of eye contact

Rinse thoroughly with plenty of water for at least 15 minutes and consult a physician.

#### If swallowed

Do NOT induce vomiting. Never give anything by mouth to an unconscious person. Rinse mouth with water. Consult a physician.

### 4.2 Most important symptoms and effects, both acute and delayed

The most important known symptoms and effects are described in the labelling (see section 2.2) and/or in section 11

### 4.3 Indication of any immediate medical attention and special treatment needed

no data available

---

## SECTION 5: Firefighting measures

### 5.1 Extinguishing media

#### Suitable extinguishing media

Use water spray, alcohol-resistant foam, dry chemical or carbon dioxide.

### 5.2 Special hazards arising from the substance or mixture

Carbon oxides

### 5.3 Advice for firefighters

Wear self contained breathing apparatus for fire fighting if necessary.

### 5.4 Further information

Use water spray to cool unopened containers.

---

## SECTION 6: Accidental release measures

### 6.1 Personal precautions, protective equipment and emergency procedures

Use personal protective equipment. Avoid breathing vapours, mist or gas. Ensure adequate ventilation. Remove all sources of ignition. Evacuate personnel to safe areas. Beware of vapours accumulating to form explosive concentrations. Vapours can accumulate in low areas. For personal protection see section 8.

### 6.2 Environmental precautions

Prevent further leakage or spillage if safe to do so. Do not let product enter drains.

### 6.3 Methods and materials for containment and cleaning up

Contain spillage, and then collect with an electrically protected vacuum cleaner or by wet-brushing and place in container for disposal according to local regulations (see section 13).

### 6.4 Reference to other sections

For disposal see section 13.

---

## SECTION 7: Handling and storage

### 7.1 Precautions for safe handling

Avoid contact with skin and eyes. Avoid inhalation of vapour or mist. Keep away from sources of ignition - No smoking. Take measures to prevent the build up of electrostatic charge. For precautions see section 2.2.

### 7.2 Conditions for safe storage, including any incompatibilities

Store in cool place. Keep container tightly closed in a dry and well-ventilated place. Containers which are opened must be carefully resealed and kept upright to prevent leakage.

### 7.3 Specific end use(s)

A part from the uses mentioned in section 1.2 no other specific uses are stipulated

---

## SECTION 8: Exposure controls/personal protection

### 8.1 Control parameters

#### Components with workplace control parameters

Component	CAS-No.	Value	Control parameters	Basis
Acetone	67-64-1	STEL	1,500 ppm 3,620 mg/m <sup>3</sup>	UK. EH40 WEL - Workplace Exposure Limits
		TWA	500 ppm 1,210 mg/m <sup>3</sup>	UK. EH40 WEL - Workplace Exposure Limits
		TWA	500 ppm 1,210 mg/m <sup>3</sup>	Europe. Commission Directive 2000/39/EC establishing a first list of indicative occupational exposure limit values
	Remarks	Indicative		

## 8.2 Exposure controls

### Appropriate engineering controls

Handle in accordance with good industrial hygiene and safety practice. Wash hands before breaks and at the end of workday.

### Personal protective equipment

#### Eye/face protection

Face shield and safety glasses Use equipment for eye protection tested and approved under appropriate government standards such as NIOSH (US) or EN 166(EU).

#### Skin protection

Handle with gloves. Gloves must be inspected prior to use. Use proper glove removal technique (without touching glove's outer surface) to avoid skin contact with this product. Dispose of contaminated gloves after use in accordance with applicable laws and good laboratory practices. Wash and dry hands.

The selected protective gloves have to satisfy the specifications of EU Directive 89/686/EEC and the standard EN 374 derived from it.

#### Full contact

Material: butyl-rubber

Minimum layer thickness: 0.3 mm

Break through time: 480 min

Material tested: Butoject® (KCL 897 / Aldrich Z677647, Size M)

#### Splash contact

Material: butyl-rubber

Minimum layer thickness: 0.3 mm

Break through time: 480 min

Material tested: Butoject® (KCL 897 / Aldrich Z677647, Size M)

data source: KCL GmbH, D-36124 Eichenzell, phone +49 (0)6659 87300, e-mail sales@kcl.de, test method: EN374

If used in solution, or mixed with other substances, and under conditions which differ from EN 374, contact the supplier of the CE approved gloves. This recommendation is advisory only and must be evaluated by an industrial hygienist and safety officer familiar with the specific situation of anticipated use by our customers. It should not be construed as offering an approval for any specific use scenario.

#### Body Protection

impervious clothing, Flame retardant antistatic protective clothing, The type of protective equipment must be selected according to the concentration and amount of the dangerous substance at the specific workplace.

#### Respiratory protection

Where risk assessment shows air-purifying respirators are appropriate use a full-face respirator with multi-purpose combination (US) or type AXBEK (EN 14387) respirator cartridges as a backup to engineering controls. If the respirator is the sole means of protection, use a full-face supplied air respirator. Use respirators and components tested and approved under appropriate government standards such as NIOSH (US) or CEN (EU).

#### Control of environmental exposure

Prevent further leakage or spillage if safe to do so. Do not let product enter drains.

---

## SECTION 9: Physical and chemical properties

### 9.1 Information on basic physical and chemical properties

- |                    |   |
|--------------------|---|
| a) Appearance      | Form: liquid, clear<br>Colour: colourless |
| b) Odour           | no data available                         |
| c) Odour Threshold | no data available                         |
| d) pH              | no data available                         |

e) Melting point/freezing point	Melting point/range: -94 °C
f) Initial boiling point and boiling range	56 °C at 1,013 hPa
g) Flash point	no data available
h) Evaporation rate	no data available
i) Flammability (solid, gas)	no data available
j) Upper/lower flammability or explosive limits	Upper explosion limit: 13 %(V) Lower explosion limit: 2 %(V)
k) Vapour pressure	533.3 hPa at 39.5 °C 245.3 hPa at 20.0 °C
l) Vapour density	no data available
m) Relative density	0.791 g/mL at 25 °C
n) Water solubility	completely miscible
o) Partition coefficient: n-octanol/water	log Pow: -0.24
p) Auto-ignition temperature	465.0 °C
q) Decomposition temperature	no data available
r) Viscosity	no data available
s) Explosive properties	no data available
t) Oxidizing properties	no data available

## 9.2 Other safety information

Surface tension	23.2 mN/m at 20.0 °C
-----------------	----------------------

---

## SECTION 10: Stability and reactivity

### 10.1 Reactivity

no data available

### 10.2 Chemical stability

Stable under recommended storage conditions.

### 10.3 Possibility of hazardous reactions

no data available

### 10.4 Conditions to avoid

Heat, flames and sparks. Extremes of temperature and direct sunlight.

### 10.5 Incompatible materials

Bases, Oxidizing agents, Reducing agents, Acetone reacts violently with phosphorous oxychloride.

### 10.6 Hazardous decomposition products

Other decomposition products - no data available  
In the event of fire: see section 5

---

## SECTION 11: Toxicological information

### 11.1 Information on toxicological effects

#### Acute toxicity

LD50 Oral - rat - 5,800 mg/kg

Remarks: Behavioral: Altered sleep time (including change in righting reflex). Behavioral: Tremor.

LC50 Inhalation - rat - 8 h - 50,100 mg/m3

Inhalation: no data available

LD50 Dermal - guinea pig - 7,426 mg/kg

**Skin corrosion/irritation**

Skin - rabbit

Result: Mild skin irritation - 24 h

**Serious eye damage/eye irritation**

Eyes - rabbit

Result: Eye irritation - 24 h

**Respiratory or skin sensitisation**

no data available

**Germ cell mutagenicity**

no data available

**Carcinogenicity**

This product is or contains a component that is not classifiable as to its carcinogenicity based on its IARC, ACGIH, NTP, or EPA classification.

IARC: No component of this product present at levels greater than or equal to 0.1% is identified as probable, possible or confirmed human carcinogen by IARC.

**Reproductive toxicity**

no data available

**Specific target organ toxicity - single exposure**

May cause drowsiness or dizziness.

**Specific target organ toxicity - repeated exposure**

no data available

**Aspiration hazard**

no data available

**Additional Information**

RTECS: AL3150000

To the best of our knowledge, the chemical, physical, and toxicological properties have not been thoroughly investigated.

Kidney - Irregularities - Based on Human Evidence

---

**SECTION 12: Ecological information**

**12.1 Toxicity**

no data available

Toxicity to daphnia and other aquatic invertebrates      EC50 - Daphnia magna (Water flea) - 13,500.00 mg/l - 48 h

**12.2 Persistence and degradability**

no data available

**12.3 Bioaccumulative potential**

no data available

**12.4 Mobility in soil**

no data available

**12.5 Results of PBT and vPvB assessment**

PBT/vPvB assessment not available as chemical safety assessment not required/not conducted

**12.6 Other adverse effects**

no data available

---

## SECTION 13: Disposal considerations

### 13.1 Waste treatment methods

#### Product

Burn in a chemical incinerator equipped with an afterburner and scrubber but exert extra care in igniting as this material is highly flammable. Offer surplus and non-recyclable solutions to a licensed disposal company.

#### Contaminated packaging

Dispose of as unused product.

---

## SECTION 14: Transport information

### 14.1 UN number

ADR/RID: 1090

IMDG: 1090

IATA: 1090

### 14.2 UN proper shipping name

ADR/RID: ACETONE

IMDG: ACETONE

IATA: Acetone

### 14.3 Transport hazard class(es)

ADR/RID: 3

IMDG: 3

IATA: 3

### 14.4 Packaging group

ADR/RID: II

IMDG: II

IATA: II

### 14.5 Environmental hazards

ADR/RID: no

IMDG Marine pollutant: no

IATA: no

### 14.6 Special precautions for user

no data available

---

## SECTION 15: Regulatory information

This safety datasheet complies with the requirements of Regulation (EC) No. 1907/2006.

### 15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

no data available

### 15.2 Chemical Safety Assessment

For this product a chemical safety assessment was not carried out

---

## SECTION 16: Other information

### Full text of H-Statements referred to under sections 2 and 3.

EUH066	Repeated exposure may cause skin dryness or cracking.
Eye Irrit.	Eye irritation
Flam. Liq.	Flammable liquids
H225	Highly flammable liquid and vapour.
H319	Causes serious eye irritation.
H336	May cause drowsiness or dizziness.
STOT SE	Specific target organ toxicity - single exposure

### Full text of R-phrases referred to under sections 2 and 3

F	Highly flammable
Xi	Irritant
R11	Highly flammable.
R36	Irritating to eyes.
R66	Repeated exposure may cause skin dryness or cracking.
R67	Vapours may cause drowsiness and dizziness.

**Further information**

The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. The information in this document is based on the present state of our knowledge and is applicable to the product with regard to appropriate safety precautions. It does not represent any guarantee of the properties of the product.

---