

## SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006 Version 5.1 Revision Date 04.02.2013

### SECTION 1: Identification of the substance/mixture and of the company/undertaking

#### 1.1 Product identifiers

Product name : METHYLATED SPIRITS

Product Number : 52-7510

Brand : Rapid

Index-No. : 603-002-00-5

REACH No. : A registration number is not available for this substance as the substance or its uses are exempted from registration, the annual tonnage does not require a registration or the registration is envisaged for a later registration deadline.

CAS-No. : 64-17-5

#### 1.2 Relevant identified uses of the substance or mixture and uses advised against

Identified uses : Laboratory chemicals, Manufacture of substances

#### 1.3 Details of the supplier of the safety data sheet

Company : Rapid Electronics,  
Severalls Lane,  
Colchester,  
Essex,  
CO4 5JS, United Kingdom

Telephone : +44 (0) 1206 751166

Fax : +44 (0)1747 833313

E-mail address : sales@rapidelec.co.uk

#### 1.4 Emergency telephone number

Emergency Phone # : +44 (0) 1206 751166

### SECTION 2: Hazards identification

#### 2.1 Classification of the substance or mixture

##### Classification according to Regulation (EC) No 1272/2008

Flammable liquids (Category 2), H225

For the full text of the H-Statements mentioned in this Section, see Section 16.

##### Classification according to EU Directives 67/548/EEC or 1999/45/EC

F Highly flammable R11

For the full text of the R-phrases mentioned in this Section, see Section 16.

#### 2.2 Label elements

##### Labelling according Regulation (EC) No 1272/2008

Pictogram



Signal word

Danger

Hazard statement(s)

H225

Highly flammable liquid and vapour.

Precautionary statement(s) P210	Keep away from heat/sparks/open flames/hot surfaces. - No smoking.
Supplemental Hazard Statements	none

### 2.3 Other hazards - none

---

## SECTION 3: Composition/information on ingredients

### 3.1 Substances

Synonyms	:	Ethyl alcohol
Formula	:	C <sub>2</sub> H <sub>6</sub> O
Molecular Weight	:	46.07 g/mol
CAS-No.	:	64-17-5
EC-No.	:	200-578-6
Index-No.	:	603-002-00-5

No components need to be disclosed according to the applicable regulations.

For the full text of the H-Statements and R-Phrases mentioned in this Section, see Section 16

---

## SECTION 4: First aid measures

### 4.1 Description of first aid measures

#### General advice

Consult a physician. Show this safety data sheet to the doctor in attendance.

#### If inhaled

If breathed in, move person into fresh air. If not breathing, give artificial respiration. Consult a physician.

#### In case of skin contact

Wash off with soap and plenty of water. Consult a physician.

#### In case of eye contact

Rinse thoroughly with plenty of water for at least 15 minutes and consult a physician.

#### If swallowed

Do NOT induce vomiting. Never give anything by mouth to an unconscious person. Rinse mouth with water. Consult a physician.

### 4.2 Most important symptoms and effects, both acute and delayed

The most important known symptoms and effects are described in the labelling (see section 2.2) and/or in section 11

### 4.3 Indication of any immediate medical attention and special treatment needed

no data available

---

## SECTION 5: Firefighting measures

### 5.1 Extinguishing media

#### Suitable extinguishing media

Use water spray, alcohol-resistant foam, dry chemical or carbon dioxide.

### 5.2 Special hazards arising from the substance or mixture

no data available

### 5.3 Advice for firefighters

Wear self contained breathing apparatus for fire fighting if necessary.

### 5.4 Further information

Use water spray to cool unopened containers.

---

**SECTION 6: Accidental release measures****6.1 Personal precautions, protective equipment and emergency procedures**

Use personal protective equipment. Avoid breathing vapours, mist or gas. Ensure adequate ventilation. Remove all sources of ignition. Evacuate personnel to safe areas. Beware of vapours accumulating to form explosive concentrations. Vapours can accumulate in low areas.  
For personal protection see section 8.

**6.2 Environmental precautions**

Prevent further leakage or spillage if safe to do so. Do not let product enter drains.

**6.3 Methods and materials for containment and cleaning up**

Contain spillage, and then collect with an electrically protected vacuum cleaner or by wet-brushing and place in container for disposal according to local regulations (see section 13).

**6.4 Reference to other sections**

For disposal see section 13.

---

**SECTION 7: Handling and storage****7.1 Precautions for safe handling**

Avoid contact with skin and eyes. Avoid inhalation of vapour or mist.  
Keep away from sources of ignition - No smoking. Take measures to prevent the build up of electrostatic charge.  
For precautions see section 2.2.

**7.2 Conditions for safe storage, including any incompatibilities**

Store in cool place. Keep container tightly closed in a dry and well-ventilated place. Containers which are opened must be carefully resealed and kept upright to prevent leakage.  
Hygroscopic.

**7.3 Specific end use(s)**

A part from the uses mentioned in section 1.2 no other specific uses are stipulated

---

**SECTION 8: Exposure controls/personal protection****8.1 Control parameters****Components with workplace control parameters**

Component	CAS-No.	Value	Control parameters	Basis
Ethanol	64-17-5	TWA	1,000 ppm 1,920 mg/m <sup>3</sup>	UK. EH40 WEL - Workplace Exposure Limits
	Remarks	Where no specific short-term exposure limit is listed, a figure three times the long-term exposure should be used		

**8.2 Exposure controls****Appropriate engineering controls**

Handle in accordance with good industrial hygiene and safety practice. Wash hands before breaks and at the end of workday.

**Personal protective equipment****Eye/face protection**

Face shield and safety glasses Use equipment for eye protection tested and approved under appropriate government standards such as NIOSH (US) or EN 166(EU).

**Skin protection**

Handle with gloves. Gloves must be inspected prior to use. Use proper glove removal technique (without touching glove's outer surface) to avoid skin contact with this product. Dispose of contaminated gloves after use in accordance with applicable laws and good laboratory practices. Wash and dry hands.

The selected protective gloves have to satisfy the specifications of EU Directive 89/686/EEC and the standard EN 374 derived from it.

Full contact  
Material: butyl-rubber  
Minimum layer thickness: 0.3 mm  
Break through time: 480 min  
Material tested: Butoject® (KCL 897 / Aldrich Z677647, Size M)

Splash contact  
Material: Nitrile rubber  
Minimum layer thickness: 0.2 mm  
Break through time: 38 min  
Material tested: Dermatril® P (KCL 743 / Aldrich Z677388, Size M)

data source: KCL GmbH, D-36124 Eichenzell, phone +49 (0)6659 87300, e-mail sales@kcl.de,  
test method: EN374

If used in solution, or mixed with other substances, and under conditions which differ from EN 374, contact the supplier of the CE approved gloves. This recommendation is advisory only and must be evaluated by an industrial hygienist and safety officer familiar with the specific situation of anticipated use by our customers. It should not be construed as offering an approval for any specific use scenario.

### **Body Protection**

impervious clothing, Flame retardant antistatic protective clothing, The type of protective equipment must be selected according to the concentration and amount of the dangerous substance at the specific workplace.

### **Respiratory protection**

Where risk assessment shows air-purifying respirators are appropriate use a full-face respirator with multi-purpose combination (US) or type ABEK (EN 14387) respirator cartridges as a backup to engineering controls. If the respirator is the sole means of protection, use a full-face supplied air respirator. Use respirators and components tested and approved under appropriate government standards such as NIOSH (US) or CEN (EU).

### **Control of environmental exposure**

Prevent further leakage or spillage if safe to do so. Do not let product enter drains.

---

## **SECTION 9: Physical and chemical properties**

### **9.1 Information on basic physical and chemical properties**

a) Appearance	Form: liquid, clear Colour: colourless
b) Odour	no data available
c) Odour Threshold	no data available
d) pH	no data available
e) Melting point/freezing point	Melting point/range: -114 °C - lit.
f) Initial boiling point and boiling range	78.3 °C
g) Flash point	14.0 °C - closed cup
h) Evaporation rate	no data available
i) Flammability (solid, gas)	no data available
j) Upper/lower flammability or explosive limits	Upper explosion limit: 19 %(V) Lower explosion limit: 3.3 %(V)
k) Vapour pressure	59.5 hPa at 20.0 °C
l) Vapour density	no data available
m) Relative density	0.789 g/mL at 20 °C 0.789 g/mL at 25 °C
n) Water solubility	completely soluble

- |   |                   |
|---|-------------------|
| o) Partition coefficient: n-octanol/water | no data available |
| p) Auto-ignition temperature              | 363.0 °C          |
| q) Decomposition temperature              | no data available |
| r) Viscosity                              | no data available |
| s) Explosive properties                   | no data available |
| t) Oxidizing properties                   | no data available |

## 9.2 Other safety information

no data available

---

## SECTION 10: Stability and reactivity

### 10.1 Reactivity

no data available

### 10.2 Chemical stability

Stable under recommended storage conditions.

### 10.3 Possibility of hazardous reactions

no data available

### 10.4 Conditions to avoid

Heat, flames and sparks. Extremes of temperature and direct sunlight.

### 10.5 Incompatible materials

Alkali metals, Ammonia, Oxidizing agents, Peroxides

### 10.6 Hazardous decomposition products

Other decomposition products - no data available

In the event of fire: see section 5

---

## SECTION 11: Toxicological information

### 11.1 Information on toxicological effects

#### Acute toxicity

LD50 Oral - rat - 7,060 mg/kg

Remarks: Lungs, Thorax, or Respiration:Other changes.

LC50 Inhalation - rat - 10 h - 20000 ppm

#### Skin corrosion/irritation

Skin - rabbit

Result: Irritating to skin. - 24 h

#### Serious eye damage/eye irritation

Eyes - rabbit

Result: Mild eye irritation - 24 h

(Draize Test)

#### Respiratory or skin sensitisation

no data available

#### Germ cell mutagenicity

no data available

#### Carcinogenicity

Carcinogenicity - mouse - Oral

Tumorigenic: Equivocal tumorigenic agent by RTECS criteria. Liver: Tumors. Blood: Lymphomas including Hodgkin's disease.

IARC: No component of this product present at levels greater than or equal to 0.1% is identified as

probable, possible or confirmed human carcinogen by IARC.

### **Reproductive toxicity**

Reproductive toxicity - Human - female - Oral

Effects on Newborn: Apgar score (human only). Effects on Newborn: Other neonatal measures or effects.

Effects on Newborn: Drug dependence.

### **Specific target organ toxicity - single exposure**

no data available

### **Specific target organ toxicity - repeated exposure**

no data available

### **Aspiration hazard**

no data available

### **Additional Information**

RTECS: KQ6300000

Central nervous system depression, narcosis, Damage to the heart., To the best of our knowledge, the chemical, physical, and toxicological properties have not been thoroughly investigated.

Heart - Irregularities - Based on Human Evidence

---

## **SECTION 12: Ecological information**

### **12.1 Toxicity**

no data available

### **12.2 Persistence and degradability**

no data available

### **12.3 Bioaccumulative potential**

no data available

### **12.4 Mobility in soil**

no data available

### **12.5 Results of PBT and vPvB assessment**

PBT/vPvB assessment not available as chemical safety assessment not required/not conducted

### **12.6 Other adverse effects**

no data available

---

## **SECTION 13: Disposal considerations**

### **13.1 Waste treatment methods**

#### **Product**

Burn in a chemical incinerator equipped with an afterburner and scrubber but exert extra care in igniting as this material is highly flammable. Offer surplus and non-recyclable solutions to a licensed disposal company.

#### **Contaminated packaging**

Dispose of as unused product.

---

## **SECTION 14: Transport information**

### **14.1 UN number**

ADR/RID: 1170

IMDG: 1170

IATA: 1170

### **14.2 UN proper shipping name**

ADR/RID: ETHANOL

IMDG: ETHANOL

IATA: Ethanol

### **14.3 Transport hazard class(es)**

ADR/RID: 3

IMDG: 3

IATA: 3

<b>14.4 Packaging group</b>			
ADR/RID: II	IMDG: II		IATA: II
<b>14.5 Environmental hazards</b>			
ADR/RID: no	IMDG Marine pollutant: no		IATA: no
<b>14.6 Special precautions for user</b>			
no data available			

---

#### **SECTION 15: Regulatory information**

This safety datasheet complies with the requirements of Regulation (EC) No. 1907/2006.

#### **15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture**

no data available

#### **15.2 Chemical Safety Assessment**

For this product a chemical safety assessment was not carried out

---

#### **SECTION 16: Other information**

##### **Full text of H-Statements referred to under sections 2 and 3.**

H225                      Highly flammable liquid and vapour.

##### **Full text of R-phrases referred to under sections 2 and 3**

R11                      Highly flammable.

##### **Further information**

The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. The information in this document is based on the present state of our knowledge and is applicable to the product with regard to appropriate safety precautions. It does not represent any guarantee of the properties of the product.