

## SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006 Version 5.1 Revision Date 09.01.2013

### SECTION 1: Identification of the substance/mixture and of the company/undertaking

#### 1.1 Product identifiers

Product name : Sodium carbonate anhydrous

Product Number : 52-7543

Brand : Rapid

Index-No. : 011-005-00-2

REACH No. : A registration number is not available for this substance as the substance or its uses are exempted from registration, the annual tonnage does not require a registration or the registration is envisaged for a later registration deadline.

CAS-No. : 497-19-8

#### 1.2 Relevant identified uses of the substance or mixture and uses advised against

Identified uses : Laboratory chemicals, Manufacture of substances

#### 1.3 Details of the supplier of the safety data sheet

Company : Rapid Electronics,  
Severalls Lane,  
Colchester,  
Essex,  
CO4 5JS, United Kingdom

Telephone : +44 (0) 1206 751166

Fax : +44 (0) 1206 751188

E-mail address : sales@rapidelec.co.uk

#### 1.4 Emergency telephone number

Emergency Phone # : +44 (0) 1206 751166

### SECTION 2: Hazards identification

#### 2.1 Classification of the substance or mixture

##### Classification according to Regulation (EC) No 1272/2008

Eye irritation (Category 2), H319

For the full text of the H-Statements mentioned in this Section, see Section 16.

##### Classification according to EU Directives 67/548/EEC or 1999/45/EC

Xi Irritant R36

For the full text of the R-phrases mentioned in this Section, see Section 16.

#### 2.2 Label elements

##### Labelling according Regulation (EC) No 1272/2008

Pictogram



Signal word

Warning

Hazard statement(s)

H319

Causes serious eye irritation.

Precautionary statement(s)  
P305 + P351 + P338

IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

Supplemental Hazard Statements  
none

### 2.3 Other hazards - none

---

## SECTION 3: Composition/information on ingredients

### 3.1 Substances

Synonyms : Soda ash  
Formula :  $\text{CNa}_2\text{O}_3$   
Molecular Weight : 105.99 g/mol  
CAS-No. : 497-19-8  
EC-No. : 207-838-8  
Index-No. : 011-005-00-2

#### Hazardous ingredients according to Regulation (EC) No 1272/2008

Component	Classification	Concentration
<b>Sodium carbonate</b>		
	Eye Irrit. 2; H319	-

#### Hazardous ingredients according to Directive 1999/45/EC

Component	Classification	Concentration
<b>Sodium carbonate</b>		
	Xi, R36	-

For the full text of the H-Statements and R-Phrases mentioned in this Section, see Section 16

---

## SECTION 4: First aid measures

### 4.1 Description of first aid measures

#### General advice

Consult a physician. Show this safety data sheet to the doctor in attendance.

#### If inhaled

If breathed in, move person into fresh air. If not breathing, give artificial respiration. Consult a physician.

#### In case of skin contact

Wash off with soap and plenty of water. Consult a physician.

#### In case of eye contact

Rinse thoroughly with plenty of water for at least 15 minutes and consult a physician.

#### If swallowed

Never give anything by mouth to an unconscious person. Rinse mouth with water. Consult a physician.

### 4.2 Most important symptoms and effects, both acute and delayed

The most important known symptoms and effects are described in the labelling (see section 2.2) and/or in section 11

### 4.3 Indication of any immediate medical attention and special treatment needed

no data available

---

## SECTION 5: Firefighting measures

### 5.1 Extinguishing media

#### Suitable extinguishing media

Use water spray, alcohol-resistant foam, dry chemical or carbon dioxide.

- 5.2 Special hazards arising from the substance or mixture**  
Carbon oxides, Sodium oxides
- 5.3 Advice for firefighters**  
Wear self contained breathing apparatus for fire fighting if necessary.
- 5.4 Further information**  
no data available

---

**SECTION 6: Accidental release measures**

- 6.1 Personal precautions, protective equipment and emergency procedures**  
Use personal protective equipment. Avoid dust formation. Avoid breathing vapors, mist or gas. Ensure adequate ventilation. Avoid breathing dust.  
For personal protection see section 8.
- 6.2 Environmental precautions**  
Do not let product enter drains.
- 6.3 Methods and materials for containment and cleaning up**  
Pick up and arrange disposal without creating dust. Sweep up and shovel. Keep in suitable, closed containers for disposal.
- 6.4 Reference to other sections**  
For disposal see section 13.

---

**SECTION 7: Handling and storage**

- 7.1 Precautions for safe handling**  
Avoid contact with skin and eyes. Avoid formation of dust and aerosols.  
Provide appropriate exhaust ventilation at places where dust is formed.  
For precautions see section 2.2.
- 7.2 Conditions for safe storage, including any incompatibilities**  
Store in cool place. Keep container tightly closed in a dry and well-ventilated place.  
  
hygroscopic
- 7.3 Specific end use(s)**  
A part from the uses mentioned in section 1.2 no other specific uses are stipulated

---

**SECTION 8: Exposure controls/personal protection**

- 8.1 Control parameters**  
**Components with workplace control parameters**  
Contains no substances with occupational exposure limit values.
- 8.2 Exposure controls**  
**Appropriate engineering controls**  
Handle in accordance with good industrial hygiene and safety practice. Wash hands before breaks and at the end of workday.
- Personal protective equipment**  
**Eye/face protection**  
Safety glasses with side-shields conforming to EN166 Use equipment for eye protection tested and approved under appropriate government standards such as NIOSH (US) or EN 166(EU).
- Skin protection**  
Handle with gloves. Gloves must be inspected prior to use. Use proper glove removal technique (without touching glove's outer surface) to avoid skin contact with this product. Dispose of contaminated gloves after use in accordance with applicable laws and good laboratory practices. Wash and dry hands.  
  
The selected protective gloves have to satisfy the specifications of EU Directive 89/686/EEC and the standard EN 374 derived from it.  
  
Full contact

Material: Nitrile rubber  
Minimum layer thickness: 0.11 mm  
Break through time: 480 min  
Material tested: Dermatril® (KCL 740 / Aldrich Z677272, Size M)

Splash protection  
Material: Nitrile rubber  
Minimum layer thickness: 0.11 mm  
Break through time: 480 min  
Material tested: Dermatril® (KCL 740 / Aldrich Z677272, Size M)

data source: KCL GmbH, D-36124 Eichenzell, phone +49 (0)6659 87300, e-mail sales@kcl.de,  
test method: EN374

If used in solution, or mixed with other substances, and under conditions which differ from EN 374, contact the supplier of the CE approved gloves. This recommendation is advisory only and must be evaluated by an Industrial Hygienist familiar with the specific situation of anticipated use by our customers. It should not be construed as offering an approval for any specific use scenario.

### **Body Protection**

Impervious clothing., The type of protective equipment must be selected according to the concentration and amount of the dangerous substance at the specific workplace.

### **Respiratory protection**

For nuisance exposures use type P95 (US) or type P1 (EU EN 143) particle respirator. For higher level protection use type OV/AG/P99 (US) or type ABEK-P2 (EU EN 143) respirator cartridges. Use respirators and components tested and approved under appropriate government standards such as NIOSH (US) or CEN (EU).

### **Control of environmental exposure**

Do not let product enter drains.

---

## **SECTION 9: Physical and chemical properties**

### **9.1 Information on basic physical and chemical properties**

- |   |                                       |
|---|---------------------------------------|
| a) Appearance                                   | Form: powder<br>Colour: white         |
| b) Odour  | no data available                     |
| c) Odour Threshold                              | no data available                     |
| d) pH   | 12 at 106 g/l at 25 °C                |
| e) Melting point/freezing point                 | Melting point/range: 851 °C           |
| f) Initial boiling point and boiling range      | no data available                     |
| g) Flash point                                  | no data available                     |
| h) Evaporation rate                             | no data available                     |
| i) Flammability (solid, gas)                    | no data available                     |
| j) Upper/lower flammability or explosive limits | no data available                     |
| k) Vapour pressure                              | no data available                     |
| l) Vapour density                               | no data available                     |
| m) Relative density                             | 2.532 g/cm <sup>3</sup>               |
| n) Water solubility                             | 106 g/l at 20 °C - completely soluble |
| o) Partition coefficient: n-octanol/water       | no data available                     |
| p) Auto-ignition                                | no data available                     |

- temperature
- q) Decomposition temperature no data available
- r) Viscosity no data available
- s) Explosive properties no data available
- t) Oxidizing properties no data available

## 9.2 Other safety information

no data available

---

## SECTION 10: Stability and reactivity

### 10.1 Reactivity

no data available

### 10.2 Chemical stability

hygroscopic

Stable under recommended storage conditions.

### 10.3 Possibility of hazardous reactions

no data available

### 10.4 Conditions to avoid

Exposure to moisture.

### 10.5 Incompatible materials

Strong acids

### 10.6 Hazardous decomposition products

Other decomposition products - no data available

In the event of fire: see section 5

---

## SECTION 11: Toxicological information

### 11.1 Information on toxicological effects

#### Acute toxicity

LD50 Oral - rat - 4,090 mg/kg

LC50 Inhalation - rat - 2 h - 5,750 mg/l

#### Skin corrosion/irritation

Skin - rabbit

Result: Mild skin irritation - 24 h

#### Serious eye damage/eye irritation

Eyes - rabbit

Result: Eye irritation - 24 h

#### Respiratory or skin sensitization

no data available

#### Germ cell mutagenicity

no data available

#### Carcinogenicity

IARC: No component of this product present at levels greater than or equal to 0.1% is identified as probable, possible or confirmed human carcinogen by IARC.

#### Reproductive toxicity

no data available

#### Specific target organ toxicity - single exposure

no data available

#### Specific target organ toxicity - repeated exposure

no data available

**Aspiration hazard**

no data available

**Additional Information**

RTECS: VZ4050000

burning sensation, Cough, wheezing, laryngitis, Shortness of breath, Headache, Nausea, Vomiting

---

**SECTION 12: Ecological information****12.1 Toxicity**

Toxicity to fish LC50 - Lepomis macrochirus (Bluegill) - 300 mg/l - 96 h

Toxicity to daphnia and other aquatic invertebrates EC50 - Daphnia magna (Water flea) - 265 mg/l - 48 h

**12.2 Persistence and degradability**

no data available

**12.3 Bioaccumulative potential**

no data available

**12.4 Mobility in soil**

no data available

**12.5 Results of PBT and vPvB assessment**

PBT/vPvB assessment not available as chemical safety assessment not required/not conducted

**12.6 Other adverse effects**

no data available

---

**SECTION 13: Disposal considerations****13.1 Waste treatment methods****Product**

Offer surplus and non-recyclable solutions to a licensed disposal company. Dissolve or mix the material with a combustible solvent and burn in a chemical incinerator equipped with an afterburner and scrubber.

**Contaminated packaging**

Dispose of as unused product.

---

**SECTION 14: Transport information****14.1 UN number**

ADR/RID: - IMDG: - IATA: -

**14.2 UN proper shipping name**ADR/RID: Not dangerous goods  
IMDG: Not dangerous goods  
IATA: Not dangerous goods**14.3 Transport hazard class(es)**

ADR/RID: - IMDG: - IATA: -

**14.4 Packaging group**

ADR/RID: - IMDG: - IATA: -

**14.5 Environmental hazards**

ADR/RID: no IMDG Marine Pollutant: no IATA: no

**14.6 Special precautions for user**

no data available

---

**SECTION 15: Regulatory information**

This safety datasheet complies with the requirements of Regulation (EC) No. 1907/2006.

**15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture**

no data available

**15.2 Chemical Safety Assessment**

For this product a chemical safety assessment was not carried out

---

**SECTION 16: Other information**

**Full text of H-Statements referred to under sections 2 and 3.**

Eye Irrit.	Eye irritation
H319	Causes serious eye irritation.

**Full text of R-phrases referred to under sections 2 and 3**

Xi	Irritant
R36	Irritating to eyes.

**Further information**

The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. The information in this document is based on the present state of our knowledge and is applicable to the product with regard to appropriate safety precautions. It does not represent any guarantee of the properties of the product.