

## SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006 Version 5.0 Revision Date 05.07.2012

---

### 1. IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

#### 1.1 Product identifiers

Product name : D-GLUCOSE MONOHYDRATE

Product Number : 52-7465

Brand : Rapid

CAS-No. : 50-99-7

#### 1.2 Relevant identified uses of the substance or mixture and uses advised against

Identified uses : Laboratory chemicals, Manufacture of substances

#### 1.3 Details of the supplier of the safety data sheet

Company : Rapid Electronics,  
Severalls Lane,  
Colchester,  
Essex,  
CO4 5JS, United Kingdom

Telephone : +44 (0) 1206 751166

Fax : +44 (0) 1206 751188

E-mail address : sales@rapidelec.co.uk

#### 1.4 Emergency telephone number

Emergency Phone # : +44 (0) 1206 751166

---

### 2. HAZARDS IDENTIFICATION

#### 2.1 Classification of the substance or mixture

Not a hazardous substance or mixture according to Regulation (EC) No. 1272/2008.  
This substance is not classified as dangerous according to Directive 67/548/EEC.

#### 2.2 Label elements

The product does not need to be labelled in accordance with EC directives or respective national laws.

#### 2.3 Other hazards - none

---

### 3. COMPOSITION/INFORMATION ON INGREDIENTS

#### 3.1 Substances

Synonyms : D-(+)-Glucose  
Dextrose

Formula : C<sub>6</sub>H<sub>12</sub>O<sub>6</sub>

Molecular Weight : 180.16 g/mol

---

### 4. FIRST AID MEASURES

#### 4.1 Description of first aid measures

##### If inhaled

If breathed in, move person into fresh air. If not breathing, give artificial respiration.

**In case of skin contact**

Wash off with soap and plenty of water.

**In case of eye contact**

Flush eyes with water as a precaution.

**If swallowed**

Never give anything by mouth to an unconscious person. Rinse mouth with water.

**4.2 Most important symptoms and effects, both acute and delayed**

To the best of our knowledge, the chemical, physical, and toxicological properties have not been thoroughly investigated.

**4.3 Indication of any immediate medical attention and special treatment needed**

no data available

---

**5. FIREFIGHTING MEASURES****5.1 Extinguishing media****Suitable extinguishing media**

Use water spray, alcohol-resistant foam, dry chemical or carbon dioxide.

**5.2 Special hazards arising from the substance or mixture**

Carbon oxides

**5.3 Advice for firefighters**

Wear self contained breathing apparatus for fire fighting if necessary.

**5.4 Further information**

no data available

---

**6. ACCIDENTAL RELEASE MEASURES****6.1 Personal precautions, protective equipment and emergency procedures**

Avoid dust formation. Avoid breathing vapors, mist or gas.

**6.2 Environmental precautions**

Do not let product enter drains.

**6.3 Methods and materials for containment and cleaning up**

Sweep up and shovel. Keep in suitable, closed containers for disposal.

**6.4 Reference to other sections**

For disposal see section 13.

---

**7. HANDLING AND STORAGE****7.1 Precautions for safe handling**

Provide appropriate exhaust ventilation at places where dust is formed. Normal measures for preventive fire protection.

**7.2 Conditions for safe storage, including any incompatibilities**

Store in cool place. Keep container tightly closed in a dry and well-ventilated place.

**7.3 Specific end uses**

no data available

---

**8. EXPOSURE CONTROLS/PERSONAL PROTECTION****8.1 Control parameters****Components with workplace control parameters**

Contains no substances with occupational exposure limit values.

**8.2 Exposure controls****Appropriate engineering controls**

General industrial hygiene practice.

## Personal protective equipment

### Eye/face protection

Use equipment for eye protection tested and approved under appropriate government standards such as NIOSH (US) or EN 166(EU).

### Skin protection

Handle with gloves. Gloves must be inspected prior to use. Use proper glove removal technique (without touching glove's outer surface) to avoid skin contact with this product. Dispose of contaminated gloves after use in accordance with applicable laws and good laboratory practices. Wash and dry hands.

The selected protective gloves have to satisfy the specifications of EU Directive 89/686/EEC and the standard EN 374 derived from it.

#### Immersion protection

Material: Nitrile rubber

Minimum layer thickness: 0.11 mm

Break through time: > 480 min

Material tested: Dermatril® (Aldrich Z677272, Size M)

#### Splash protection

Material: Nitrile rubber

Minimum layer thickness: 0.11 mm

Break through time: > 30 min

Material tested: Dermatril® (Aldrich Z677272, Size M)

data source: KCL GmbH, D-36124 Eichenzell, phone +49 (0)6659 873000, e-mail sales@kcl.de, test method: EN374

If used in solution, or mixed with other substances, and under conditions which differ from EN 374, contact the supplier of the CE approved gloves. This recommendation is advisory only and must be evaluated by an Industrial Hygienist familiar with the specific situation of anticipated use by our customers. It should not be construed as offering an approval for any specific use scenario.

### Body Protection

Choose body protection in relation to its type, to the concentration and amount of dangerous substances, and to the specific work-place., The type of protective equipment must be selected according to the concentration and amount of the dangerous substance at the specific workplace.

### Respiratory protection

Respiratory protection is not required. Where protection from nuisance levels of dusts are desired, use type N95 (US) or type P1 (EN 143) dust masks. Use respirators and components tested and approved under appropriate government standards such as NIOSH (US) or CEN (EU).

---

## 9. PHYSICAL AND CHEMICAL PROPERTIES

### 9.1 Information on basic physical and chemical properties

- |  |  |
|--|--|
| a) Appearance                              | Form: crystalline, powder<br>Colour: white |
| b) Odour                                   | no data available                          |
| c) Odour Threshold                         | no data available                          |
| d) pH                                      | no data available                          |
| e) Melting point/freezing point            | Melting point/range: 150 - 152 °C          |
| f) Initial boiling point and boiling range | no data available                          |
| g) Flash point                             | no data available                          |
| h) Evaporation rate                        | no data available                          |
| i) Flammability (solid, gas)               | no data available                          |
| j) Upper/lower                             | no data available                          |

flammability or  
explosive limits

- |   |                   |
|---|-------------------|
| k) Vapour pressure                        | no data available |
| l) Vapour density                         | no data available |
| m) Relative density                       | no data available |
| n) Water solubility                       | soluble           |
| o) Partition coefficient: n-octanol/water | no data available |
| p) Autoignition temperature               | no data available |
| q) Decomposition temperature              | no data available |
| r) Viscosity                              | no data available |
| s) Explosive properties                   | no data available |
| t) Oxidizing properties                   | no data available |

## 9.2 Other safety information

no data available

---

## 10. STABILITY AND REACTIVITY

### 10.1 Reactivity

no data available

### 10.2 Chemical stability

no data available

### 10.3 Possibility of hazardous reactions

no data available

### 10.4 Conditions to avoid

no data available

### 10.5 Incompatible materials

Strong oxidizing agents

### 10.6 Hazardous decomposition products

Other decomposition products - no data available

---

## 11. TOXICOLOGICAL INFORMATION

### 11.1 Information on toxicological effects

#### Acute toxicity

LD50 Oral - rat - 25,800 mg/kg

Remarks: Behavioral:Coma. Cyanosis Diarrhoea

#### Skin corrosion/irritation

no data available

#### Serious eye damage/eye irritation

no data available

#### Respiratory or skin sensitization

no data available

#### Germ cell mutagenicity

Genotoxicity in vitro - mouse - lymphocyte

Mutation in mammalian somatic cells.

#### Carcinogenicity

IARC: No component of this product present at levels greater than or equal to 0.1% is identified as probable, possible or confirmed human carcinogen by IARC.

**Reproductive toxicity**

no data available

**Specific target organ toxicity - single exposure**

no data available

**Specific target organ toxicity - repeated exposure**

no data available

**Aspiration hazard**

no data available

**Potential health effects**

<b>Inhalation</b>	May be harmful if inhaled. May cause respiratory tract irritation.
<b>Ingestion</b>	May be harmful if swallowed.
<b>Skin</b>	May be harmful if absorbed through skin. May cause skin irritation.
<b>Eyes</b>	May cause eye irritation.

**Signs and Symptoms of Exposure**

To the best of our knowledge, the chemical, physical, and toxicological properties have not been thoroughly investigated.

**Additional Information**

RTECS: Not available

---

**12. ECOLOGICAL INFORMATION**

**12.1 Toxicity**

no data available

**12.2 Persistence and degradability**

no data available

**12.3 Bioaccumulative potential**

no data available

**12.4 Mobility in soil**

no data available

**12.5 Results of PBT and vPvB assessment**

no data available

**12.6 Other adverse effects**

no data available

---

**13. DISPOSAL CONSIDERATIONS**

**13.1 Waste treatment methods**

**Product**

Offer surplus and non-recyclable solutions to a licensed disposal company.

**Contaminated packaging**

Dispose of as unused product.

---

**14. TRANSPORT INFORMATION**

**14.1 UN number**

ADR/RID: -

IMDG: -

IATA: -

**14.2 UN proper shipping name**

ADR/RID: Not dangerous goods

IMDG: Not dangerous goods

IATA: Not dangerous goods

<b>14.3 Transport hazard class(es)</b>			
ADR/RID: -	IMDG: -		IATA: -
<b>14.4 Packaging group</b>			
ADR/RID: -	IMDG: -		IATA: -
<b>14.5 Environmental hazards</b>			
ADR/RID: no	IMDG Marine pollutant: no		IATA: no
<b>14.6 Special precautions for user</b>			
no data available			

---

## 15. REGULATORY INFORMATION

This safety datasheet complies with the requirements of Regulation (EC) No. 1907/2006.

**15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture**  
no data available

**15.2 Chemical Safety Assessment**  
no data available

---

## 16. OTHER INFORMATION

### Further information

The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. The information in this document is based on the present state of our knowledge and is applicable to the product with regard to appropriate safety precautions. It does not represent any guarantee of the properties of the product.

---