

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006 (Reach)

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1 Product identifiers

Product name : Propionaldehyde

Product Number : CHE5862
Brand : RAPID
Index-No. : 605-018-00-8
REACH No. : A registration number is not available for this substance as the substance or its uses are exempted from registration, the annual tonnage does not require a registration or the registration is envisaged for a later registration deadline.

CAS-No. : 123-38-6

1.2 Relevant identified uses of the substance or mixture and uses advised against

Identified uses : Laboratory chemicals, Manufacture of substances

1.3 Details of the supplier of the safety data sheet

Company : Rapid Electronics,
Severalls Lane,
Colchester,
Essex,
CO4 5JS, United Kingdom

Telephone : +44 (0) 1206 751166
Fax : +44 (0) 1206 751188
E-mail address : sales@rapidelec.co.uk
Emergency telephone number
Emergency Phone # : +44 (0) 1206 751166

SECTION 2: Hazards identification

2.1 Classification of the substance or mixture

Classification according to Regulation (EC) No 1272/2008

Flammable liquids (Category 2), H225
Acute toxicity, Oral (Category 4), H302
Acute toxicity, Inhalation (Category 4), H332
Skin irritation (Category 2), H315
Serious eye damage (Category 1), H318
Specific target organ toxicity - single exposure (Category 3), Respiratory system, H335

For the full text of the H-Statements mentioned in this Section, see Section 16.

Classification according to EU Directives 67/548/EEC or 1999/45/EC

F	Highly flammable	R11
Xn	Harmful	R20/22
Xi	Irritant	R41, R37/38

For the full text of the R-phrases mentioned in this Section, see Section 16.

2.2 Label elements

Labelling according Regulation (EC) No 1272/2008

Pictogram



Signal word

Danger

Hazard statement(s)

H225

Highly flammable liquid and vapour.

H302 + H332

Harmful if swallowed or if inhaled

H315

Causes skin irritation.

H318

Causes serious eye damage.

H335

May cause respiratory irritation.

Precautionary statement(s)

P210

Keep away from heat/sparks/open flames/hot surfaces. - No smoking.

P261

Avoid breathing vapours.

P280

Wear protective gloves/ eye protection/ face protection.

P305 + P351 + P338

IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

Supplemental Hazard Statements

none

2.3 Other hazards

Stench.

SECTION 3: Composition/information on ingredients

3.1 Substances

Synonyms : Propanal
Aldehyde C-3

Formula : C₃H₆O
Molecular Weight : 58.08 g/mol
CAS-No. : 123-38-6
EC-No. : 204-623-0
Index-No. : 605-018-00-8

Hazardous ingredients according to Regulation (EC) No 1272/2008

Component	Classification	Concentration
Propanal		
CAS-No. 123-38-6 EC-No. 204-623-0 Index-No. 605-018-00-8	Flam. Liq. 2; Acute Tox. 4; Skin Irrit. 2; Eye Irrit. 1; STOT SE 3; H225, H302 + H332, H315, H318, H335	<= 100 %

Hazardous ingredients according to Directive 1999/45/EC

Component	Classification	Concentration
Propanal		
CAS-No. 123-38-6 EC-No. 204-623-0 Index-No. 605-018-00-8	F, Xn, R11 - R20/22 - R37/38 - R41	<= 100 %

For the full text of the H-Statements and R-Phrases mentioned in this Section, see Section 16

SECTION 4: First aid measures

4.1 Description of first aid measures

General advice

Consult a physician. Show this safety data sheet to the doctor in attendance.

If inhaled

If breathed in, move person into fresh air. If not breathing, give artificial respiration. Consult a physician.

In case of skin contact

Wash off with soap and plenty of water. Consult a physician.

In case of eye contact

Rinse thoroughly with plenty of water for at least 15 minutes and consult a physician.

If swallowed

Do NOT induce vomiting. Never give anything by mouth to an unconscious person. Rinse mouth with water. Consult a physician.

4.2 Most important symptoms and effects, both acute and delayed

The most important known symptoms and effects are described in the labelling (see section 2.2) and/or in section 11

4.3 Indication of any immediate medical attention and special treatment needed

no data available

SECTION 5: Firefighting measures**5.1 Extinguishing media****Suitable extinguishing media**

Use water spray, alcohol-resistant foam, dry chemical or carbon dioxide.

5.2 Special hazards arising from the substance or mixture

Carbon oxides

5.3 Advice for firefighters

Wear self contained breathing apparatus for fire fighting if necessary.

5.4 Further information

Use water spray to cool unopened containers.

SECTION 6: Accidental release measures**6.1 Personal precautions, protective equipment and emergency procedures**

Use personal protective equipment. Avoid breathing vapours, mist or gas. Ensure adequate ventilation. Remove all sources of ignition. Evacuate personnel to safe areas. Beware of vapours accumulating to form explosive concentrations. Vapours can accumulate in low areas. For personal protection see section 8.

6.2 Environmental precautions

Prevent further leakage or spillage if safe to do so. Do not let product enter drains. Discharge into the environment must be avoided.

6.3 Methods and materials for containment and cleaning up

Contain spillage, and then collect with an electrically protected vacuum cleaner or by wet-brushing and place in container for disposal according to local regulations (see section 13).

6.4 Reference to other sections

For disposal see section 13.

SECTION 7: Handling and storage**7.1 Precautions for safe handling**

Avoid contact with skin and eyes. Avoid inhalation of vapour or mist.

Keep away from sources of ignition - No smoking. Take measures to prevent the build up of electrostatic charge.

For precautions see section 2.2.

7.2 Conditions for safe storage, including any incompatibilities

Store in cool place. Keep container tightly closed in a dry and well-ventilated place. Containers which are opened must be carefully resealed and kept upright to prevent leakage. Recommended storage temperature: 2 - 8 °C

Handle and open container with care. Handle and store under inert gas. Air and moisture sensitive.

7.3 Specific end use(s)

Apart from the uses mentioned in section 1.2 no other specific uses are stipulated

SECTION 8: Exposure controls/personal protection

8.1 Control parameters

Components with workplace control parameters

Contains no substances with occupational exposure limit values.

8.2 Exposure controls

Appropriate engineering controls

Handle in accordance with good industrial hygiene and safety practice. Wash hands before breaks and at the end of workday.

Personal protective equipment

Eye/face protection

Tightly fitting safety goggles. Faceshield (8-inch minimum). Use equipment for eye protection tested and approved under appropriate government standards such as NIOSH (US) or EN 166(EU).

Skin protection

Handle with gloves. Gloves must be inspected prior to use. Use proper glove removal technique (without touching glove's outer surface) to avoid skin contact with this product. Dispose of contaminated gloves after use in accordance with applicable laws and good laboratory practices. Wash and dry hands.

The selected protective gloves have to satisfy the specifications of EU Directive 89/686/EEC and the standard EN 374 derived from it.

Splash contact

Material: butyl-rubber

Minimum layer thickness: 0.3 mm

Break through time: 343 min

Material tested: Butoject® (KCL 897 / Aldrich Z677647, Size M)

data source: KCL GmbH, D-36124 Eichenzell, phone +49 (0)6659 87300, e-mail sales@kcl.de, test method: EN374

If used in solution, or mixed with other substances, and under conditions which differ from EN 374, contact the supplier of the CE approved gloves. This recommendation is advisory only and must be evaluated by an industrial hygienist and safety officer familiar with the specific situation of anticipated use by our customers. It should not be construed as offering an approval for any specific use scenario.

Body Protection

Complete suit protecting against chemicals, Flame retardant antistatic protective clothing, The type of protective equipment must be selected according to the concentration and amount of the dangerous substance at the specific workplace.

Respiratory protection

Where risk assessment shows air-purifying respirators are appropriate use a full-face respirator with multi-purpose combination (US) or type AXBEK (EN 14387) respirator cartridges as a backup to engineering controls. If the respirator is the sole means of protection, use a full-face supplied air respirator. Use respirators and components tested and approved under appropriate government standards such as NIOSH (US) or CEN (EU).

Control of environmental exposure

Prevent further leakage or spillage if safe to do so. Do not let product enter drains. Discharge into the environment must be avoided.

SECTION 9: Physical and chemical properties

9.1 Information on basic physical and chemical properties

a) Appearance	Form: clear, liquid Colour: colourless
b) Odour	Stench.
c) Odour Threshold	no data available
d) pH	no data available
e) Melting point/freezing point	Melting point/range: -81 °C - lit.
f) Initial boiling point and boiling range	46 - 50 °C - lit.
g) Flash point	-40 °C - closed cup
h) Evaporation rate	no data available
i) Flammability (solid, gas)	no data available
j) Upper/lower flammability or explosive limits	Upper explosion limit: 16.1 %(V) Lower explosion limit: 2.6 %(V)
k) Vapour pressure	343 hPa at 20 °C
l) Vapour density	2.01 - (Air = 1.0)
m) Relative density	0.805 g/cm ³ at 25 °C
n) Water solubility	completely soluble
o) Partition coefficient: n-octanol/water	log Pow: 0.83
p) Auto-ignition temperature	no data available
q) Decomposition temperature	no data available
r) Viscosity	no data available
s) Explosive properties	no data available
t) Oxidizing properties	no data available

9.2 Other safety information

Surface tension	23.4 mN/m at 20 °C
Relative vapour density	2.01 - (Air = 1.0)

SECTION 10: Stability and reactivity

10.1 Reactivity

no data available

10.2 Chemical stability

Stable under recommended storage conditions.

10.3 Possibility of hazardous reactions

no data available

10.4 Conditions to avoid

Heat, flames and sparks. Extremes of temperature and direct sunlight.

10.5 Incompatible materials

Oxidizing agents, Strong bases, Strong reducing agents

10.6 Hazardous decomposition products

Other decomposition products - no data available

In the event of fire: see section 5

SECTION 11: Toxicological information

11.1 Information on toxicological effects

Acute toxicity

LD50 Oral - rat - 1,690 mg/kg

(OECD Test Guideline 401)

LC50 Inhalation - rat - 4 h - > 4.6 mg/l

(OECD Test Guideline 403)

LD50 Dermal - rabbit - 2,460 mg/kg

Remarks: Behavioral:Somnolence (general depressed activity). Behavioral:Convulsions or effect on seizure threshold. Lungs, Thorax, or Respiration:Dyspnea.

Skin corrosion/irritation

Irritating to skin.

Serious eye damage/eye irritation

Eyes - rabbit

Result: Risk of serious damage to eyes.

(OECD Test Guideline 405)

Respiratory or skin sensitisation

no data available

Germ cell mutagenicity

in vitro assay

Other cell types

Result: positive

DNA damage

Ames test

Result: Not mutagenic in Ames Test.

Mutagenicity (micronucleus test)

mouse

Result: In vivo tests did not show any chromosomal changes.

Carcinogenicity

IARC: No component of this product present at levels greater than or equal to 0.1% is identified as probable, possible or confirmed human carcinogen by IARC.

Reproductive toxicity

no data available

Specific target organ toxicity - single exposure

May cause respiratory irritation.

Specific target organ toxicity - repeated exposure

no data available

Aspiration hazard

no data available

Additional Information

RTECS: UE0350000

Material is extremely destructive to tissue of the mucous membranes and upper respiratory tract, eyes, and skin., Cough, Shortness of breath, Headache, Nausea

SECTION 12: Ecological information**12.1 Toxicity**

Toxicity to fish LC50 - Pimephales promelas (fathead minnow) - 14 mg/l - 96 h

12.2 Persistence and degradability

Biodegradability Result: - Readily biodegradable.

Ratio BOD/ThBOD 95 %

12.3 Bioaccumulative potential

no data available

12.4 Mobility in soil

no data available

12.5 Results of PBT and vPvB assessment

PBT/vPvB assessment not available as chemical safety assessment not required/not conducted

12.6 Other adverse effects

Harmful to aquatic life.

no data available

SECTION 13: Disposal considerations**13.1 Waste treatment methods****Product**

Burn in a chemical incinerator equipped with an afterburner and scrubber but exert extra care in igniting as this material is highly flammable. Offer surplus and non-recyclable solutions to a licensed disposal company.

Contaminated packaging

Dispose of as unused product.

SECTION 14: Transport information**14.1 UN number**

ADR/RID: 1275

IMDG: 1275

IATA: 1275

14.2 UN proper shipping name

ADR/RID: PROPIONALDEHYDE

IMDG: PROPIONALDEHYDE

IATA: Propionaldehyde

14.3 Transport hazard class(es)

ADR/RID: 3

IMDG: 3

IATA: 3

14.4 Packaging group

ADR/RID: II

IMDG: II

IATA: II

14.5 Environmental hazards

ADR/RID: no

IMDG Marine pollutant: no

IATA: no

14.6 Special precautions for user

no data available

SECTION 15: Regulatory information

This safety datasheet complies with the requirements of Regulation (EC) No. 1907/2006.

15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

no data available

15.2 Chemical Safety Assessment

For this product a chemical safety assessment was not carried out

SECTION 16: Other information

Full text of H-Statements referred to under sections 2 and 3.

Acute Tox.	Acute toxicity
Eye Irrit.	Eye irritation
Flam. Liq.	Flammable liquids
H225	Highly flammable liquid and vapour.
H302	Harmful if swallowed.
H302 + H332	Harmful if swallowed or if inhaled
H315	Causes skin irritation.
H318	Causes serious eye damage.
H332	Harmful if inhaled.

Full text of R-phrases referred to under sections 2 and 3

F	Highly flammable
Xn	Harmful
R11	Highly flammable.
R20/22	Harmful by inhalation and if swallowed.
R37/38	Irritating to respiratory system and skin.
R41	Risk of serious damage to eyes.

Further information

The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. The information in this document is based on the present state of our knowledge and is applicable to the product with regard to appropriate safety precautions. It does not represent any guarantee of the properties of the product.