

## SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006

### SECTION 1: Identification of the substance/mixture and of the company/undertaking

#### 1.1 Product identifiers

Product name : Isoamyl alcohol

Product Number : 52-7613

Brand : RAPID

Index-No. : 603-006-00-7

REACH No. : A registration number is not available for this substance as the substance or its uses are exempted from registration, the annual tonnage does not require a registration or the registration is envisaged for a later registration deadline.

CAS-No. : 123-51-3

#### 1.2 Relevant identified uses of the substance or mixture and uses advised against

Identified uses : Laboratory chemicals, Manufacture of substances

#### 1.3 Details of the supplier of the safety data sheet

Company : Rapid Electronics,  
Severalls Lane,  
Colchester,  
Essex,  
CO4 5JS, United Kingdom

Telephone : +44 (0) 1206 751166

Fax : +44 (0) 1206 751188

E-mail address : sales@rapidelec.co.uk

Emergency telephone number  
Emergency Phone # : +44 (0) 1206 751166

### SECTION 2: Hazards identification

#### 2.1 Classification of the substance or mixture

##### Classification according to Regulation (EC) No 1272/2008

Flammable liquids (Category 3), H226  
Acute toxicity, Inhalation (Category 4), H332  
Specific target organ toxicity - single exposure (Category 3), H335

For the full text of the H-Statements mentioned in this Section, see Section 16.

##### Classification according to EU Directives 67/548/EEC or 1999/45/EC

		R10
Xn	Harmful	R20
Xi	Irritant	R37
		R66

For the full text of the R-phrases mentioned in this Section, see Section 16.

#### 2.2 Label elements

##### Labelling according Regulation (EC) No 1272/2008

Pictogram



Signal word	Warning
Hazard statement(s)	
H226	Flammable liquid and vapour.
H332	Harmful if inhaled.
H335	May cause respiratory irritation.
Precautionary statement(s)	
P261	Avoid breathing vapours.
Supplemental Hazard information (EU)	
EUH066	Repeated exposure may cause skin dryness or cracking.

### 2.3 Other hazards - none

## SECTION 3: Composition/information on ingredients

### 3.1 Substances

Synonyms	:	3-Methyl-1-butanol Isoamyl alcohol Isopentyl alcohol
Formula	:	C <sub>5</sub> H <sub>12</sub> O
Molecular Weight	:	88.15 g/mol
CAS-No.	:	123-51-3
EC-No.	:	204-633-5
Index-No.	:	603-006-00-7

#### Hazardous ingredients according to Regulation (EC) No 1272/2008

Component	Classification	Concentration
<b>3-Methylbutan-1-ol</b>		
CAS-No.	123-51-3	Flam. Liq. 3; Acute Tox. 4; STOT SE 3; H226, H332, H335, EUH066
EC-No.	204-633-5	
Index-No.	603-006-00-7	
		<= 100 %

#### Hazardous ingredients according to Directive 1999/45/EC

Component	Classification	Concentration
<b>3-Methylbutan-1-ol</b>		
CAS-No.	123-51-3	Xn, R10 - R20 - R37 - R66
EC-No.	204-633-5	
Index-No.	603-006-00-7	
		<= 100 %

For the full text of the H-Statements and R-Phrases mentioned in this Section, see Section 16

## SECTION 4: First aid measures

### 4.1 Description of first aid measures

#### General advice

Consult a physician. Show this safety data sheet to the doctor in attendance.

#### If inhaled

If breathed in, move person into fresh air. If not breathing, give artificial respiration. Consult a physician.

#### In case of skin contact

Wash off with soap and plenty of water. Consult a physician.

#### In case of eye contact

Rinse thoroughly with plenty of water for at least 15 minutes and consult a physician.

**If swallowed**

Do NOT induce vomiting. Never give anything by mouth to an unconscious person. Rinse mouth with water. Consult a physician.

**4.2 Most important symptoms and effects, both acute and delayed**

The most important known symptoms and effects are described in the labelling (see section 2.2) and/or in section 11

**4.3 Indication of any immediate medical attention and special treatment needed**

no data available

---

**SECTION 5: Firefighting measures****5.1 Extinguishing media****Suitable extinguishing media**

For small (incipient) fires, use media such as "alcohol" foam, dry chemical, or carbon dioxide. For large fires, apply water from as far as possible. Use very large quantities (flooding) of water applied as a mist or spray; solid streams of water may be ineffective. Cool all affected containers with flooding quantities of water.

**5.2 Special hazards arising from the substance or mixture**

Carbon oxides

Nature of decomposition products not known.

**5.3 Advice for firefighters**

Wear self contained breathing apparatus for fire fighting if necessary.

**5.4 Further information**

Use water spray to cool unopened containers.

---

**SECTION 6: Accidental release measures****6.1 Personal precautions, protective equipment and emergency procedures**

Use personal protective equipment. Avoid breathing vapours, mist or gas. Ensure adequate ventilation. Remove all sources of ignition. Beware of vapours accumulating to form explosive concentrations. Vapours can accumulate in low areas. For personal protection see section 8.

**6.2 Environmental precautions**

Prevent further leakage or spillage if safe to do so. Do not let product enter drains.

**6.3 Methods and materials for containment and cleaning up**

Contain spillage, and then collect with an electrically protected vacuum cleaner or by wet-brushing and place in container for disposal according to local regulations (see section 13).

**6.4 Reference to other sections**

For disposal see section 13.

---

**SECTION 7: Handling and storage****7.1 Precautions for safe handling**

Avoid contact with skin and eyes. Avoid inhalation of vapour or mist. Keep away from sources of ignition - No smoking. Take measures to prevent the build up of electrostatic charge. For precautions see section 2.2.

**7.2 Conditions for safe storage, including any incompatibilities**

Store in cool place. Keep container tightly closed in a dry and well-ventilated place. Containers which are opened must be carefully resealed and kept upright to prevent leakage.

**7.3 Specific end use(s)**

Apart from the uses mentioned in section 1.2 no other specific uses are stipulated

## SECTION 8: Exposure controls/personal protection

### 8.1 Control parameters

#### Components with workplace control parameters

Component	CAS-No.	Value	Control parameters	Basis
3-Methylbutan-1-ol	123-51-3	TWA	100 ppm 366 mg/m <sup>3</sup>	UK. EH40 WEL - Workplace Exposure Limits
		STEL	125 ppm 458 mg/m <sup>3</sup>	UK. EH40 WEL - Workplace Exposure Limits

### 8.2 Exposure controls

#### Appropriate engineering controls

Handle in accordance with good industrial hygiene and safety practice. Wash hands before breaks and at the end of workday.

#### Personal protective equipment

##### Eye/face protection

Face shield and safety glasses Use equipment for eye protection tested and approved under appropriate government standards such as NIOSH (US) or EN 166(EU).

##### Skin protection

Handle with gloves. Gloves must be inspected prior to use. Use proper glove removal technique (without touching glove's outer surface) to avoid skin contact with this product. Dispose of contaminated gloves after use in accordance with applicable laws and good laboratory practices. Wash and dry hands.

The selected protective gloves have to satisfy the specifications of EU Directive 89/686/EEC and the standard EN 374 derived from it.

##### Full contact

Material: Nitrile rubber

Minimum layer thickness: 0.11 mm

Break through time: 480 min

Material tested: Dermatril® (KCL 740 / Aldrich Z677272, Size M)

##### Splash contact

Material: Nitrile rubber

Minimum layer thickness: 0.11 mm

Break through time: 480 min

Material tested: Dermatril® (KCL 740 / Aldrich Z677272, Size M)

data source: KCL GmbH, D-36124 Eichenzell, phone +49 (0)6659 87300, e-mail sales@kcl.de, test method: EN374

If used in solution, or mixed with other substances, and under conditions which differ from EN 374, contact the supplier of the CE approved gloves. This recommendation is advisory only and must be evaluated by an industrial hygienist and safety officer familiar with the specific situation of anticipated use by our customers. It should not be construed as offering an approval for any specific use scenario.

##### Body Protection

Complete suit protecting against chemicals, Flame retardant antistatic protective clothing, The type of protective equipment must be selected according to the concentration and amount of the dangerous substance at the specific workplace.

##### Respiratory protection

Where risk assessment shows air-purifying respirators are appropriate use a full-face respirator with multi-purpose combination (US) or type ABEK (EN 14387) respirator cartridges as a backup to engineering controls. If the respirator is the sole means of protection, use a full-face supplied air respirator. Use respirators and components tested and approved under appropriate government standards such as NIOSH (US) or CEN (EU).

## Control of environmental exposure

Prevent further leakage or spillage if safe to do so. Do not let product enter drains.

---

### SECTION 9: Physical and chemical properties

#### 9.1 Information on basic physical and chemical properties

a) Appearance	Form: liquid, clear Colour: colourless
b) Odour	no data available
c) Odour Threshold	no data available
d) pH	5.6 at 25 g/l at 20 °C
e) Melting point/freezing point	Melting point/range: -117 °C - lit.
f) Initial boiling point and boiling range	130 °C - lit.
g) Flash point	43 °C - closed cup
h) Evaporation rate	no data available
i) Flammability (solid, gas)	no data available
j) Upper/lower flammability or explosive limits	Upper explosion limit: 9 %(V) Lower explosion limit: 1.2 %(V)
k) Vapour pressure	3 hPa at 20 °C 23.6 hPa at 50 °C
l) Vapour density	3.04 - (Air = 1.0)
m) Relative density	0.809 g/cm <sup>3</sup> at 25 °C
n) Water solubility	soluble
o) Partition coefficient: n-octanol/water	log Pow: 1.28
p) Auto-ignition temperature	no data available
q) Decomposition temperature	no data available
r) Viscosity	no data available
s) Explosive properties	no data available
t) Oxidizing properties	no data available

#### 9.2 Other safety information

Bulk density	808 kg/m <sup>3</sup>
Relative vapour density	3.04 - (Air = 1.0)

---

### SECTION 10: Stability and reactivity

#### 10.1 Reactivity

no data available

#### 10.2 Chemical stability

Stable under recommended storage conditions.

Test for peroxide formation before distillation or evaporation. Test for peroxide formation or discard after 1 year.

- 10.3 Possibility of hazardous reactions**  
no data available
- 10.4 Conditions to avoid**  
Heat, flames and sparks.
- 10.5 Incompatible materials**  
Strong oxidizing agents, Acid chlorides, Acid anhydrides, Reducing agents
- 10.6 Hazardous decomposition products**  
Other decomposition products - no data available  
In the event of fire: see section 5

---

## SECTION 11: Toxicological information

### 11.1 Information on toxicological effects

#### Acute toxicity

LD50 Oral - rat - > 5,000 mg/kg

LC50 Inhalation - rat - male and female - 6 h - > 14 mg/l

LD50 Dermal - rabbit - > 3,000 mg/kg

#### Skin corrosion/irritation

Skin - rabbit

Result: Skin irritation

#### Serious eye damage/eye irritation

Eyes - rabbit Result:

Eye irritation

#### Respiratory or skin sensitisation

no data available

#### Germ cell mutagenicity

no data available

#### Carcinogenicity

IARC: No component of this product present at levels greater than or equal to 0.1% is identified as probable, possible or confirmed human carcinogen by IARC.

#### Reproductive toxicity

no data available

#### Specific target organ toxicity - single exposure

May cause respiratory irritation.

#### Specific target organ toxicity - repeated exposure

no data available

#### Aspiration hazard

no data available

#### Additional Information

RTECS: EL5425000

prolonged or repeated exposure can cause: Nausea, Headache, Vomiting, To the best of our knowledge, the chemical, physical, and toxicological properties have not been thoroughly investigated.

Liver - Irregularities - Based on Human Evidence

---

## SECTION 12: Ecological information

### 12.1 Toxicity

Toxicity to daphnia and other aquatic invertebrates EC50 - Daphnia magna (Water flea) - 260 mg/l - 48 h

Toxicity to algae                      EC50 - Desmodesmus subspicatus (green algae) - 490 mg/l - 72 h

**12.2 Persistence and degradability**

Biodegradability                      Result: > 70 % - Readily biodegradable.

**12.3 Bioaccumulative potential**

no data available

**12.4 Mobility in soil**

no data available

**12.5 Results of PBT and vPvB assessment**

PBT/vPvB assessment not available as chemical safety assessment not required/not conducted

**12.6 Other adverse effects**

no data available

---

**SECTION 13: Disposal considerations**

**13.1 Waste treatment methods**

**Product**

Burn in a chemical incinerator equipped with an afterburner and scrubber but exert extra care in igniting as this material is highly flammable. Offer surplus and non-recyclable solutions to a licensed disposal company. Contact a licensed professional waste disposal service to dispose of this material.

**Contaminated packaging**

Dispose of as unused product.

---

**SECTION 14: Transport information**

**14.1 UN number**

ADR/RID: 1105                                      IMDG: 1105                                      IATA: 1105

**14.2 UN proper shipping name**

ADR/RID: PENTANOLS  
IMDG: PENTANOLS  
IATA: Pentanols

**14.3 Transport hazard class(es)**

ADR/RID: 3    IMDG: 3    IATA: 3

**14.4 Packaging group**

ADR/RID: III    IMDG: III    IATA: III

**14.5 Environmental hazards**

ADR/RID: no    IMDG Marine pollutant: no    IATA: no

**14.6 Special precautions for user**

no data available

---

**SECTION 15: Regulatory information**

This safety datasheet complies with the requirements of Regulation (EC) No. 1907/2006.

**15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture**

no data available

**15.2 Chemical Safety Assessment**

For this product a chemical safety assessment was not carried out

---

**SECTION 16: Other information**

**Full text of H-Statements referred to under sections 2 and 3.**

Acute Tox.                      Acute toxicity

EUH066	Repeated exposure may cause skin dryness or cracking.
Flam. Liq.	Flammable liquids
H226	Flammable liquid and vapour.
H332	Harmful if inhaled.
H335	May cause respiratory irritation.
STOT SE	Specific target organ toxicity - single exposure

**Full text of R-phrases referred to under sections 2 and 3**

Xn	Harmful
R10	Flammable.
R20	Harmful by inhalation.
R37	Irritating to respiratory system.
R66	Repeated exposure may cause skin dryness or cracking.

**Further information**

The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. The information in this document is based on the present state of our knowledge and is applicable to the product with regard to appropriate safety precautions. It does not represent any guarantee of the properties of the product.

---