

## SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006 Version 5.0 Revision Date 12.12.2012

### 1. IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

#### 1.1 Product identifiers

Product name : Sebacoyl chloride 5% in cyclohexane

Product Number : 52-7537

Brand : Rapid

#### 1.2 Relevant identified uses of the substance or mixture and uses advised against

Identified uses : Laboratory chemicals, Manufacture of substances

#### 1.3 Details of the supplier of the safety data sheet

Company : Rapid Electronics,  
Severalls Lane,  
Colchester,  
Essex,  
CO4 5JS, United Kingdom

Telephone : +44 (0) 1206 751166

Fax : +44 (0) 1206 751188

E-mail address : sales@rapidelec.co.uk

#### 1.4 Emergency telephone number

Emergency Phone # : +44 (0) 1206 751166

### 2. HAZARDS IDENTIFICATION

#### 2.1 Classification of the substance or mixture

##### Classification according to Regulation (EC) No 1272/2008 [EU-GHS/CLP]

Flammable liquids (Category 2)

Aspiration hazard (Category 1)

Skin irritation (Category 2)

Specific target organ toxicity - single exposure (Category 3)

Acute aquatic toxicity (Category 1)

Chronic aquatic toxicity (Category 1)

##### Classification according to EU Directives 67/548/EEC or 1999/45/EC

Highly flammable. Harmful: may cause lung damage if swallowed. Irritating to skin. Vapours may cause drowsiness and dizziness. Very toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

#### 2.2 Label elements

##### Labelling according Regulation (EC) No 1272/2008 [CLP]



Pictogram

Signal word

Danger

Hazard statement(s)

H225

Highly flammable liquid and vapour.

H304




May be fatal if swallowed and enters airways.

H315

Causes skin irritation.

H336	May cause drowsiness or dizziness.
H410	Very toxic to aquatic life with long lasting effects.
Precautionary statement(s)	
P210	Keep away from heat/sparks/open flames/hot surfaces. - No smoking.
P261	Avoid breathing dust/ fume/ gas/ mist/ vapours/ spray.
P273	Avoid release to the environment.
P301 + P310	IF SWALLOWED: Immediately call a POISON CENTER or doctor/ physician.
P331	Do NOT induce vomiting.
P501	Dispose of contents/ container to an approved waste disposal plant.
Supplemental Hazard Statements	none

**According to European Directive 67/548/EEC as amended.**

Hazard symbol(s)	  
R-phrases(s)	
R11	Highly flammable.
R38	Irritating to skin.
R65	Harmful: may cause lung damage if swallowed.
R67	Vapours may cause drowsiness and dizziness.
R50/53	Very toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.
S-phrases(s)	
S 9	Keep container in a well-ventilated place.
S16	Keep away from sources of ignition - No smoking.
S25	Avoid contact with eyes.
S33	Take precautionary measures against static discharges.
S60	This material and its container must be disposed of as hazardous waste.
S61	Avoid release to the environment. Refer to special instructions/ Safety data sheets.
S62	If swallowed, do not induce vomiting: seek medical advice immediately and show this container or label.

**2.3 Other hazards - none**

**3. COMPOSITION/INFORMATION ON INGREDIENTS**

**3.1 Substances**

Formula	:	C <sub>6</sub> H <sub>12</sub>
Molecular Weight	:	84.16 g/mol

Component		Concentration
<b>Cyclohexane</b>		
CAS-No.	110-82-7	95%
EC-No.	203-806-2	
Index-No.	601-017-00-1	
<b>Sebacoyl chloride</b>		
CAS-No.	111-19-3	5%
EC-No.	203-843-4	

**4. FIRST AID MEASURES**

**4.1 Description of first aid measures**

**General advice**

Consult a physician. Show this safety data sheet to the doctor in attendance.

**If inhaled**

If breathed in, move person into fresh air. If not breathing, give artificial respiration. Consult a physician.

**In case of skin contact**

Wash off with soap and plenty of water. Consult a physician.

**In case of eye contact**

Rinse thoroughly with plenty of water for at least 15 minutes and consult a physician.

**If swallowed**

Do NOT induce vomiting. Never give anything by mouth to an unconscious person. Rinse mouth with water. Consult a physician.

**4.2 Most important symptoms and effects, both acute and delayed**

Central nervous system depression, Drowsiness, Irritability, Dizziness, Gastrointestinal disturbance, Lung irritation, chest pain, pulmonary edema

**4.3 Indication of any immediate medical attention and special treatment needed**

no data available

---

**5. FIREFIGHTING MEASURES****5.1 Extinguishing media****Suitable extinguishing media**

Use water spray, alcohol-resistant foam, dry chemical or carbon dioxide.

**5.2 Special hazards arising from the substance or mixture**

Carbon oxides

**5.3 Advice for firefighters**

Wear self contained breathing apparatus for fire fighting if necessary.

**5.4 Further information**

Use water spray to cool unopened containers.

---

**6. ACCIDENTAL RELEASE MEASURES****6.1 Personal precautions, protective equipment and emergency procedures**

Use personal protective equipment. Avoid breathing vapors, mist or gas. Ensure adequate ventilation. Remove all sources of ignition. Evacuate personnel to safe areas. Beware of vapours accumulating to form explosive concentrations. Vapours can accumulate in low areas.

**6.2 Environmental precautions**

Prevent further leakage or spillage if safe to do so. Do not let product enter drains. Discharge into the environment must be avoided.

**6.3 Methods and materials for containment and cleaning up**

Contain spillage, and then collect with an electrically protected vacuum cleaner or by wet-brushing and place in container for disposal according to local regulations (see section 13).

**6.4 Reference to other sections**

For disposal see section 13.

---

**7. HANDLING AND STORAGE****7.1 Precautions for safe handling**

Avoid contact with skin and eyes. Avoid inhalation of vapour or mist. Keep away from sources of ignition - No smoking. Take measures to prevent the build up of electrostatic charge.

**7.2 Conditions for safe storage, including any incompatibilities**

Store in cool place. Keep container tightly closed in a dry and well-ventilated place. Containers which are opened must be carefully resealed and kept upright to prevent leakage.

Store under inert gas.

**7.3 Specific end use(s)**

no data available

---

**8. EXPOSURE CONTROLS/PERSONAL PROTECTION****8.1 Control parameters**

**Components with workplace control parameters**

Component	CAS-No.	Value	Control parameters	Basis
Cyclohexane	110-82-7	STEL	300 ppm 1,050 mg/m <sup>3</sup>	UK. EH40 WEL - Workplace Exposure Limits
		TWA	100 ppm 350 mg/m <sup>3</sup>	UK. EH40 WEL - Workplace Exposure Limits
		TWA	200 ppm 700 mg/m <sup>3</sup>	Europe. Indicative occupational exposure limit values
	Remarks	Indicative		

## 8.2 Exposure controls

### Appropriate engineering controls

Handle in accordance with good industrial hygiene and safety practice. Wash hands before breaks and at the end of workday.

### Personal protective equipment

#### Eye/face protection

Face shield and safety glasses Use equipment for eye protection tested and approved under appropriate government standards such as NIOSH (US) or EN 166(EU).

#### Skin protection

Handle with gloves. Gloves must be inspected prior to use. Use proper glove removal technique (without touching glove's outer surface) to avoid skin contact with this product. Dispose of contaminated gloves after use in accordance with applicable laws and good laboratory practices. Wash and dry hands.

The selected protective gloves have to satisfy the specifications of EU Directive 89/686/EEC and the standard EN 374 derived from it.

Full contact

Material: Nitrile rubber

Minimum layer thickness: 0.4 mm

Break through time: 480 min

Material tested: Camatril® (KCL 730 / Aldrich Z677442, Size M)

Splash protection

Material: Nitrile rubber

Minimum layer thickness: 0.11 mm

Break through time: 35 min

Material tested: Dermatril® (KCL 740 / Aldrich Z677272, Size M)

data source: KCL GmbH, D-36124 Eichenzell, phone +49 (0)6659 87300, e-mail sales@kcl.de, test method: EN374

If used in solution, or mixed with other substances, and under conditions which differ from EN 374, contact the supplier of the CE approved gloves. This recommendation is advisory only and must be evaluated by an Industrial Hygienist familiar with the specific situation of anticipated use by our customers. It should not be construed as offering an approval for any specific use scenario.

#### Body Protection

Complete suit protecting against chemicals, Flame retardant antistatic protective clothing, The type of protective equipment must be selected according to the concentration and amount of the dangerous substance at the specific workplace.

#### Respiratory protection

Where risk assessment shows air-purifying respirators are appropriate use a full-face respirator with multi-purpose combination (US) or type ABEK (EN 14387) respirator cartridges as a backup to engineering controls. If the respirator is the sole means of protection, use a full-face supplied air respirator. Use respirators and components tested and approved under appropriate government standards such as NIOSH (US) or CEN (EU).

## 9. PHYSICAL AND CHEMICAL PROPERTIES

### 9.1 Information on basic physical and chemical properties

- a) Appearance                      Form: liquid

	Colour: colourless
b) Odour	no data available
c) Odour Threshold	no data available
d) pH	no data available
e) Melting point/freezing point	Melting point/range: 4 - 7 °C - lit.
f) Initial boiling point and boiling range	80.7 °C - lit.
g) Flash point	-18.0 °C - closed cup
h) Evaporation rate	no data available
i) Flammability (solid, gas)	no data available
j) Upper/lower flammability or explosive limits	Upper explosion limit: 9 %(V) Lower explosion limit: 1 %(V)
k) Vapour pressure	225.0 hPa at 37.7 °C 102.7 hPa at 20.0 °C
l) Vapour density	no data available
m) Relative density	0.779 g/cm <sup>3</sup> at 25 °C
n) Water solubility	no data available
o) Partition coefficient: n-octanol/water	log Pow: 3.44
p) Auto-ignition temperature	260.0 °C
q) Decomposition temperature	no data available
r) Viscosity	no data available
s) Explosive properties	no data available
t) Oxidizing properties	no data available

## 9.2 Other safety information

no data available

---

## 10. STABILITY AND REACTIVITY

### 10.1 Reactivity

no data available

### 10.2 Chemical stability

no data available

### 10.3 Possibility of hazardous reactions

no data available

### 10.4 Conditions to avoid

Heat, flames and sparks. Extremes of temperature and direct sunlight.

### 10.5 Incompatible materials

Strong oxidizing agents

### 10.6 Hazardous decomposition products

Other decomposition products - no data available

---

## 11. TOXICOLOGICAL INFORMATION

### 11.1 Information on toxicological effects

#### Acute toxicity

LD50 Oral - rat - 12,705 mg/kg

LC50 Inhalation - rat - 4 h - 13,900 mg/m<sup>3</sup>

LD50 Dermal - rabbit - > 2,000 mg/kg

#### Skin corrosion/irritation

Skin - rabbit - No skin irritation

#### Serious eye damage/eye irritation

Eyes - rabbit - Mild eye irritation

#### Respiratory or skin sensitization

no data available

#### Germ cell mutagenicity

no data available

#### Carcinogenicity

IARC: No component of this product present at levels greater than or equal to 0.1% is identified as probable, possible or confirmed human carcinogen by IARC.

#### Reproductive toxicity

no data available

#### Specific target organ toxicity - single exposure

May cause drowsiness or dizziness.

#### Specific target organ toxicity - repeated exposure

no data available

#### Aspiration hazard

May be fatal if swallowed and enters airways.

#### Potential health effects

<b>Inhalation</b>	Harmful if inhaled. Causes respiratory tract irritation. Vapours may cause drowsiness and dizziness.
<b>Ingestion</b>	May be harmful if swallowed. Aspiration hazard if swallowed - can enter lungs and cause damage.
<b>Skin</b>	May be harmful if absorbed through skin. Causes skin irritation.
<b>Eyes</b>	Causes eye irritation.

#### Signs and Symptoms of Exposure

Central nervous system depression, Drowsiness, Irritability, Dizziness, Gastrointestinal disturbance, Lung irritation, chest pain, pulmonary edema

#### Additional Information

RTECS: GU6300000

---

## 12. ECOLOGICAL INFORMATION

### 12.1 Toxicity

Toxicity to fish	LC50 - Lepomis macrochirus (Bluegill) - 34.7 mg/l - 96.0 h
	LC50 - Pimephales promelas (fathead minnow) - 32 - 93 mg/l - 96.0 h
Toxicity to daphnia and other aquatic invertebrates	EC50 - Daphnia magna (Water flea) - 3.78 mg/l - 48 h

### 12.2 Persistence and degradability

Biodegradability Result: - Not readily biodegradable.

---

**12.3 Bioaccumulative potential**

no data available

**12.4 Mobility in soil**

no data available

**12.5 Results of PBT and vPvB assessment**

no data available

**12.6 Other adverse effects**

Very toxic to aquatic life with long lasting effects.

---

**13. DISPOSAL CONSIDERATIONS****13.1 Waste treatment methods****Product**

Burn in a chemical incinerator equipped with an afterburner and scrubber but exert extra care in igniting as this material is highly flammable. Offer surplus and non-recyclable solutions to a licensed disposal company.

**Contaminated packaging**

Dispose of as unused product.

---

**14. TRANSPORT INFORMATION****14.1 UN number**

ADR/RID: 2924

IMDG: 2924

IATA: 2924

**14.2 UN proper shipping name**

ADR/RID: Flammable liquid, corrosive, n.o.s.

IMDG: Flammable liquid, corrosive, n.o.s.

IATA: Flammable liquid, corrosive, n.o.s.

**14.3 Transport hazard class(es)**

ADR/RID: 3(8)

IMDG: 3(8)

IATA: 3(8)

**14.4 Packaging group**

ADR/RID: II

IMDG: II

IATA: II

**14.5 Environmental hazards**

ADR/RID: yes

IMDG Marine Pollutant: yes

IATA: no

**14.6 Special precautions for user**

no data available

---

**15. REGULATORY INFORMATION**

This safety datasheet complies with the requirements of Regulation (EC) No. 1907/2006.

**15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture**

no data available

**15.2 Chemical Safety Assessment**

no data available

---

**16. OTHER INFORMATION****Further information**

The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. The information in this document is based on the present state of our knowledge and is applicable to the product with regard to appropriate safety precautions. It does not represent any guarantee of the properties of the product.