

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006 Version 5.3 Revision Date 16.12.2011

1. IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

1.1 Product identifiers

Product name : Silver nitrate

Product Number : 52-7539
Brand : Rapid
Index-No. : 047-001-00-2
CAS-No. : 7761-88-8

1.2 Relevant identified uses of the substance or mixture and uses advised against

Identified uses : Laboratory chemicals, Manufacture of substances

1.3 Details of the supplier of the safety data sheet

Company : Rapid Electronics,
Severalls Lane,
Colchester,
Essex,
CO4 5JS, United Kingdom

Telephone : +44 (0) 1206 751166
Fax : +44 (0) 1206 751188
E-mail address : sales@rapidelec.co.uk

1.4 Emergency telephone number

Emergency Phone # : +44 (0) 1206 751166

2. HAZARDS IDENTIFICATION

2.1 Classification of the substance or mixture

Classification according to Regulation (EC) No 1272/2008 [EU-GHS/CLP]

Skin corrosion (Category 1B)
Acute aquatic toxicity (Category 1)
Chronic aquatic toxicity (Category 1)
Oxidizing solids (Category 2)

Classification according to EU Directives 67/548/EEC or 1999/45/EC

Causes burns. Very toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment. Contact with combustible material may cause fire.

2.2 Label elements

Labelling according Regulation (EC) No 1272/2008 [CLP]

Pictogram



Signal word : Danger

Hazard statement(s)

H272 : May intensify fire; oxidiser.
H314 : Causes severe skin burns and eye damage.
H410 : Very toxic to aquatic life with long lasting effects.

Precautionary statement(s)

P220 : Keep/Store away from clothing/ combustible materials.

P273 Avoid release to the environment.
P280 Wear protective gloves/ protective clothing/ eye protection/ face protection.
P305 + P351 + P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P310 Immediately call a POISON CENTER or doctor/ physician.
P501 Dispose of contents/ container to an approved waste disposal plant.

Supplemental Hazard Statements none

According to European Directive 67/548/EEC as amended.



Hazard symbol(s)
R-phrase(s)
R 8 Contact with combustible material may cause fire.
R34 Causes burns.
R50/53 Very toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

S-phrase(s)
S26 In case of contact with eyes, rinse immediately with plenty of water and seek medical advice.
S36/37/39 Wear suitable protective clothing, gloves and eye/face protection.
S45 In case of accident or if you feel unwell, seek medical advice immediately (show the label where possible).
S60 This material and its container must be disposed of as hazardous waste.
S61 Avoid release to the environment. Refer to special instructions/ Safety data sheets.

2.3 Other hazards - none

3. COMPOSITION/INFORMATION ON INGREDIENTS

3.1 Substances

Formula : AgNO₃
Molecular Weight : 169.87 g/mol

Component	Concentration
Silver nitrate	
CAS-No. 7761-88-8	-
EC-No. 231-853-9	
Index-No. 047-001-00-2	

4. FIRST AID MEASURES

4.1 Description of first aid measures

General advice

Consult a physician. Show this safety data sheet to the doctor in attendance.

If inhaled

If breathed in, move person into fresh air. If not breathing, give artificial respiration. Consult a physician.

In case of skin contact

Take off contaminated clothing and shoes immediately. Wash off with soap and plenty of water. Consult a physician.

In case of eye contact

Rinse thoroughly with plenty of water for at least 15 minutes and consult a physician.

If swallowed

Do NOT induce vomiting. Never give anything by mouth to an unconscious person. Rinse mouth with water. Consult a physician.

4.2 Most important symptoms and effects, both acute and delayed

May cause argyria (a slate-gray or bluish discoloration of the skin and deep tissues due to the deposit of insoluble albuminate of silver)., Absorption into the body leads to the formation of methemoglobin which in sufficient concentration causes cyanosis. Onset may be delayed 2 to 4 hours or longer.

4.3 Indication of any immediate medical attention and special treatment needed

no data available

5. FIREFIGHTING MEASURES

5.1 Extinguishing media

Suitable extinguishing media

Use water spray, alcohol-resistant foam, dry chemical or carbon dioxide.

5.2 Special hazards arising from the substance or mixture

nitrogen oxides (NOx), Silver/silver oxides

5.3 Advice for firefighters

Wear self contained breathing apparatus for fire fighting if necessary.

5.4 Further information

Use water spray to cool unopened containers.

6. ACCIDENTAL RELEASE MEASURES

6.1 Personal precautions, protective equipment and emergency procedures

Use personal protective equipment. Avoid dust formation. Avoid breathing vapors, mist or gas. Ensure adequate ventilation. Evacuate personnel to safe areas. Avoid breathing dust.

6.2 Environmental precautions

Prevent further leakage or spillage if safe to do so. Do not let product enter drains. Discharge into the environment must be avoided.

6.3 Methods and materials for containment and cleaning up

Sweep up and shovel. Contain spillage, and then collect with an electrically protected vacuum cleaner or by wet-brushing and place in container for disposal according to local regulations (see section 13). Keep in suitable, closed containers for disposal.

6.4 Reference to other sections

For disposal see section 13.

7. HANDLING AND STORAGE

7.1 Precautions for safe handling

Avoid contact with skin and eyes. Avoid formation of dust and aerosols.

Provide appropriate exhaust ventilation at places where dust is formed.Keep away from sources of ignition

- No smoking.Keep away from heat and sources of ignition.

7.2 Conditions for safe storage, including any incompatibilities

Store in cool place. Keep container tightly closed in a dry and well-ventilated place.

Light sensitive.

7.3 Specific end uses

no data available

8. EXPOSURE CONTROLS/PERSONAL PROTECTION

8.1 Control parameters

Components with workplace control parameters

Component	CAS-No.	Value	Control parameters	Basis
Silver nitrate	7761-88-8	TWA	0.01 mg/m ³	UK. EH40 WEL - Workplace Exposure Limits

		TWA	0.01 mg/m ³	Europe. Indicative occupational exposure limit values
	Remarks	Indicative		

8.2 Exposure controls

Appropriate engineering controls

Handle in accordance with good industrial hygiene and safety practice. Wash hands before breaks and at the end of workday.

Personal protective equipment

Eye/face protection

Face shield and safety glasses Use equipment for eye protection tested and approved under appropriate government standards such as NIOSH (US) or EN 166(EU).

Skin protection

Handle with gloves. Gloves must be inspected prior to use. Use proper glove removal technique (without touching glove's outer surface) to avoid skin contact with this product. Dispose of contaminated gloves after use in accordance with applicable laws and good laboratory practices. Wash and dry hands.

The selected protective gloves have to satisfy the specifications of EU Directive 89/686/EEC and the standard EN 374 derived from it.

Body Protection

Complete suit protecting against chemicals, The type of protective equipment must be selected according to the concentration and amount of the dangerous substance at the specific workplace.

Respiratory protection

Where risk assessment shows air-purifying respirators are appropriate use a full-face particle respirator type N100 (US) or type P3 (EN 143) respirator cartridges as a backup to engineering controls. If the respirator is the sole means of protection, use a full-face supplied air respirator. Use respirators and components tested and approved under appropriate government standards such as NIOSH (US) or CEN (EU).

9. PHYSICAL AND CHEMICAL PROPERTIES

9.1 Information on basic physical and chemical properties

- | | |
|---|------------------------------------|
| a) Appearance | Form: solid
Colour: white |
| b) Odour | no data available |
| c) Odour Threshold | no data available |
| d) pH | no data available |
| e) Melting point/freezing point | Melting point/range: 212 °C - dec. |
| f) Initial boiling point and boiling range | 440 °C - Decomposes on heating. |
| g) Flash point | no data available |
| h) Evaporation rate | no data available |
| i) Flammability (solid, gas) | no data available |
| j) Upper/lower flammability or explosive limits | no data available |
| k) Vapour pressure | no data available |
| l) Vapour density | no data available |
| m) Relative density | 4.350 g/cm ³ |
| n) Water solubility | no data available |

- | | |
|---|---|
| o) Partition coefficient: n-octanol/water | log Pow: 5 |
| p) Autoignition temperature | no data available |
| q) Decomposition temperature | no data available |
| r) Viscosity | no data available |
| s) Explosive properties | no data available |
| t) Oxidizing properties | The substance or mixture is classified as oxidizing with the subcategory 2. |

9.2 Other safety information

no data available

10. STABILITY AND REACTIVITY

10.1 Reactivity

no data available

10.2 Chemical stability

no data available

10.3 Possibility of hazardous reactions

no data available

10.4 Conditions to avoid

Light.

10.5 Incompatible materials

Strong reducing agents, Alcohols, Ammonia, Magnesium, Strong bases

10.6 Hazardous decomposition products

Other decomposition products - no data available

11. TOXICOLOGICAL INFORMATION

11.1 Information on toxicological effects

Acute toxicity

LD50 Oral - rat - 1,173 mg/kg

Remarks: Behavioral:Tetany. Cyanosis Diarrhoea

Skin corrosion/irritation

no data available

Serious eye damage/eye irritation

Eyes - rabbit - Severe eye irritation

Respiratory or skin sensitization

no data available

Germ cell mutagenicity

Laboratory experiments have shown mutagenic effects.

Carcinogenicity

IARC: No component of this product present at levels greater than or equal to 0.1% is identified as probable, possible or confirmed human carcinogen by IARC.

Reproductive toxicity

no data available

Specific target organ toxicity - single exposure

no data available

Specific target organ toxicity - repeated exposure

no data available

Aspiration hazard

no data available

Potential health effects**Inhalation**

May be harmful if inhaled. Material is extremely destructive to the tissue of the mucous membranes and upper respiratory tract.

Ingestion

Harmful if swallowed. Causes burns.

Skin

May be harmful if absorbed through skin. Causes skin burns.

Eyes

Causes eye burns.

Signs and Symptoms of Exposure

May cause argyria (a slate-gray or bluish discoloration of the skin and deep tissues due to the deposit of insoluble albuminate of silver)., Absorption into the body leads to the formation of methemoglobin which in sufficient concentration causes cyanosis. Onset may be delayed 2 to 4 hours or longer.

Additional Information

RTECS: VW4725000

12. ECOLOGICAL INFORMATION**12.1 Toxicity**

Toxicity to fish mortality NOEC - Oncorhynchus mykiss (rainbow trout) - 0.108 mg/l - 96.0 h
 mortality LOEC - Oncorhynchus mykiss (rainbow trout) - > 0.007 mg/l - 7.0 d
 LC50 - Leuciscus idus (Golden orfe) - 0.029 mg/l - 96.0 h
 LC50 - Oncorhynchus mykiss (rainbow trout) - 0.006 mg/l - 96.0 h

Toxicity to daphnia and other aquatic invertebrates. EC50 - Daphnia magna (Water flea) - 0.0006 mg/l - 48 h

12.2 Persistence and degradability**12.3 Bioaccumulative potential**

Bioaccumulation Lepomis macrochirus - 60 d -70 µg/l
 Bioconcentration factor (BCF): 120

12.4 Mobility in soil

no data available

12.5 Results of PBT and vPvB assessment

no data available

12.6 Other adverse effects

Very toxic to aquatic life.

13. DISPOSAL CONSIDERATIONS**13.1 Waste treatment methods****Product**

Burn in a chemical incinerator equipped with an afterburner and scrubber but exert extra care in igniting as this material is highly flammable. Offer surplus and non-recyclable solutions to a licensed disposal company.

Contaminated packaging

Dispose of as unused product.

14. TRANSPORT INFORMATION**14.1 UN number**

ADR/RID: 1493

IMDG: 1493

IATA: 1493

14.2 UN proper shipping name

ADR/RID: SILVER NITRATE

IMDG: SILVER NITRATE
IATA: Silver nitrate

14.3 Transport hazard class(es)		
ADR/RID: 5.1	IMDG: 5.1	IATA: 5.1
14.4 Packaging group		
ADR/RID: II	IMDG: II	IATA: II
14.5 Environmental hazards		
ADR/RID: yes	IMDG Marine pollutant: yes	IATA: no
14.6 Special precautions for user		
no data available		

15. REGULATORY INFORMATION

This safety datasheet complies with the requirements of Regulation (EC) No. 1907/2006.

- 15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture**
no data available
- 15.2 Chemical Safety Assessment**
no data available

16. OTHER INFORMATION

Further information

The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. The information in this document is based on the present state of our knowledge and is applicable to the product with regard to appropriate safety precautions. It does not represent any guarantee of the properties of the product.
