

162 i PH/S VDE Insulated screwdriver for PlusMinus screws (Phillips/slotted), PH/S

1 x 80 mm

Kraftform Plus – Series 100 VDE



EAN/GTIN: 4013288102614
Part no.: 05006380001
Article no.: 162 i PH/S VDE

Dimension: 178x33x33 mm
Weight: 56 g
Country of origin: CZ
Customs tariff number: 82054000

- Insulated VDE blades for secure work at 1,000 volts
- Smooth hard zones for high speed turning, soft grip zones for high torque transfer
- Handle markings simplify finding and sorting of tools
- Hexagonal anti-roll feature against rolling away
- Combination profile - Phillips / slotted

Wera VDE screwdrivers with multi-component Kraftform Plus handle for fast and low-fatigue working: hard gripping zones for high working speeds whereas soft zones ensure high torque transfer. Combination profile - slotted and Phillips particularly for jobs on terminal blocks, fuse boxes, switches and relays. Individually tested in water bath at 10,000 volts for secure work at the permissible voltage of 1,000 volts. The hexagonal anti-roll feature prevents any bothersome rolling away at the workplace.

Weblink

http://products.wera.de/en/vde_tools_kraftform_plus_series_100_vde_162_i_ph_s_vde.html

Wera - 162 i PH/S VDE
05006380001 - 4013288102614

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

162 i PH/S VDE Insulated screwdriver for PlusMinus screws (Phillips/slotted), PH/S

1 x 80 mm

Kraftform Plus – Series 100 VDE



PlusMinus screwdrivers



Our screwdrivers are tested for dielectric strength under a 10,000 volt load to make sure that their most important property, their insulation, has been exhaustively tested. Each individual Wera VDE screwdriver is subjected to this test to guarantee safe working up to 1,000 volts.




For the use in terminal blocks, control cabinets, switches, relays, sockets etc.

Individually tested



The individual testing at 10,000 volts, in accordance with IEC 60900, ensures safe working with loads up to 1,000 volts.

Impact strength test



Impact strength tested at -40°C , guaranteeing safety even under extreme conditions.

Multicomponent Kraftform handle




Wera produces the Kraftform handle out of several materials with different properties. A resistant plastic is used for the core which ensures that the blade is held securely even under high strain. A softer material is used for the coloured soft zones, which provides high frictional resistance and allows the transfer of high forces – resulting in less required screwdriving effort. The red sections with their hard surfaces prevent any “sticking” of the hand to the handle, making rapid repositioning of the hand possible.

Prevents hand injuries



The outstanding design of the Kraftform handle that fits perfectly into the hand prevents hand injuries such as blisters and calluses.

Rapid hand repositioning



The hard materials used for the handle ensure rapid hand repositioning without any danger of the skin “sticking” to the handle. The surrounding hard zones with large diameters glide like wheels across the hand.

Identification marking



All Kraftform Plus screwdrivers are marked with their drive profile and size. This enables faster and more reliable selection of the correct tool from the tool case.

Weblink

http://products.wera.de/en/vde_tools_kraftform_plus_series_100_vde_162_i_ph_s_vde.html

Wera - 162 i PH/S VDE

05006380001 - 4013288102614

Wera Werkzeuge GmbH

Korzter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: info@wera.de

162 i PH/S VDE Insulated screwdriver for PlusMinus screws (Phillips/slotted), PH/S

1 x 80 mm

Kraftform Plus – Series 100 VDE



More variants of this product family:



mm



mm



inch

	mm	mm	inch
05006380001	1	80	98
05006381001	2	100	105

Weblink

http://products.wera.de/en/vde_tools_kraftform_plus_series_100_vde_162_i_ph_s_vde.html

Wera - 162 i PH/S VDE

05006380001 - 4013288102614

Wera Werkzeuge GmbH

Korzter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: info@wera.de