

2067 TORX® HF screwdriver with holding function for electronic applications, TX 6
x 40 mm
Series Kraftform Micro



EAN/GTIN: 4013288108647
Part no.: 05118182001
Article no.: 2067 TORX® HF

Dimension: 137x13x13 mm
Weight: 12 g
Country of origin: CZ
Customs tariff number: 82054000



- Kraftform Micro TORX® HF screwdriver with holding function for recessed TORX® screws
- Multi-component Kraftform Micro handle with anti-roll feature and swivel cap
- The Wera Black Point tip offers an exact fit and optimum corrosion protection
- Holding function for TORX® screws, chrome-plated
- E.g. for electricians, opticians, precision mechanics, jewellers or IT hardware fitters

High quality Wera Micro nutsetter set for precision mechanical work. Comes with practical holding function: the wedging forces resulting from the contact pressure between the drive tip and the screw profile securely hold the screw on the tool. Rapid twisting is possible by fixing the hand on the twist cap and using the fast-turning zone just below it. This makes time-consuming grip adjustments unnecessary. Power zone with integrated soft zones ensure the transfer of higher tightening and loosening torque. Precision zone for the right angle for adjustment work. The Wera Black Point tip offers high corrosion protection and an exact fit.

Weblink
http://products.wera.de/en/screwdrivers_series_kraftform_micro_2067_torx_hf.html

Wera - 2067 TORX® HF
05118182001 - 4013288108647

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

TORX® HF profile



Screwdriving jobs in electrical and precision engineering applications are often tedious and time-consuming. We learned from users what is important for them: working speeds, torque, precision – and we then focused particularly on these issues.




In tight assembly or disassembly situations, for example in engine compartments, it is not possible to securely hold the screw with the hand on the screwdriver, and the screw subsequently often gets lost. Lengthy searches or the loss of the screw (with the associated danger that could bring about) are the consequence. The HF tools developed by Wera are ideal because they feature an optimised geometry of the original TORX® profile. The wedging forces resulting from the surface pressure between the drive tip and the screw profile mean that the screw is securely held on the tool!

Kraftform Micro Handle



Multi-component screwdriver handle for ergonomic working.

The refined screwdriver for electronics technicians



The Kraftform Micro, with its three zones and their specific arrangement, satisfies these requirements perfectly. The free-turning cap that provides support for the hand works with these advantages, enabling quick and easy precision work.

The precision zone



The precision zone directly above the blade gives the user a better feel for the right rotation angle during fine adjustment work.

The power zone



The power zone has integrated soft zones near the blade tip to ensure high torque transfer for loosening or tightening screws without losing contact with the screw.

The fast-turning zone



The fast-turning zone just below the rotating cap allows rapid twisting.

Wera Black Point tip



The Wera Black Point tip and a refined hardening process ensure long service life of the tip, improved corrosion protection and an exact fit.

Weblink

http://products.wera.de/en/screwdrivers_series_kraftform_micro_2067_torx_hf.html

Wera - 2067 TORX® HF
05118182001 - 4013288108647

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de






2067 TORX® HF screwdriver with holding function for electronic applications, TX 6

x 40 mm

Series Kraftform Micro



More variants of this product family:

| |  |  |  |  |  |
|--------------------|---|---|---|---|---|
| | | mm | mm | mm | inch |
| 05118180001 | TX 4 | 40 | 97 | 2.5 | 1 9/16 |
| 05118181001 | TX 5 | 40 | 97 | 3.0 | 1 9/16 |
| 05118182001 | TX 6 | 40 | 97 | 3.0 | 1 9/16 |
| 05118183001 | TX 7 | 60 | 97 | 3.0 | 2 3/8 |
| 05118184001 | TX 8 | 60 | 97 | 3.0 | 2 3/8 |
| 05118185001 | TX 9 | 60 | 97 | 4.0 | 2 3/8 |
| 05118186001 | TX 10 | 60 | 97 | 4.0 | 2 3/8 |

Weblink

http://products.wera.de/en/screwdrivers_series_kraftform_micro_2067_torx_hf.html

Wera - 2067 TORX® HF
05118182001 - 4013288108647

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de