

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006 Version 5.2 Revision Date 28.11.2012

1. IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

1.1 Product identifiers

Product name : Sulphuric acid 2M solution

Product Number : 52-7570
Brand : Rapid
REACH No. : 01-2119458838-20-XXXX
CAS-No. : 7664-93-9

1.2 Relevant identified uses of the substance or mixture and uses advised against

Identified uses : Laboratory chemicals, Manufacture of substances

1.3 Details of the supplier of the safety data sheet

Company : Rapid Electronics,
Severalls Lane,
Colchester,
Essex,
CO4 5JS, United Kingdom

Telephone : +44 (0) 1206 751166
Fax : +44 (0) 1206 751188
E-mail address : sales@rapidelec.co.uk

1.4 Emergency telephone number

Emergency Phone # : +44 (0) 1206 751166

2. HAZARDS IDENTIFICATION

2.1 Classification of the substance or mixture

Classification according to Regulation (EC) No 1272/2008 [EU-GHS/CLP]

Skin corrosion (Category 1A)

Classification according to EU Directives 67/548/EEC or 1999/45/EC

Causes severe burns.

2.2 Label elements

Labelling according Regulation (EC) No 1272/2008 [CLP]



Pictogram

Signal word

Danger

Hazard statement(s)

H314

Causes severe skin burns and eye damage.

Precautionary statement(s)

P280

Wear protective gloves/ protective clothing/ eye protection/ face protection.

P305 + P351 + P338

IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

P310

Immediately call a POISON CENTER or doctor/ physician.

Supplemental Hazard

none

Statements

According to European Directive 67/548/EEC as amended.

Hazard symbol(s)



R-phrases)

R35 Causes severe burns.

S-phrases)

S26 In case of contact with eyes, rinse immediately with plenty of water and seek medical advice.

S30 Never add water to this product.

S45 In case of accident or if you feel unwell, seek medical advice immediately (show the label where possible).

2.3 Other hazards - none

3. COMPOSITION/INFORMATION ON INGREDIENTS

3.2 Mixtures

Formula : H₂O₄S

Molecular Weight : 98.08 g/mol

Component	Classification	Concentration
Sulfuric acid		
CAS-No.	7664-93-9	Skin Corr. 1A; H314 C, R35
EC-No.	231-639-5	
Index-No.	016-020-00-8	
Registration number	01-21 19458838-20-XXXX	

For the full text of the H-Statements and R-Phrases mentioned in this Section, see Section 16

4. FIRST AID MEASURES

4.1 Description of first aid measures

General advice

Consult a physician. Show this safety data sheet to the doctor in attendance.

If inhaled

If breathed in, move person into fresh air. If not breathing, give artificial respiration. Consult a physician.

In case of skin contact

Take off contaminated clothing and shoes immediately. Wash off with soap and plenty of water. Consult a physician.

In case of eye contact

Rinse thoroughly with plenty of water for at least 15 minutes and consult a physician.

If swallowed

Do NOT induce vomiting. Never give anything by mouth to an unconscious person. Rinse mouth with water. Consult a physician.

4.2 Most important symptoms and effects, both acute and delayed

burning sensation, Cough, wheezing, laryngitis, Shortness of breath, spasm, inflammation and edema of the larynx, spasm, inflammation and edema of the bronchi, pneumonitis, pulmonary edema, Material is extremely destructive to tissue of the mucous membranes and upper respiratory tract, eyes, and skin.

4.3 Indication of any immediate medical attention and special treatment needed

no data available

5. FIREFIGHTING MEASURES

5.1 Extinguishing media

Suitable extinguishing media

Use water spray, alcohol-resistant foam, dry chemical or carbon dioxide.

- 5.2 **Special hazards arising from the substance or mixture**
Sulphur oxides
- 5.3 **Advice for firefighters**
Wear self contained breathing apparatus for fire fighting if necessary.
- 5.4 **Further information**
no data available

6. ACCIDENTAL RELEASE MEASURES

- 6.1 **Personal precautions, protective equipment and emergency procedures**
Use personal protective equipment. Avoid breathing vapors, mist or gas. Ensure adequate ventilation. Evacuate personnel to safe areas.
- 6.2 **Environmental precautions**
Prevent further leakage or spillage if safe to do so. Do not let product enter drains. Discharge into the environment must be avoided.
- 6.3 **Methods and materials for containment and cleaning up**
Soak up with inert absorbent material and dispose of as hazardous waste. Keep in suitable, closed containers for disposal.
- 6.4 **Reference to other sections**
For disposal see section 13.

7. HANDLING AND STORAGE

- 7.1 **Precautions for safe handling**
Avoid inhalation of vapour or mist.
- 7.2 **Conditions for safe storage, including any incompatibilities**
Store in cool place. Keep container tightly closed in a dry and well-ventilated place. Containers which are opened must be carefully resealed and kept upright to prevent leakage.
- 7.3 **Specific end uses**
no data available

8. EXPOSURE CONTROLS/PERSONAL PROTECTION

8.1 Control parameters

Components with workplace control parameters

Component	CAS-No.	Value	Control parameters	Basis
Sulfuric acid	7664-93-9	TWA	0.05 mg/m3	Europe. COMMISSION DIRECTIVE 2009/161/EU establishing a third list of indicative occupational exposure limit values in implementation of Council Directive 98/24/EC and amending Commission Directive 2000/39/EC
	Remarks	When selecting an appropriate exposure monitoring method, account should be taken of potential limitations and interferences that may arise in the presence of other sulphur compounds. Indicative		

8.2 Exposure controls

Appropriate engineering controls

Handle in accordance with good industrial hygiene and safety practice. Wash hands before breaks and at the end of workday.

Personal protective equipment

Eye/face protection

Tightly fitting safety goggles. Faceshield (8-inch minimum). Use equipment for eye protection tested and approved under appropriate government standards such as NIOSH (US) or EN 166(EU).

Skin protection

Handle with gloves. Gloves must be inspected prior to use. Use proper glove removal technique (without touching glove's outer surface) to avoid skin contact with this product. Dispose of contaminated gloves after use in accordance with applicable laws and good laboratory practices. Wash and dry hands.

The selected protective gloves have to satisfy the specifications of EU Directive 89/686/EEC and the standard EN 374 derived from it.

Full contact

Material: Fluorinated rubber

Minimum layer thickness: 0.7 mm

Break through time: > 480 min

Material tested: Vitoject® (Aldrich Z677698, Size M)

Splash protection

Material: Nitrile rubber

Minimum layer thickness: 0.2 mm

Break through time: > 30 min

Material tested: Dermatril® P (Aldrich Z677388, Size M)

data source: KCL GmbH, D-36124 Eichenzell, phone +49 (0)6659 87300, e-mail sales@kcl.de, test method: EN374

If used in solution, or mixed with other substances, and under conditions which differ from EN 374, contact the supplier of the CE approved gloves. This recommendation is advisory only and must be evaluated by an Industrial Hygienist familiar with the specific situation of anticipated use by our customers. It should not be construed as offering an approval for any specific use scenario.

Body Protection

Complete suit protecting against chemicals, The type of protective equipment must be selected according to the concentration and amount of the dangerous substance at the specific workplace.

Respiratory protection

Where risk assessment shows air-purifying respirators are appropriate use a full-face respirator with multi-purpose combination (US) or type ABEK (EN 14387) respirator cartridges as a backup to engineering controls. If the respirator is the sole means of protection, use a full-face supplied air respirator. Use respirators and components tested and approved under appropriate government standards such as NIOSH (US) or CEN (EU).

9. PHYSICAL AND CHEMICAL PROPERTIES

9.1 Information on basic physical and chemical properties

- | | |
|--|-------------------|
| a) Appearance | Form: liquid |
| b) Odour | no data available |
| c) Odour Threshold | no data available |
| d) pH | no data available |
| e) Melting point/freezing point | 3 °C |
| f) Initial boiling point and boiling range | no data available |
| g) Flash point | not applicable |
| h) Evaporation rate | no data available |
| i) Flammability (solid, gas) | no data available |

j)	Upper/lower flammability or explosive limits	no data available
k)	Vapour pressure	1.33 hPa at 145.8 °C
l)	Vapour density	3.39 - (Air = 1.0)
m)	Relative density	1.80 - 1.84 g/cm ³
n)	Water solubility	soluble
o)	Partition coefficient: n-octanol/water	no data available
p)	Autoignition temperature	no data available
q)	Decomposition temperature	no data available
r)	Viscosity	no data available
s)	Explosive properties	no data available
t)	Oxidizing properties	no data available

9.2 Other safety information

Surface tension	55.1 mN/m at 20 °C
-----------------	--------------------

10. STABILITY AND REACTIVITY

10.1 Reactivity

no data available

10.2 Chemical stability

no data available

10.3 Possibility of hazardous reactions

no data available

10.4 Conditions to avoid

no data available

10.5 Incompatible materials

Bases, Halides, Organic materials, Carbides, fulminates, Nitrates, picrates, Cyanides, Chlorates, alkali halides, Zinc salts, permanganates, e.g. potassium permanganate, Hydrogen peroxide, Azides, Perchlorates., Nitromethane, phosphorous, Reacts violently with:, cyclopentadiene, cyclopentanone oxime, nitroaryl amines, hexalithium disilicide, phosphorous(III) oxide, Powdered metals

10.6 Hazardous decomposition products

Other decomposition products - no data available

11. TOXICOLOGICAL INFORMATION

11.1 Information on toxicological effects

Acute toxicity

no data available

Skin corrosion/irritation

no data available

Serious eye damage/eye irritation

no data available

Respiratory or skin sensitization

no data available

Germ cell mutagenicity

no data available

Carcinogenicity

IARC: 1 - Group 1: Carcinogenic to humans (Sulfuric acid)

Reproductive toxicity

no data available

Specific target organ toxicity - single exposure

no data available

Specific target organ toxicity - repeated exposure

no data available

Aspiration hazard

no data available

Potential health effects

Inhalation

May be harmful if inhaled. Material is extremely destructive to the tissue of the mucous membranes and upper respiratory tract.

Ingestion

May be harmful if swallowed. Causes burns.

Skin

May be harmful if absorbed through skin. Causes skin burns.

Eyes

Causes eye burns.

Signs and Symptoms of Exposure

burning sensation, Cough, wheezing, laryngitis, Shortness of breath, spasm, inflammation and edema of the larynx, spasm, inflammation and edema of the bronchi, pneumonitis, pulmonary edema, Material is extremely destructive to tissue of the mucous membranes and upper respiratory tract, eyes, and skin.

Additional Information

RTECS: WS5600000

12. ECOLOGICAL INFORMATION

12.1 Toxicity

no data available

12.2 Persistence and degradability

no data available

12.3 Bioaccumulative potential

no data available

12.4 Mobility in soil

no data available

12.5 Results of PBT and vPvB assessment

no data available

12.6 Other adverse effects

Harmful to aquatic life.

13. DISPOSAL CONSIDERATIONS

13.1 Waste treatment methods

Product

Offer surplus and non-recyclable solutions to a licensed disposal company.

Contaminated packaging

Dispose of as unused product.

14. TRANSPORT INFORMATION

14.1 UN number

ADR/RID: 2796

IMDG: 2796

IATA: 2796

14.2 UN proper shipping name

ADR/RID: SULPHURIC ACID

IMDG: SULPHURIC ACID

IATA: Sulphuric acid

14.3 Transport hazard class(es)

ADR/RID: 8

IMDG: 8

IATA: 8

14.4 Packaging group

ADR/RID: II

IMDG: II

IATA: II

14.5 Environmental hazards

ADR/RID: no

IMDG Marine pollutant: no

IATA: no

14.6 Special precautions for user

no data available

15. REGULATORY INFORMATION

This safety datasheet complies with the requirements of Regulation (EC) No. 1907/2006.

15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

no data available

15.2 Chemical Safety Assessment

no data available

16. OTHER INFORMATION

Text of H-code(s) and R-phrase(s) mentioned in Section 3

H314	Causes severe skin burns and eye damage.
Skin Corr.	Skin corrosion
C	Corrosive
R35	Causes severe burns.

Further information

The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. The information in this document is based on the present state of our knowledge and is applicable to the product with regard to appropriate safety precautions. It does not represent any guarantee of the properties of the product.