







DSA800 series pectrum Analyzer

- · All-Digital IF Technology
- 9 kHz 1.5 GHz Frequency Range
- Up to -135dBm Displayed Average Noise Level (DANL)
- -80dBc/Hz @ 10kHz Oset Phase Noise
- Total Amplitude Uncertainty < 1.5dB
- 100Hz Minimum Resolution Bandwidth (RBW)
- 1.5GHz Tracking Generator (DSA815-TG)
- · Advanced Measurement functions (Option)
- EMI Filter & Quasi-Peak Detector Kit(Option)
- VSWR Measurement Kit(Option)
- Complete Connectivity: LAN, USB host, USB device, GPIB (option)
- 8 Inch WVGA (800x480) Display
- · Compact Size,Light weight design

DSA800 series is one of RIGOL's compact size, light weighteconomic spectrum analyzers, the digital IF technology guarantees its reliability and performance to meet the most demanding RF applications.

Unique widescreen display, friendly interface and easy-to-use operations








Product Dimensions: Width X Height X Depth = 361.6 mm x 178.8 mm x 128 mm Weight: 4.25kg (9.4lbs)

Benefits of Rigol's all digital IF design


- 1. The ability to measure smaller signals: on the basis of this technology, the IF filter enables smaller bandwidth settings, which greatly reduce the displayed average noise level.
- 2. The ability to distinguish between small signals by frequency: using the IF filter with the smallest bandwidth setting it is possible to make out signals with a frequency difference of only 100 Hz.
- 3. High precision amplitude readings: this technology almost eliminates the errors generated by filter switching, reference level uncertainty, scale distortion, as well as errors produced in the process of switching between logarithmic and linear display of amplitude when using a traditional analog IF design.
- 4. Higher reliability: compared with traditional analog designs, the digital IF greatly reduces the complexity of the hardware, the system instability caused by channel aging, and the temperature sensitivity that can contribute to parts failure.
- 5. High measurement speed: the use of digital IF technology improves the bandwidth precision and selectivity of the filter, minimizing the scanning time and improving the speed of the measurement.

► Features and Benefits


Distinguish the two nearby signals clearly with the 100Hz RBW



Zero span to demodulate the AM signal




Measure lower than -130dBm signal with the standard Preamplifier



EMI Measurement (EMI Filter & Quasi-Peak & Pass_Fail)



Compare the spectrums when change the RBW settings with different color trace




Readout the Spectrum Peak values with the Peak table function



VSWR Measureasurement



The GUI to control the RF Demo Kit (Transmitter) directly



RF Demo Kit (TX1000)



DSA Accessories Package (DSA Utility Kit)



VSWR Bridge (VB1020/VB1030)




Tracking Generator (DSA815–TG)



Advanced Measurement Kit (DSA800-AMK)



DSA PC Software (Ultra Spectrum)



USB to GPIB Interface Converter for Instrument (USB-GPIB)



Rack Mount Kit (DSA800-RMSA)



Specifications

Specifications are valid after 30 minute warm up time with a valid calibration.

Typical value and nominal value are defined as follows.

- Typical value: defined as the specifications when the product is under specified conditions.
- Nominal value: defined as the approximate quantity in the application of the product.

Frequency

Frequency		
Frequency Range	DSA815	9 kHz to 1.5 GHz
Frequency Resolution		1Hz
Internal Frequency Reference		
Reference Frequency		10 MHz
Aging Rate		<2 ppm/year
Temperature Stability	20℃ to 30℃	<2 ppm
Frequency Readout Accuracy		
Marker Resolution		span / (sweep points-1)
Marker Uncertainty		±(frequency indication × frequency reference
		uncertainty + 1% × span + 10% × resolution
		bandwidth + marker resolution)
Marker Frequency Counter		
Resolution		1 Hz,10 Hz,100 Hz,1 KHz,10 KHz,100 KHz
Uncertainty		±(frequency indication × frequency reference
		uncertainty + counter resolution)
Note: Frequency Reference Uncertainty = (agin	g rate × period since adjustment + temperature drift).	
Frequency Span		
Range	DSA815	0 Hz 100 Hz to 1.5 GHz

Frequency Span										
Range	DSA815	0 Hz, 100 Hz to 1.5 GHz								
Uncertainty		±span / (sweep points-1)								
SSB Phase Noise										
Carrier Offset	10 kHz offset	<-80 dBc/Hz								
Bandwidths										
Resolution Bandwidth (-3dB)		100 Hz to 1 MHz, in 1-3-10 sequence								
Resolution Bandwidth (-6dB)	Opt	200 Hz, 9 kHz, 120 kHz								
RBW Uncertainty		<5%, nominal								
Resolution Filter Shape Factor		<5, nominal								
(60dB: 3dB)										
Video Bandwidth (-3dB)		1 Hz to 3 MHz, in 1-3-10 sequence								

Amplitude

Measurement Range		
Range	10 MHz to 1.5 GHz	DANL to +20 dBm
Maximum rated input level		
DC Voltage		50 V
CW RF Power	RF attenuation = 30dB	+20 dBm (100mW)
Max. Damage Level		+30 dBm (1W)
Note: When input level >+25dBm, the protect	tion switch will be on.	1 too dBiii (111)
Displayed Average Noise Level (D		
	=100 Hz, Sample Detector, Trace Average	: ≥ 50
DANL	100 kHz to 1 MHz	<-90 dBm,
(Preamplifier Off)		typ110 dBm
	1 MHz to 1.5 GHz	<-110 dBm+6 x (f/1GHz) dB,
		typ115 dBm
DANL	100 kHz to 1 MHz	<-110 dBm
(Preamplifier On)		typ130 dBm
	1 MHz to 1.5 GHz	<-130 dBm+6 x (f/1 GHz) dB,
		typ135 dBm
Level Display		
Logarithmic Level Axis		1 dB to 200 dB
Linear Level Axis		0 to Reference Level
Number of Display Points		601
Number of Traces		3 + Math Trace
Trace Detectors		Normal, Positive-peak, Negative-peak, Sample, RM
Trace Beleetere		Voltage Average, Quasi-peak
Trace Functions		Clear Write, Max Hold, Min Hold, Averag
Trace Functions		View, Blank
Units of Level Axis		dBm, dBmV, dBµV, nV, µV, mV, V, nW, µW, mW, W
Office of Level Axis		ασιιί, ασιτίν, ασμν, τίν, μν, τίιν, ν, τίνν, μνν, τίίνν, νν
Francisco December		
Frequency Response	50 MLI= 20 9C to 20 9C	
10 dB RF attenuation, relative to 5		<0.7 dD
Frequency Response	100 kHz to 1.5 GHz	<0.7 dB
(Preamplifier Off)		.4.0.10
Frequency Response	1 MHz to 1.5 GHz	<1.0 dB
(Preamplifier On)		
Innut Attanuation Cuitabina Unaca	ata in to	
Input Attenuation Switching Uncer	Tainty	0 to 20 dD in 1 dD atom
Setting Range		0 to 30 dB, in 1 dB step
Switching Uncertainty	fc=50 MHz, relative to 10 dB,	< 0.5 dB
	20 °C to 30 °C	
About the American Library		
Absolute Amplitude Uncertainty	la access	
Uncertainty	fc=50 MHz, peak detector,	±0.4 dB
	preamplifier off, 10 dB RF attenuation,	
	input signal=-10 dBm, 20 °C to 30 °C	
RBW Switching Uncertainty		
Uncertainty	100 Hz to 1 MHz, relative to 1 kHz	<0.1 dB
	RBW	
Reference Level		
Range		-100 dBm to +20 dBm, in 1 dB step
Resolution	Log Scale	0.01 dB
. Coolation	Linear Scale	4 digits
	Linear dodie	1 . 4.3
Lovel Magaurement Uncertaint		
Level Measurement Uncertainty	050/6-1	<1.5 dD nominal
Lovel Messurement Harriet		<1.5 dB, nominal
Level Measurement Uncertainty	95% confidence level, S/N>20 dB,	
Level Measurement Uncertainty	RBW=VBW=1 kHz,	
Level Measurement Uncertainty		

	-50 dBm <reference level<0,<="" td=""><td></td></reference>	
	10 MHz <fc<1.5 ghz,<="" td=""><td></td></fc<1.5>	
	20 °C to 30 °C	
RF Input VSWR		
10 dB RF Attenuation		
VSWR	1 MHz to 1.5 GHz	<1.5
Intermodulation		
Second Harmonic Intercept (SHI)		+40 dBm
Third-order Intermodulation (TOI)	fc > 30 MHz	+10 dBm
1100:0		
1dB Gain Compression	fc ≥ 50MHz,	>0 dBm
Total Power at Input Mixer	preamplifier off	>0 dBill
Note: Mixer power level (dBm) = input pov		
Note. Mixel power level (dbill) = iliput por	ver (ubiii) – input attenuation (ub).	
Spurious Responses		
Image Frequency		<-60 dBc
Intermediate Frequency		<-60 dBc
Spurious Response, Inherent		<-88 dBm, typ.
Spurious Response, Others	Referenced to local oscillators,	<-60 dBc
	referenced to A/D conversion,	
	referenced to subharmonic of first LO,	
	referenced to harmonic of first LO	4.00 dD - 6 iii
Input Related Spurious	Mixer level: -30 dBm	<-60 dBc, typ.
Sweep		
Sweep		
Sweep Time Range	100 Hz ≤ Span ≤ 1.5 GHz	10 ms to 1500 s
o noop mile range	Span=0 Hz	20 µs to 1500 s
Sweep Time Uncertainty	100 Hz ≤ Span ≤ 1.5 GHz	5%, nominal
	Span=0 Hz	0.5%, nominal
Sweep Mode		Continuous, single
Trigger Functions		
Trigger		
Trigger Source		Free run, Video, External
External Trigger Level		5 V TTL level
zacana magar zara		
Tracking Generator (DSA81	5-TG)	
TG Output		
Frequency Range		9 kHz to 1.5 GHz
Output Level		-20 dBm to 0 dBm, in 1 dB steps
Output Flatness	1 MHz to 1.5 GHz, referenced to 50 MHz	±3 dB
Inputs and Outputs		
DE Input		
RF Input Impedance		50 Ω
Connector		N female
5555.5.		
TG out		
Impedance		50 Ω
Connector		N female
10 MHz DEE In / 10 MHz DEE O.	t / External Trigger In	
10 MHz REF In / 10 MHz REF Our Connector	L/ External migger in	BNC female
10 MHz REF In Amplitude		0 dBm to +10 dBm
10 MHz REF Out Amplitude		+3dBm to +10dBm
Trigger Voltage		5 V TTL level

USB			
	USB Host		
Connector		B plug	
Protocol		Version 2.0	
	USB Device		
Connector		A plug	
Protocol		Version 2.0	

General Specifications

Display										
Туре		TFT LCD								
Resolution		800 x 480 pixels								
Size		8 inch								
Colors		64k								
Printer Supported										
Protocol		PictBridge								
		1								
D (0 ()										
Remote Control	1	1								
USB		USB TMC								
LAN Interface		10/100 Base-T, RJ-45,								
		LXI Class C								
IEC/IEEE Bus (GPIB)	with opt. USB-GPIB	IEEE 488.2								
Mass Memory										
Mass Memory		Flash Disk (internal),								
,		USB Disk (not supplied)								
		(,								
Power Supply										
Input Voltage Range, AC		100 V - 240 V, nominal								
AC Supply Frequency		45 Hz - 440 Hz,								
Power Consumption		35 W typ.								
		Max 50 W with all options.								
		'								
Temperature										
		5 °C to 40 °C								
Operating temperature range										
Storage temperature range		-20 °C to 70 °C								
Discounting										
Dimensions	(M :: 11 :: D)	004.0 470.0 400								
	(W x H x D)	361.6 mm x 178.8 mm x 128 mm								
		(14.2 inches×7.0 inches×5.0 inches)								
Weight										
	With TG	4.25kg (9.4lbs)								

Ordering Information

	Description	Order Number
Mode	Spectrum Analyzer, 9 kHz to 1.5 GHz (with preamplifier)	DSA815
	Spectrum Analyzer, 9 kHz to 1.5 GHz, with preamplifier, with track generator, installed before leaving factory	DSA815-TG
Standard	Quick Guide (Hard Copy)	QGD03X00
Accessories	CDROM (User's Guide, Programming Guide)	-
7.0000001100	Power Cable	-
	EMI Filter & Quasi-Peak Detector Kit (DSA815 only)	DSA800-EMI
	VSWR Measure Kit (DSA815 only)	DSA800-VSWR
	VSWR Bridge (2 GHz)	VB1020
	VSWR Bridge (3 GHz)	VB1030
Options	DSA PC Software	Ultra Spectrum
	Advanced Measurement Kit	DSA800-AMK
	RF Demo Kit (Transmitter)	TX1000
	USB to GPIB Interface Converter for Instrument	USB-GPIB
	Rack Mount Kit	DSA800-RMSA
Optional Accessories	DSA Accessories Package Including: N-SMA Cable, BNC-BNC Cable, N-BNC Adapter, N-SMA Adapter, 75Ω-50Ω Adapter, Antenna 2 (900MHz/1.8GHz), Antenna 2 (2.4GHz)	DSA Utility Kit
	Quick Guide, Chinese& English	QGD03X00
Orderable	User's Guide, Chinese	UGD03000
Manuals	User's Guide, English	UGD03100
(Hard Copy)	Programming Guide, Chinese	PGD03000
1-37	Programming Guide, English	PGD03100

RIGOL

Headquarter

RIGOL TECHNOLOGIES, INC. No.156,Cai He Village, Sha He Town, Chang Ping District, Beijing, 102206 P.R.China Tel:+86-10-80706688 Fax:+86-10-80705070 Email: info@rigol.com

USA

RIGOL TECHNOLOGIES, USA INC.
7401 First Place, Suite N
Oakwood Village
OH 44164, USA
Toll free: 1-877-4-RIGOL-1
Tel: (440) 232-4488
Fax: (216)-754-8107
Email: beyondmeasure@
rigoltech.com

Europe

RIGOL TECHNOLOGIES EU, GmbH Lindbergh str. 4 82178 Puchheim, Germany Tel: +49(0)89-8941895-0 Email: info-europe@ rigoltech.com

,	 	-	-	 	-	-	-	-	-	-	-	-	-	-	 -	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	 	-	-	-	-	-	-	 -	 -	-	-
1																																									
1																																									
•																																									
•																																									
:																																									
:																																									
:																																									
:																																									
:																																									
:																																									
î.																																									

RIGOL® is the registered trademark of RIGOL Technologies, Inc. Product information in this document subject to update without notice. For the latest information about RIGOL's products, applications and services, please contact local RIGOL office or access RIGOL official

website: www.rigol.com