

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006 Version 5.0 Revision Date 14.09.2012

1. IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

1.1 Product identifiers

Product name : Zinc nitrate hexahydrate

Product Number : 52-7582

Brand : Rapid

CAS-No. : 10196-18-6

1.2 Relevant identified uses of the substance or mixture and uses advised against

Identified uses : Laboratory chemicals, Manufacture of substances

1.3 Details of the supplier of the safety data sheet

Company : Rapid Electronics,
Severalls Lane,
Colchester,
Essex,
CO4 5JS, United Kingdom

Telephone : +44 (0) 1206 751166

Fax : +44 (0) 1206 751188

E-mail address : sales@rapidelec.co.uk

1.4 Emergency telephone number

Emergency Phone # : +44 (0) 1206 751166

2. HAZARDS IDENTIFICATION

2.1 Classification of the substance or mixture

Classification according to Regulation (EC) No 1272/2008 [EU-GHS/CLP]

Oxidizing solids (Category 2)

Acute toxicity, Oral (Category 4)

Skin irritation (Category 2)

Eye irritation (Category 2)

Specific target organ toxicity - single exposure (Category 3)

Classification according to EU Directives 67/548/EEC or 1999/45/EC

Contact with combustible material may cause fire. Harmful if swallowed. Irritating to eyes, respiratory system and skin.

2.2 Label elements

Labelling according Regulation (EC) No 1272/2008 [CLP]



Pictogram

Signal word

Danger

Hazard statement(s)

H272

May intensify fire; oxidiser.

H302

Harmful if swallowed.

H315

Causes skin irritation.

H319

Causes serious eye irritation.

H335

May cause respiratory irritation.

Precautionary statement(s)
 P220 Keep/Store away from clothing/ combustible materials.
 P261 Avoid breathing dust.
 P305 + P351 + P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

Supplemental Hazard Statements none

According to European Directive 67/548/EEC as amended.
 Hazard symbol(s)



R-phrase(s)

R 8 Contact with combustible material may cause fire.
 R22 Harmful if swallowed.
 R36/37/38 Irritating to eyes, respiratory system and skin.

S-phrase(s)

S17 Keep away from combustible material.
 S26 In case of contact with eyes, rinse immediately with plenty of water and seek medical advice.

2.3 Other hazards - none

3. COMPOSITION/INFORMATION ON INGREDIENTS

3.1 Substances

Formula : $N_2O_6Zn \cdot 6H_2O$
 Molecular Weight : 297.49 g/mol

| Component | Concentration |
|---------------------------------|---------------|
| Zinc nitrate hexahydrate | |
| CAS-No. 10196-18-6 | - |
| EC-No. 231-943-8 | - |

4. FIRST AID MEASURES

4.1 Description of first aid measures

General advice

Consult a physician. Show this safety data sheet to the doctor in attendance.

If inhaled

If breathed in, move person into fresh air. If not breathing, give artificial respiration. Consult a physician.

In case of skin contact

Wash off with soap and plenty of water. Consult a physician.

In case of eye contact

Rinse thoroughly with plenty of water for at least 15 minutes and consult a physician.

If swallowed

Never give anything by mouth to an unconscious person. Rinse mouth with water. Consult a physician.

4.2 Most important symptoms and effects, both acute and delayed

Fever, Cough, Nausea, Vomiting, Weakness

4.3 Indication of any immediate medical attention and special treatment needed

no data available

5. FIREFIGHTING MEASURES

5.1 Extinguishing media

Suitable extinguishing media

Use water spray, alcohol-resistant foam, dry chemical or carbon dioxide.

5.2 Special hazards arising from the substance or mixture

Zinc/zinc oxides

5.3 Advice for firefighters

Wear self contained breathing apparatus for fire fighting if necessary.

5.4 Further information

Use water spray to cool unopened containers.

6. ACCIDENTAL RELEASE MEASURES

6.1 Personal precautions, protective equipment and emergency procedures

Use personal protective equipment. Avoid dust formation. Avoid breathing vapors, mist or gas. Ensure adequate ventilation. Evacuate personnel to safe areas. Avoid breathing dust.

6.2 Environmental precautions

Do not let product enter drains.

6.3 Methods and materials for containment and cleaning up

Sweep up and shovel. Contain spillage, and then collect with an electrically protected vacuum cleaner or by wet-brushing and place in container for disposal according to local regulations (see section 13). Keep in suitable, closed containers for disposal.

6.4 Reference to other sections

For disposal see section 13.

7. HANDLING AND STORAGE

7.1 Precautions for safe handling

Avoid contact with skin and eyes. Avoid formation of dust and aerosols.

Provide appropriate exhaust ventilation at places where dust is formed. Keep away from sources of ignition - No smoking. Keep away from heat and sources of ignition.

7.2 Conditions for safe storage, including any incompatibilities

Store in cool place. Keep container tightly closed in a dry and well-ventilated place.

Hygroscopic.

7.3 Specific end uses

no data available

8. EXPOSURE CONTROLS/PERSONAL PROTECTION

8.1 Control parameters

Components with workplace control parameters

Contains no substances with occupational exposure limit values.

8.2 Exposure controls

Appropriate engineering controls

Handle in accordance with good industrial hygiene and safety practice. Wash hands before breaks and at the end of workday.

Personal protective equipment

Eye/face protection

Safety glasses with side-shields conforming to EN166 Use equipment for eye protection tested and approved under appropriate government standards such as NIOSH (US) or EN 166(EU).

Skin protection

Handle with gloves. Gloves must be inspected prior to use. Use proper glove removal technique (without touching glove's outer surface) to avoid skin contact with this product. Dispose of contaminated gloves after use in accordance with applicable laws and good laboratory practices. Wash and dry hands.

The selected protective gloves have to satisfy the specifications of EU Directive 89/686/EEC and the standard EN 374 derived from it.

Body Protection

Complete suit protecting against chemicals, The type of protective equipment must be selected according to the concentration and amount of the dangerous substance at the specific workplace.

Respiratory protection

Where risk assessment shows air-purifying respirators are appropriate use a full-face particle respirator type N100 (US) or type P3 (EN 143) respirator cartridges as a backup to engineering controls. If the respirator is the sole means of protection, use a full-face supplied air respirator. Use respirators and components tested and approved under appropriate government standards such as NIOSH (US) or CEN (EU).

9. PHYSICAL AND CHEMICAL PROPERTIES

9.1 Information on basic physical and chemical properties

- | | |
|---|--|
| a) Appearance | Form: crystalline Colour: colourless |
| b) Odour | no data available |
| c) Odour Threshold | no data available |
| d) pH | no data available |
| e) Melting point/freezing point | Melting point/range: 36 °C |
| f) Initial boiling point and boiling range | no data available |
| g) Flash point | not applicable |
| h) Evaporation rate | no data available |
| i) Flammability (solid, gas) | no data available |
| j) Upper/lower flammability or explosive limits | no data available |
| k) Vapour pressure | no data available |
| l) Vapour density | no data available |
| m) Relative density | 2.065 g/cm ³ |
| n) Water solubility | no data available |
| o) Partition coefficient: n-octanol/water | no data available |
| p) Autoignition temperature | no data available |
| q) Decomposition temperature | no data available |
| r) Viscosity | no data available |
| s) Explosive properties | no data available |
| t) Oxidizing properties | The substance or mixture is classified as oxidizing with the category 2. |

9.2 Other safety information

no data available

10. STABILITY AND REACTIVITY

10.1 Reactivity

no data available

10.2 Chemical stability

no data available

10.3 Possibility of hazardous reactions

no data available

10.4 Conditions to avoid

hygroscopic

10.5 Incompatible materials

Powdered metals, Cyanides, Sodium hypophosphite, Stannous chloride, Thiocyanates, Strong reducing agents

10.6 Hazardous decomposition products

Other decomposition products - no data available

11. TOXICOLOGICAL INFORMATION

11.1 Information on toxicological effects

Acute toxicity

LD50 Oral - rat - 1,190 mg/kg

Skin corrosion/irritation

Skin - rabbit - Severe skin irritation - 24 h

Serious eye damage/eye irritation

Eyes - rabbit - Moderate eye irritation - 24 h

Respiratory or skin sensitization

no data available

Germ cell mutagenicity

no data available

Carcinogenicity

IARC: 2A - Group 2A: Probably carcinogenic to humans (Zinc nitrate hexahydrate)

Reproductive toxicity

no data available

Specific target organ toxicity - single exposure

Inhalation - May cause respiratory irritation.

Specific target organ toxicity - repeated exposure

no data available

Aspiration hazard

no data available

Potential health effects

Inhalation

May be harmful if inhaled. Causes respiratory tract irritation.

Ingestion

Harmful if swallowed.

Skin

May be harmful if absorbed through skin. Causes skin irritation.

Eyes

Causes serious eye irritation.

Signs and Symptoms of Exposure

Fever, Cough, Nausea, Vomiting, Weakness

Additional Information

RTECS: ZH4775000

12. ECOLOGICAL INFORMATION

- 12.1 **Toxicity**
no data available
- 12.2 **Persistence and degradability**
no data available
- 12.3 **Bioaccumulative potential**
no data available
- 12.4 **Mobility in soil**
no data available
- 12.5 **Results of PBT and vPvB assessment**
no data available
- 12.6 **Other adverse effects**
no data available

13. DISPOSAL CONSIDERATIONS**13.1 Waste treatment methods****Product**

Burn in a chemical incinerator equipped with an afterburner and scrubber but exert extra care in igniting as this material is highly flammable. Offer surplus and non-recyclable solutions to a licensed disposal company.

Contaminated packaging

Dispose of as unused product.

14. TRANSPORT INFORMATION

- 14.1 **UN number**
ADR/RID: 1514 IMDG: 1514 IATA: 1514
- 14.2 **UN proper shipping name**
ADR/RID: ZINC NITRATE
IMDG: ZINC NITRATE
IATA: Zinc nitrate
- 14.3 **Transport hazard class(es)**
ADR/RID: 5.1 IMDG: 5.1 IATA: 5.1
- 14.4 **Packaging group**
ADR/RID: II IMDG: II IATA: II
- 14.5 **Environmental hazards**
ADR/RID: no IMDG Marine pollutant: no IATA: no
- 14.6 **Special precautions for user**
no data available

15. REGULATORY INFORMATION

This safety datasheet complies with the requirements of Regulation (EC) No. 1907/2006.

- 15.1 **Safety, health and environmental regulations/legislation specific for the substance or mixture**
no data available
- 15.2 **Chemical Safety Assessment**
no data available

16. OTHER INFORMATION

Further information

The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. The information in this document is based on the present state of our knowledge and is applicable to the product with regard to appropriate safety precautions. It does not represent any guarantee of the properties of the product.
