

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006 Version 5.0 Revision Date 08.08.2012

1. IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

1.1 Product identifiers

Product name : Zinc sulfate heptahydrate

Product Number : 52-7583
Brand : Rapid
Index-No. : 030-006-00-9
CAS-No. : 7446-20-0

1.2 Relevant identified uses of the substance or mixture and uses advised against

Identified uses : Laboratory chemicals, Manufacture of substances

1.3 Details of the supplier of the safety data sheet

Company : Rapid Electronics,
Severalls Lane,
Colchester,
Essex,
CO4 5JS, United Kingdom

Telephone : +44 (0) 1206 751166
Fax : +44 (0) 1206 751188
E-mail address : sales@rapidelec.co.uk

1.4 Emergency telephone number

Emergency Phone # : +44 (0) 1206 751166

2. HAZARDS IDENTIFICATION

2.1 Classification of the substance or mixture

Classification according to Regulation (EC) No 1272/2008 [EU-GHS/CLP]

Acute aquatic toxicity (Category 1)
Chronic aquatic toxicity (Category 1)
Acute toxicity, Oral (Category 4)
Serious eye damage (Category 1)
Acute aquatic toxicity (Category 1)

Classification according to EU Directives 67/548/EEC or 1999/45/EC

Harmful if swallowed. Risk of serious damage to eyes. Very toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

2.2 Label elements

Labelling according Regulation (EC) No 1272/2008 [CLP]

Pictogram




Signal word Danger

Hazard statement(s)

H302 Harmful if swallowed.
H318 Causes serious eye damage.
H410 Very toxic to aquatic life with long lasting effects.

Precautionary statement(s)	
P273	Avoid release to the environment.
P280	Wear protective gloves/ eye protection/ face protection.
P305 + P351 + P338	IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P501	Dispose of contents/ container to an approved waste disposal plant.
Supplemental Hazard Statements	none

According to European Directive 67/548/EEC as amended.

Hazard symbol(s)	
R-phrases(s)	
R22	Harmful if swallowed.
R41	Risk of serious damage to eyes.
R50/53	Very toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.
S-phrases(s)	
S22	Do not breathe dust.
S26	In case of contact with eyes, rinse immediately with plenty of water and seek medical advice.
S39	Wear eye/face protection.
S46	If swallowed, seek medical advice immediately and show this container or label.
S60	This material and its container must be disposed of as hazardous waste.
S61	Avoid release to the environment. Refer to special instructions/ Safety data sheets.

2.3 Other hazards - none

3. COMPOSITION/INFORMATION ON INGREDIENTS

3.1 Substances

Formula	:	O ₄ SZn · 7H ₂ O
Molecular Weight	:	287.56 g/mol

Component	Concentration
Zinc sulfate heptahydrate	
CAS-No.	7446-20-0
EC-No.	231-793-3
Index-No.	030-006-00-9
	-

4. FIRST AID MEASURES

4.1 Description of first aid measures

General advice

Consult a physician. Show this safety data sheet to the doctor in attendance.

If inhaled

If breathed in, move person into fresh air. If not breathing, give artificial respiration. Consult a physician.

In case of skin contact

Wash off with soap and plenty of water. Consult a physician.

In case of eye contact

Rinse thoroughly with plenty of water for at least 15 minutes and consult a physician.

If swallowed

Never give anything by mouth to an unconscious person. Rinse mouth with water. Consult a physician.

4.2 Most important symptoms and effects, both acute and delayed

Zinc oxide dust or fume can irritate the respiratory tract. Prolonged skin contact can produce a severe dermatitis called oxide pox. Exposure to high levels of dust or fume can cause metallic taste, marked thirst, coughing, fatigue, weakness, muscular pain, and nausea followed by fever and chills. Severe overexposure may result in bronchitis or pneumonia with a bluish tint to the skin., burning sensation, Cough, wheezing, laryngitis, Shortness of breath, Headache, Nausea, Vomiting, airway resistance, Cardiovascular effects., pulmonary edema, congestive heart failure

4.3 Indication of any immediate medical attention and special treatment needed

no data available

5. FIREFIGHTING MEASURES

5.1 Extinguishing media

Suitable extinguishing media

Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

5.2 Special hazards arising from the substance or mixture

Sulphur oxides, Borane/boron oxides, Zinc/zinc oxides

5.3 Advice for firefighters

Wear self contained breathing apparatus for fire fighting if necessary.

5.4 Further information

The product itself does not burn.

6. ACCIDENTAL RELEASE MEASURES

6.1 Personal precautions, protective equipment and emergency procedures

Use personal protective equipment. Avoid dust formation. Avoid breathing vapors, mist or gas. Ensure adequate ventilation. Evacuate personnel to safe areas. Avoid breathing dust.

6.2 Environmental precautions

Prevent further leakage or spillage if safe to do so. Do not let product enter drains. Discharge into the environment must be avoided.

6.3 Methods and materials for containment and cleaning up

Pick up and arrange disposal without creating dust. Sweep up and shovel. Keep in suitable, closed containers for disposal.

6.4 Reference to other sections

For disposal see section 13.

7. HANDLING AND STORAGE

7.1 Precautions for safe handling

Avoid contact with skin and eyes. Avoid formation of dust and aerosols. Provide appropriate exhaust ventilation at places where dust is formed.

7.2 Conditions for safe storage, including any incompatibilities

Store in cool place. Keep container tightly closed in a dry and well-ventilated place.

Hygroscopic.

7.3 Specific end uses

no data available

8. EXPOSURE CONTROLS/PERSONAL PROTECTION

8.1 Control parameters

Components with workplace control parameters

Contains no substances with occupational exposure limit values.

8.2 Exposure controls

Appropriate engineering controls

Handle in accordance with good industrial hygiene and safety practice. Wash hands before breaks and at the end of workday.

Personal protective equipment

Eye/face protection

Face shield and safety glasses Use equipment for eye protection tested and approved under appropriate government standards such as NIOSH (US) or EN 166(EU).

Skin protection

Handle with gloves. Gloves must be inspected prior to use. Use proper glove removal technique (without touching glove's outer surface) to avoid skin contact with this product. Dispose of contaminated gloves after use in accordance with applicable laws and good laboratory practices. Wash and dry hands.

The selected protective gloves have to satisfy the specifications of EU Directive 89/686/EEC and the standard EN 374 derived from it.

Immersion protection

Material: Nitrile rubber

Minimum layer thickness: 0.11 mm

Break through time: > 480 min

Material tested: Dermatril® (Aldrich Z677272, Size M)

Splash protection

Material: Nitrile rubber

Minimum layer thickness: 0.11 mm

Break through time: > 30 min

Material tested: Dermatril® (Aldrich Z677272, Size M)

data source: KCL GmbH, D-36124 Eichenzell, phone +49 (0)6659 873000, e-mail sales@kcl.de, test method: EN374

If used in solution, or mixed with other substances, and under conditions which differ from EN 374, contact the supplier of the CE approved gloves. This recommendation is advisory only and must be evaluated by an Industrial Hygienist familiar with the specific situation of anticipated use by our customers. It should not be construed as offering an approval for any specific use scenario.

Body Protection

Complete suit protecting against chemicals, The type of protective equipment must be selected according to the concentration and amount of the dangerous substance at the specific workplace.

Respiratory protection

Where risk assessment shows air-purifying respirators are appropriate use a full-face particle respirator type N100 (US) or type P3 (EN 143) respirator cartridges as a backup to engineering controls. If the respirator is the sole means of protection, use a full-face supplied air respirator. Use respirators and components tested and approved under appropriate government standards such as NIOSH (US) or CEN (EU).

9. PHYSICAL AND CHEMICAL PROPERTIES

9.1 Information on basic physical and chemical properties

- | | |
|--|------------------------------------|
| a) Appearance | Form: crystalline
Colour: white |
| b) Odour | no data available |
| c) Odour Threshold | no data available |
| d) pH | 4.0 - 6.0 at 50 g/l at 20 °C |
| e) Melting point/freezing point | Melting point/range: > 500 °C |
| f) Initial boiling point and boiling range | no data available |

g) Flash point	not applicable
h) Evaporation rate	no data available
i) Flammability (solid, gas)	no data available
j) Upper/lower flammability or explosive limits	no data available
k) Vapour pressure	no data available
l) Vapour density	no data available
m) Relative density	1.957 g/cm ³ at 20 °C
n) Water solubility	965 g/l at 20 °C
o) Partition coefficient: n-octanol/water	no data available
p) Autoignition temperature	no data available
q) Decomposition temperature	no data available
r) Viscosity	no data available
s) Explosive properties	no data available
t) Oxidizing properties	no data available

9.2 Other safety information

Bulk density	800 - 1,000 kg/m ³
--------------	-------------------------------

10. STABILITY AND REACTIVITY

10.1 Reactivity

no data available

10.2 Chemical stability

no data available

10.3 Possibility of hazardous reactions

no data available

10.4 Conditions to avoid

no data available

10.5 Incompatible materials

Strong oxidizing agents

10.6 Hazardous decomposition products

Other decomposition products - no data available

11. TOXICOLOGICAL INFORMATION

11.1 Information on toxicological effects

Acute toxicity

LD50 Oral - rat - 2,150 mg/kg

LD50 Intraperitoneal - rat - 200 mg/kg

Skin corrosion/irritation

no data available

Serious eye damage/eye irritation

Eyes - rabbit - Moderate eye irritation - Draize Test

Respiratory or skin sensitization

no data available

Germ cell mutagenicity

no data available

Carcinogenicity

IARC: No component of this product present at levels greater than or equal to 0.1% is identified as probable, possible or confirmed human carcinogen by IARC.

Reproductive toxicity

no data available

Specific target organ toxicity - single exposure

no data available

Specific target organ toxicity - repeated exposure

no data available

Aspiration hazard

no data available

Potential health effects

Inhalation	May be harmful if inhaled. May cause respiratory tract irritation.
Ingestion	Harmful if swallowed.
Skin	May be harmful if absorbed through skin. May cause skin irritation.
Eyes	Causes eye burns.

Signs and Symptoms of Exposure

Zinc oxide dust or fume can irritate the respiratory tract. Prolonged skin contact can produce a severe dermatitis called oxide pox. Exposure to high levels of dust or fume can cause metallic taste, marked thirst, coughing, fatigue, weakness, muscular pain, and nausea followed by fever and chills. Severe overexposure may result in bronchitis or pneumonia with a bluish tint to the skin., burning sensation, Cough, wheezing, laryngitis, Shortness of breath, Headache, Nausea, Vomiting, airway resistance, Cardiovascular effects., pulmonary edema, congestive heart failure

Additional Information

RTECS: ZH5300000

12. ECOLOGICAL INFORMATION**12.1 Toxicity**

Toxicity to fish mortality LC50 - other fish - 1 - 10 mg/l - 96.0 h

12.2 Persistence and degradability

no data available

12.3 Bioaccumulative potential

no data available

12.4 Mobility in soil

no data available

12.5 Results of PBT and vPvB assessment

no data available

12.6 Other adverse effects

Very toxic to aquatic life with long lasting effects.

13. DISPOSAL CONSIDERATIONS**13.1 Waste treatment methods****Product**

Offer surplus and non-recyclable solutions to a licensed disposal company.

Contaminated packaging

Dispose of as unused product.

14. TRANSPORT INFORMATION**14.1 UN number**

ADR/RID: 3077

IMDG: 3077

IATA: 3077

14.2 UN proper shipping name

ADR/RID: ENVIRONMENTALLY HAZARDOUS SUBSTANCE, SOLID, N.O.S. (Zinc sulfate heptahydrate)

IMDG: ENVIRONMENTALLY HAZARDOUS SUBSTANCE, SOLID, N.O.S. (Zinc sulfate heptahydrate)

IATA: Environmentally hazardous substance, solid, n.o.s. (Zinc sulfate heptahydrate)

14.3 Transport hazard class(es)

ADR/RID: 9

IMDG: 9

IATA: 9

14.4 Packaging group

ADR/RID: III

IMDG: III

IATA: III

14.5 Environmental hazards

ADR/RID: yes

IMDG Marine pollutant: yes

IATA: yes

14.6 Special precautions for user**Further information**

EHS-Mark required (ADR 2.2.9.1.10, IMDG code 2.10.3) for single packagings and combination packagings containing inner packagings with Dangerous Goods > 5L for liquids or > 5kg for solids.

15. REGULATORY INFORMATION

This safety datasheet complies with the requirements of Regulation (EC) No. 1907/2006.

15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

no data available

15.2 Chemical Safety Assessment

no data available

16. OTHER INFORMATION**Further information**

The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. The information in this document is based on the present state of our knowledge and is applicable to the product with regard to appropriate safety precautions. It does not represent any guarantee of the properties of the product.