



## 1-Piece Fixing Ties with Arrowhead, with Disc

- releasable
- for Oval Holes

### Features and Benefits

A simple one piece bundling and fixing tie with an arrowhead mount. When inserted into the hole the arrowhead locks into place and the 'disc', between the fixing and the head of the cable tie, covers the hole and minimises the ingress of dust, dirt and water, whilst adjusting for variations in panel thickness thereby ensuring a secure fixing at all times.

The RT versions are releasable and reusable, ideal for the removal or addition of cables after the initial installation is complete.


The T50SST type has a small 'tab' placed below the head which gives additional protection against axial forces and is particularly useful to assist retention on convoluted tubing.

### Application


With a diverse range of fixing possibilities this range of fixing ties are ideal for use in many different industries, for example: automotive, aerospace, white goods manufacture and panel building.



The flexible 'discs' adjust to take up variations in panel thickness - ensuring a firm fixing at all times.



Common head/fixing design



Special design without a gap between head and bundle; T50MD7

#### Material Data

Material	<b>Polyamide 6.6 (PA66)</b>
Operating Temperature	<b>-40 °C to +85 °C Continuous, (+105 °C for 500 h)</b>
Flammability	<b>UL94 V2</b>



#### Material Data

Material	<b>Polyamide 6.6 Heat Stabilised (PA66HS)</b>
Operating Temperature	<b>-40 °C to +105 °C Continuous, (+145 °C for 500 h)</b>
Flammability	<b>UL94 V2</b>



#### Technical Table

Article-No.	Type	Length (L)	Width (W)	Bundle Ø max.	Min. Tensile strength for ties (N)	Disc Ø	Hole Ø	Panel Thickness min.	Panel Thickness max.	Material	Colour
111-85350	<b>T50SD6</b>	160	5.0	31.0	225	18.0	6.3-7.5	0.6	1.8	PA66HS	Black (BK)
126-02300	<b>T50SST5</b>	170	4.6	31.0	225	16.2	6.1-6.5	0.7	1.5	PA66	Natural (NA)
126-00017	<b>T50SST5</b>	170	4.6	31.0	225	16.2	6.1-6.5	0.7	1.5	PA66HS	Black (BK)
111-85850	<b>T50MD7</b>	225	5.0	59.0	225	16.0	6.8-7.2	1.2	2.0	PA66HS	Black (BK)
126-03102	<b>T50SOSFT6.5E</b>	160	4.6	35.0	225	16.0	6.3-6.7	1.9	2.5	PA66HS	Black (BK)
126-00099	<b>T50SOSKSFT5SE</b>	156	4.6	35.0	180	16,0	4.8-5.2	0.7	1.3	PA66HS	Black (BK)
126-00111	<b>T50SOSFT5S-E</b>	156	4,6	35.0	180	16,0	4.8-5.2	0,7	1,3	PA66HS	Natural (NA)
126-00075	<b>T50SOSKSFT5.4E</b>	156	4.6	35.0	225	16,0	5.2-5.6	0.7	1.3	PA66HS	Black (BK)
126-00081	<b>T50SOSKSFT6SE</b>	156	4.6	35.0	180	16,0	6.3-6.7	0.7	1.3	PA66HS	Black (BK)
126-00086	<b>T50SOSFT6.5S2-E</b>	157	4.6	35.0	225	16.0	6.3-6.7	1.7	2.3	PA66HS	Black (BK)
Releasable											
111-85480	<b>RT50SD6</b>	160	5.0	31.0	180	18.0	6.3-7.5	0.6	1.8	PA66HS	Black (BK)
for Oval Holes											
126-00015	<b>T50SDOP</b>	160	5.0	30.0	225	22.0	6.2x12.2	0.7	2.0	PA66HS	Black (BK)
126-01600	<b>T50SDOR</b>	160.0	5.0	30.0	225	22.0	6.2x12.2	0.5	1.5	PA66HS	Black (BK)

All dimensions in mm. Subject to technical changes.