

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1 Product identifiers

Product name : Butyraldehyde

Product Number : 52-7588

Brand : Rapid

Index-No. : 605-006-00-2

REACH No. : A registration number is not available for this substance as the substance or its uses are exempted from registration, the annual tonnage does not require a registration or the registration is envisaged for a later registration deadline.

CAS-No. : 123-72-8

1.2 Relevant identified uses of the substance or mixture and uses advised against

Identified uses : Laboratory chemicals, Manufacture of substances

1.3 Details of the supplier of the safety data sheet

Company : Rapid Electronics,
Severalls Lane,
Colchester,
Essex,
CO4 5JS, United Kingdom

Telephone : +44 (0) 1206 751166

Fax : +44 (0) 1206 751188

E-mail address : sales@rapidelec.co.uk

Emergency telephone number : +44 (0) 1206 751166

SECTION 2: Hazards identification

2.1 Classification of the substance or mixture

Classification according to Regulation (EC) No 1272/2008

Flammable liquids (Category 2), H225

Eye irritation (Category 2), H319

For the full text of the H-Statements mentioned in this Section, see Section 16.

Classification according to EU Directives 67/548/EEC or 1999/45/EC

F Highly flammable R11

For the full text of the R-phrases mentioned in this Section, see Section 16.

2.2 Label elements

Labelling according Regulation (EC) No 1272/2008

Pictogram



Signal word : Danger

Hazard statement(s)
H225

Highly flammable liquid and vapour.

H319	Causes serious eye irritation.
Precautionary statement(s) P210 P305 + P351 + P338	Keep away from heat/sparks/open flames/hot surfaces. - No smoking. IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
Supplemental Hazard Statements	none

2.3 Other hazards - none

SECTION 3: Composition/information on ingredients

3.1 Substances

Synonyms	:	Butanal
Formula	:	C ₄ H ₈ O
Molecular Weight	:	72.11 g/mol
CAS-No.	:	123-72-8
EC-No.	:	204-646-6
Index-No.	:	605-006-00-2

No components need to be disclosed according to the applicable regulations.

For the full text of the H-Statements and R-Phrases mentioned in this Section, see Section 16

SECTION 4: First aid measures

4.1 Description of first aid measures

General advice

Consult a physician. Show this safety data sheet to the doctor in attendance.

If inhaled

If breathed in, move person into fresh air. If not breathing, give artificial respiration. Consult a physician.

In case of skin contact

Wash off with soap and plenty of water. Consult a physician.

In case of eye contact

Rinse thoroughly with plenty of water for at least 15 minutes and consult a physician.

If swallowed

Do NOT induce vomiting. Never give anything by mouth to an unconscious person. Rinse mouth with water. Consult a physician.

4.2 Most important symptoms and effects, both acute and delayed

The most important known symptoms and effects are described in the labelling (see section 2.2) and/or in section 11

4.3 Indication of any immediate medical attention and special treatment needed

no data available

SECTION 5: Firefighting measures

5.1 Extinguishing media

Suitable extinguishing media

Use water spray, alcohol-resistant foam, dry chemical or carbon dioxide.

5.2 Special hazards arising from the substance or mixture

Carbon oxides

5.3 Advice for firefighters

Wear self contained breathing apparatus for fire fighting if necessary.

5.4 Further information

Use water spray to cool unopened containers.

SECTION 6: Accidental release measures

6.1 Personal precautions, protective equipment and emergency procedures

Use personal protective equipment. Avoid breathing vapours, mist or gas. Ensure adequate ventilation. Remove all sources of ignition. Evacuate personnel to safe areas. Beware of vapours accumulating to form explosive concentrations. Vapours can accumulate in low areas.
For personal protection see section 8.

6.2 Environmental precautions

Prevent further leakage or spillage if safe to do so. Do not let product enter drains. Discharge into the environment must be avoided.

6.3 Methods and materials for containment and cleaning up

Contain spillage, and then collect with an electrically protected vacuum cleaner or by wet-brushing and place in container for disposal according to local regulations (see section 13).

6.4 Reference to other sections

For disposal see section 13.

SECTION 7: Handling and storage

7.1 Precautions for safe handling

Avoid contact with skin and eyes. Avoid inhalation of vapour or mist.
Keep away from sources of ignition - No smoking. Take measures to prevent the build up of electrostatic charge.
For precautions see section 2.2.

7.2 Conditions for safe storage, including any incompatibilities

Store in cool place. Keep container tightly closed in a dry and well-ventilated place. Containers which are opened must be carefully resealed and kept upright to prevent leakage.

Stench. Dry residue is explosive.

7.3 Specific end use(s)

Apart from the uses mentioned in section 1.2 no other specific uses are stipulated

SECTION 8: Exposure controls/personal protection

8.1 Control parameters

Components with workplace control parameters

Contains no substances with occupational exposure limit values.

8.2 Exposure controls

Appropriate engineering controls

Handle in accordance with good industrial hygiene and safety practice. Wash hands before breaks and at the end of workday.

Personal protective equipment

Eye/face protection

Face shield and safety glasses Use equipment for eye protection tested and approved under appropriate government standards such as NIOSH (US) or EN 166(EU).

Skin protection

Handle with gloves. Gloves must be inspected prior to use. Use proper glove removal technique (without touching glove's outer surface) to avoid skin contact with this product. Dispose of contaminated gloves after use in accordance with applicable laws and good laboratory practices. Wash and dry hands.

The selected protective gloves have to satisfy the specifications of EU Directive 89/686/EEC and the standard EN 374 derived from it.

Splash contact

Material: butyl-rubber
Minimum layer thickness: 0.3 mm
Break through time: 30 min
Material tested: Butoject® (KCL 897 / Aldrich Z677647, Size M)

data source: KCL GmbH, D-36124 Eichenzell, phone +49 (0)6659 87300, e-mail sales@kcl.de,
test method: EN374

If used in solution, or mixed with other substances, and under conditions which differ from EN 374, contact the supplier of the CE approved gloves. This recommendation is advisory only and must be evaluated by an industrial hygienist and safety officer familiar with the specific situation of anticipated use by our customers. It should not be construed as offering an approval for any specific use scenario.

Body Protection

impervious clothing, Flame retardant antistatic protective clothing, The type of protective equipment must be selected according to the concentration and amount of the dangerous substance at the specific workplace.

Respiratory protection

Where risk assessment shows air-purifying respirators are appropriate use a full-face respirator with multi-purpose combination (US) or type ABEK (EN 14387) respirator cartridges as a backup to engineering controls. If the respirator is the sole means of protection, use a full-face supplied air respirator. Use respirators and components tested and approved under appropriate government standards such as NIOSH (US) or CEN (EU).

Control of environmental exposure

Prevent further leakage or spillage if safe to do so. Do not let product enter drains. Discharge into the environment must be avoided.

SECTION 9: Physical and chemical properties

9.1 Information on basic physical and chemical properties

a) Appearance	Form: clear, liquid Colour: colourless
b) Odour	pungent
c) Odour Threshold	no data available
d) pH	6.0 - 7.0 at 71 g/l at 20 °C
e) Melting point/freezing point	Melting point/range: -96 °C - lit.
f) Initial boiling point and boiling range	75 °C - lit.
g) Flash point	-5 °C - closed cup
h) Evaporation rate	no data available
i) Flammability (solid, gas)	no data available
j) Upper/lower flammability or explosive limits	Upper explosion limit: 8 %(V) Lower explosion limit: 1.8 %(V)
k) Vapour pressure	120 hPa at 20 °C
l) Vapour density	2.49 - (Air = 1.0)
m) Relative density	0.8 g/cm ³ at 25 °C
n) Water solubility	50 g/l at 20 °C - OECD Test Guideline 105 - soluble
o) Partition coefficient: n-octanol/water	log Pow: 0.79
p) Auto-ignition	190 °C at 1,013.0 hPa

temperature

- | | |
|------------------------------|-------------------|
| q) Decomposition temperature | no data available |
| r) Viscosity | no data available |
| s) Explosive properties | no data available |
| t) Oxidizing properties | no data available |

9.2 Other safety information

- | | |
|-------------------------|--------------------|
| Surface tension | 70 mN/m at 20 °C |
| Relative vapour density | 2.49 - (Air = 1.0) |

SECTION 10: Stability and reactivity

10.1 Reactivity

no data available

10.2 Chemical stability

Stable under recommended storage conditions.

10.3 Possibility of hazardous reactions

no data available

10.4 Conditions to avoid

Heat, flames and sparks. Extremes of temperature and direct sunlight.

10.5 Incompatible materials

Oxidizing agents, Strong bases, Strong reducing agents, Strong acids

10.6 Hazardous decomposition products

Other decomposition products - no data available

In the event of fire: see section 5

SECTION 11: Toxicological information

11.1 Information on toxicological effects

Acute toxicity

LD50 Oral - rat - male and female - 5,890 mg/kg
(OECD Test Guideline 401)

LC50 Inhalation - rat - male and female - 4 h - > 5.46 mg/l
(OECD Test Guideline 403)

LD50 Dermal - rabbit - 3,560 mg/kg

Skin corrosion/irritation

Skin - rabbit

Result: No skin irritation - 4 h
(OECD Test Guideline 404)

Serious eye damage/eye irritation

Eyes - rabbit

Result: Irritating to eyes. - 24 h
(Directive 67/548/EEC, Annex V, B.5.)

Respiratory or skin sensitisation

Buehler Test - guinea pig

Result: Does not cause skin sensitisation.
(OECD Test Guideline 406)

Germ cell mutagenicity

no data available

Ames test
S. typhimurium
Result: negative

Drosophila melanogaster - male
Result: negative

Carcinogenicity

IARC: No component of this product present at levels greater than or equal to 0.1% is identified as probable, possible or confirmed human carcinogen by IARC.

Reproductive toxicity

no data available

Specific target organ toxicity - single exposure

no data available

Specific target organ toxicity - repeated exposure

no data available

Aspiration hazard

no data available

Additional Information

RTECS: ES2275000

To the best of our knowledge, the chemical, physical, and toxicological properties have not been thoroughly investigated.

SECTION 12: Ecological information

12.1 Toxicity

Toxicity to fish static test LC50 - Pimephales promelas (fathead minnow) - 25.8 mg/l - 96 h

Toxicity to daphnia and other aquatic invertebrates static test EC50 - Daphnia magna (Water flea) - 195 mg/l - 24 h (DIN 38412)

Toxicity to bacteria EC50 - Photobacterium phosphoreum - 99.1 mg/l - 25 min

12.2 Persistence and degradability

Biodegradability aerobic - Exposure time 5 d
Result: 46 - 57 % - Readily biodegradable.
(OECD Test Guideline 301C)

Ratio BOD/ThBOD 28 - 43 %

12.3 Bioaccumulative potential

No bioaccumulation is to be expected ($\log Pow \leq 4$).

12.4 Mobility in soil

no data available

12.5 Results of PBT and vPvB assessment

PBT/vPvB assessment not available as chemical safety assessment not required/not conducted

12.6 Other adverse effects

Harmful to aquatic life.

SECTION 13: Disposal considerations**13.1 Waste treatment****methods Product**

Burn in a chemical incinerator equipped with an afterburner and scrubber but exert extra care in igniting as this material is highly flammable. Offer surplus and non-recyclable solutions to a licensed disposal company.

Contaminated packaging

Dispose of as unused product.

SECTION 14: Transport information**14.1 UN number**

ADR/RID: 1129

IMDG: 1129

IATA: 1129

14.2 UN proper shipping name

ADR/RID: BUTYRALDEHYDE

IMDG: BUTYRALDEHYDE

IATA: Butyraldehyde

14.3 Transport hazard class(es)

ADR/RID: 3

IMDG: 3

IATA: 3

14.4 Packaging group

ADR/RID: II

IMDG: II

IATA: II

14.5 Environmental hazards

ADR/RID: no

IMDG Marine pollutant: no

IATA: no

14.6 Special precautions for user

no data available

SECTION 15: Regulatory information

This safety datasheet complies with the requirements of Regulation (EC) No. 1907/2006.

15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

no data available

15.2 Chemical Safety Assessment

For this product a chemical safety assessment was not carried out

SECTION 16: Other information**Full text of H-Statements referred to under sections 2 and 3.**

H225

Highly flammable liquid and vapour.

H319

Causes serious eye irritation.

Full text of R-phrases referred to under sections 2 and 3

R11

Highly flammable.

Further information

The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. The information in this document is based on the present state of our knowledge and is applicable to the product with regard to appropriate safety precautions. It does not represent any guarantee of the properties of the product.
