

DATA SHEET

Light Bars and Bargraphs

Order code	Manufacturer code	Description
55-0190	DC-10EWA	RED 10 BAR DIL LED ARRAY (RC)
55-0195	DC-10GWA	GREEN 10 BAR DIL LED ARRAY (RC)
55-0197	DC-10YWA	YELLOW 10 BAR DIL LED ARRAY (RC)

Light Dara and Dargrapha	Page 1 of
The enclosed information is believed to be correct, information may change 'without notice' due to	Revision A ^o
product improvement. Users should ensure that the product is suitable for their use. E. & O. E.	12/12/2006

Sales: 01206 751166 Technical: 01206 835555 Fax: 01206 751188 Sales@rapidelec.co.uk Tech@rapidelec.co.uk www.rapidelectronics.co.uk

Kingbright

10 SEGMENT BAR GRAPH ARRAYS

DC-10E DC-10Y DC-10G DC-10SR

DC-7G3H

Features

- •SUITABLE FOR LEVEL INDICATORS.
- •LOW CURRENT OPERATION.
- •EXCELLENT ON/OFF CONTRAST.
- •WIDE VIEWING ANGLE.
- •END STACKABLE.
- •MECHANICALLY RUGGED.
- •BI-COLOR VERSION AVAILABLE.
- •DIFFERENT COLORS IN ONE UNIT AVAILABLE.

Description

The Bright Red source color devices are made with Gallium Phosphide Red Light Emitting Diode.


The Green source color devices are made with Gallium Phosphide Green Light Emitting Diode.


The High Efficiency Red source color devices are made with Gallium Arsenide Phosphide on Gallium Phosphide Orange Light Emitting Diode.


The Yellow source color devices are made with Gallium Arsenide Phosphide on Gallium Phosphide Yellow Light Emitting Diode.


The Super Bright Red source color devices are made with Gallium Aluminum Arsenide Red Light Emitting Diode.

Package Dimensions & Internal Circuit Diagram









Notes:

- 1. All dimensions are inmillimeters (inches), Tolerance is ±0.25(0.01")unless otherwise noted.
 2. Specifications are subjected to change whitout notice.

Selection Guide

Part No.	Dice	lv (ucd) @ 10 mA			
	2.00	Min.	Max.	Description	
DC-10EWA	HIGH EFFICIENCY RED (GaAsP/GaP)	2200	5600		
DC-10GWA	GREEN (GaP)	2200	5600		
DC-10YWA	YELLOW (GaAsP/GaP)	2200	5600	10 Segments	
DC-10SRWA	SUPER BRIGHT RED (GaAlAs)	5600	31000	Bargraph-Display	
DO 7001 IIMA	GREEN (GaP)	000	0000		
DC-7G3HWA	BRIGHT RED (GaP)	900	2200		


Electrical / Optical Characteristics at T $_{\text{A}}\text{=-}25^{\circ}\text{C}$

Symbol	Parameter	Device	Тур.	Max.	Unit	Test Conditions
λpeak	Peak Wavelength	Bright Red High Efficiency Red Green Yellow Super Bright Red	700 625 565 590 660		nm	IF=20mA
Δλ1/2	Spectral Line Halfwidth	Bright Red High Efficiency Red Green Yellow Super Bright Red	45 45 30 35 20		nm	IF=20mA
С	Capacitance	Bright Red High Efficiency Red Green Yellow Super Bright Red	40 12 45 10 95		pF	VF=0V;f=1MHz
VF	Forward Voltage	Bright Red High Efficiency Red Green Yellow Super Bright Red	2.0 2.0 2.2 2.1 1.85	2.5 2.5 2.5 2.5 2.5 2.5	V	IF=20mA
I _R	Reverse Current	All	10		uA	VR = 5V

Absolute Maximum Ratings at T_A=25°C


Parameter	Bright Red	High Efficiency Red	Green	Yellow	Super Bright Red	Units
Power dissipation	120	105	105	105	100	mW
DC Forward Current	25	30	25	30	30	mA
Peak Forward Current [1]	150	150	150	150	150	mA
Reverse Voltage	5	5	5	5	5	V
Operating/Storage Temperature	-40°C To +85°C					
Lead Soldering Temperature [2]	260 °C For 5 Seconds					

Notes: 1. 1/10 Duty Cycle, 0.1ms Pulse Width. 2. 4mm below package base.





Wavelength λ (nm) RELATIVE INTENSITY Vs. WAVELENGTH


Bright Red




IF-Forward Current(mA) LUMINOUS INTENSITY Vs. FORWARD CURRENT




















Super Bright Red

