

## Safety Data Sheet according to Regulation (EC) No. 1907/2006 (REACH)

---

### 1. Identification of the substance/mixture and of the company/undertaking

#### 1.1 Product identifier

Trade name/designation	Styrene monomer
Product No.	52-7602
Substance name	Styrene
CAS No.	100-42-5
INDEX no.	601-026-00-0
REACH registration No.	Not yet communicated down the supply chain.
other means of identification	Phenylethene Phenylethylene Vinylbenzene

#### 1.2 Relevant identified uses of the substance or mixture and uses advised against

Relevant identified uses for laboratory use and chemical production.

#### 1.3 Details of the supplier of the safety data sheet

Supplier (manufacturer/importer/only representative/downstream user/distributor)

Address	Rapid Electronics, Severalls Lane, Colchester, Essex, CO4 5JS, United Kingdom
Telephone	: +44 (0) 1206 751166
Fax	: +44 (0) 1206 751188
E-mail address	: sales@rapidelec.co.uk

#### 1.4 Emergency telephone

Telephone +44 (0) 1206 751166

---

### 2. Hazards identification

#### 2.1 Classification of the substance or mixture

##### 2.1.1 Classification according to Regulation (EC) No. 1272/2008 [CLP]

hazard classes and hazard categories	Hazard Statements	classification procedure	remark
Flammable liquid, category 3	H226		
Acute toxicity, category 4, inhalation	H332		

Eye irritation, category 2	H319		
Skin irritation, category 2	H315		

## 2.1.2 Classification according to Directive 67/548/EEC or 1999/45/EC

Hazard symbols:	R-phrases
	R10
Xn	R20
Xi	R36/38

## 2.2 Label elements

### 2.2.1 Labelling according to Regulation (EC) No. 1272/2008 [CLP]



Signal word

Danger

#### Hazard Statements

H226	Flammable liquid and vapour.
H332	Harmful if inhaled.
H319	Causes serious eye irritation.
H315	Causes skin irritation.

#### Precautionary statements

P210	Keep away from heat/sparks/open flames/hot surfaces. No smoking.
P243	Take precautionary measures against static discharge.
P280	Wear protective gloves/protective clothing/eye protection/face protection.
P302+P352	IF ON SKIN: Wash with plenty of soap and water.
P304+P340	IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing.
P305+P351+P338	IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P309+P311	IF exposed or if you feel unwell: Call a POISON CENTER or doctor/physician.

### 2.2.2 Labelling (67/548/EEC or 1999/45/EC)

Hazard symbols:

Xn

R-phrases

R10	Flammable.
R20	Harmful by inhalation.
R36/38	Irritating to eyes and skin.

S-phrases

S23	Do not breathe gas/fumes/vapour/spray (appropriate wording to be specified by the manufacturer).
-----	--

## 2.3 Other hazards

SVHC

No

---

## 3. Composition/ Information on ingredients

Molecular formula	C8H8
Molecular weight (g/mol)	104.15 g/mol
CAS No.	100-42-5
EC No	202-851-5
INDEX no.	601-026-00-0

---

## 4. First-aid measures

### 4.1 General information

IF exposed or if you feel unwell: Call a POISON CENTER or doctor/physician. If unconscious place in recovery position and seek medical advice. Never give anything by mouth to an unconscious person or a person with cramps. Change contaminated, saturated clothing. Do not leave affected person unattended.

### 4.2 After inhalation

Call a POISON CENTER or doctor/physician. Remove casualty to fresh air and keep warm and at rest. If breathing is irregular or stopped, administer artificial respiration.

### 4.3 In case of skin contact

After contact with skin, wash immediately with plenty of water and soap. Remove contaminated, saturated clothing immediately. In case of skin reactions, consult a physician.

### 4.4 After eye contact

In case of contact with eyes flush immediately with plenty of flowing water for 10 to 15 minutes holding eyelids apart and consult an ophthalmologist. Protect uninjured eye. Remove contact lenses, if present and easy to do. Continue rinsing.

### 4.5 After ingestion

If accidentally swallowed rinse the mouth with plenty of water (only if the person is conscious) and obtain immediate medical attention. Do not induce vomiting. Give nothing to eat or drink.

### 4.6 Self-protection of the first aider

First aider: Pay attention to self-protection!

### 4.7 Information to physician:

Symptoms	No data available
Hazards	No data available
Treatment	No data available

---

## 5. Firefighting measures

### 5.1 Suitable extinguishing media

Water spray ABC-powder Carbon dioxide (CO<sub>2</sub>) Nitrogen

### 5.2 Extinguishing media which must not be used for safety reasons:

no restriction

### 5.3 Special hazards arising from the substance or mixture

In case of fire may be liberated: Carbon dioxide (CO<sub>2</sub>) Carbon monoxide

### 5.4 Advice for firefighters

DO NOT fight fire when fire reaches explosives. In case of fire: Wear self-contained breathing apparatus.

### 5.5 Additional information

Do not allow run-off from fire-fighting to enter drains or water courses. Do not inhale explosion and combustion gases. Use caution when applying carbon dioxide in confined spaces. Carbon dioxide can displace oxygen. Use water spray jet to protect personnel and to cool endangered containers.

---

## 6. Accidental release measures

### 6.1 Personal precautions, protective equipment and emergency procedures

Avoid generation of dust. Do not breathe dust/fume/gas/mist/vapours/spray. Provide adequate ventilation. Avoid contact with skin, eyes and clothes.

### 6.2 Environmental precautions

Do not allow to enter into surface water or drains. Danger of explosion.

### 6.3 Methods and material for containment and cleaning up

Spilled product must never be returned to the original container for recycling. Clean contaminated objects and areas thoroughly observing environmental regulations. Absorb with liquid-binding material (e.g. sand, diatomaceous earth, acid- or universal binding agents). Collect in closed and suitable containers for disposal.

### 6.4 Additional information

Clear spills immediately.

---

## 7. Handling and storage

### 7.1 Precautions for safe handling

Avoid: Inhalation. Avoid contact with skin and eyes. Use extractor hood (laboratory). If handled uncovered, arrangements with local exhaust ventilation have to be used. If local exhaust ventilation is not possible or not sufficient, the entire working area must be ventilated by technical means. Protect from moisture.

## 7.2 Conditions for safe storage, including any incompatibilities

storage temperature No data available

Keep container tightly closed in a cool, well-ventilated place.

## 7.3 Specific end use(s)

No data available

---

## 8. Exposure controls / Personal protection

### 8.1 Control parameters

Does not contain substances above concentration limits fixing an occupational exposure limit.

### 8.2 Appropriate engineering controls

Technical measures and the application of suitable work processes have priority over personal protection equipment. If handled uncovered, arrangements with local exhaust ventilation have to be used.

### 8.3 Personal protective equipment

Wear suitable protective clothing. When handling with chemical substances, protective clothing with CE-labels including the four control digits must be worn.

#### 8.3.1 Eye / face protection

Eye glasses with side protection DIN-/EN-Norms: DIN EN 166

#### 8.3.2 Skin protection

When handling with chemical substances, protective gloves must be worn with the CE-label including the four control digits. Recommended glove articles DIN-/EN-Norms: DIN EN 374 In the case of wanting to use the gloves again, clean them before taking off and air them well.

##### By short-term hand contact

Suitable material: No data available

Thickness of the glove material No data available

Breakthrough time (maximum wearing time) No data available

Recommended glove articles No data available

##### By long-term hand contact

Suitable material: No data available

Thickness of the glove material No data available

Breakthrough time (maximum wearing time) No data available

Recommended glove articles

No data available

### 8.3.3 Protective clothing

Wash hands before breaks and after work. Avoid contact with skin and eyes. When using do not eat, drink or smoke. Provide eye shower and label its location conspicuously.

### 8.3.4 Respiratory protection

Respiratory protection necessary at: aerosol or mist formation.

Suitable respiratory protection apparatus:	No data available
Recommendation	No data available
Suitable material:	No data available
Recommendation	No data available

### 8.4 Additional information

Wash hands before breaks and after work. Avoid contact with skin and eyes. When using do not eat, drink or smoke. Provide eye shower and label its location conspicuously.

---

## 9. Physical and chemical properties

### 9.1 Information on basic physical and chemical properties

(a) Appearance	
Physical state	liquid
Colour	colourless
(b) Odour	No data available
(c) Odour threshold	No data available

#### **Safety relevant basic data**

(d) pH	No data available
(e) Melting point/freezing point	-31°C
(f) Initial boiling point and boiling range	145.2°C (1013 hPa)
(g) Flash point	31°C
(h) Evaporation rate	No data available
(i) Flammability (solid, gas)	Flammable liquid and vapour.
(j) Upper/lower flammability or explosive limits	
Lower explosion limit (Vol-%)	1.1
Upper explosion limit (Vol-%)	8.9
(k) Vapour pressure	6 hPa (20°C)
(l) Vapour density	3.6 (20°C)
(m) Relative density	0.906 g/cm <sup>3</sup> (20°C)
(n) Solubility(ies)	
Water solubility (g/l)	0,3 g/l (20°C)
at °C:	20
Soluble (g/l) in	No data available
(o) Partition coefficient: n-octanol/water	2.95 (20°C)
(p) Auto-ignition temperature	490°C
(q) Decomposition temperature	No data available
(r) Viscosity	

Kinematic viscosity	No data available
Dynamic viscosity	No data available
(s) Explosive properties	not applicable
(t) Oxidising properties	not applicable

## 9.2 Other information

Bulk density	No data available
refraction index	1.5463 (589 nm, 20°C)
dissociation constant	No data available
Surface tension	No data available
Henry constant	No data available

## 10. Stability and reactivity

### 10.1 Reactivity

No data available

### 10.2 Chemical stability

No data available

### 10.3 Possibility of hazardous reactions

No data available

### 10.4 Conditions to avoid

No data available

### 10.5 Incompatible materials

No data available

### 10.6 Hazardous decomposition products

No data available

### 10.7 Additional information

No data available

## 11. Toxicological information

### 11.1 Information on toxicological effects

#### **Acute effects**

Acute oral toxicity

Effective dose No data available  
species: No data available  
Exposure time  
remark  
source

Acute dermal toxicity  
Effective dose No data available  
species: No data available  
Exposure time  
remark  
source

Acute inhalation toxicity  
Effective dose No data available  
species: No data available  
Exposure time  
remark  
source

#### **Irritant and corrosive effects**

Primary irritation to the skin  
Exposure time  
species:  
Result

Irritation to eyes  
Exposure time  
species:  
Result

Irritation to respiratory tract  
Exposure time  
species:  
Result

#### **Sensitisation**

In case of skin contact not sensitising.  
After inhalation not sensitising.

#### **Specific target organ toxicity (single exposure)**

not relevant

#### **Specific target organ toxicity (repeated exposure)**

not relevant

#### **CMR effects (carcinogenicity, mutagenicity and**



**toxicity for reproduction)**

**Carcinogenicity**

No indication of human carcinogenicity.

**Germ cell mutagenicity/Genotoxicity**

No indications of human germ cell mutagenicity exist.

**Reproductive toxicity**

No indications of human reproductive toxicity exist.

**Aspiration hazard**

not relevant

11.2 Other adverse effects

No data available

11.3 Additional information

No data available

---

12. Ecological information

12.1 Ecotoxicity

**Acute (short-term) fish toxicity**

LC50: No data available  
EC50  
species:  
Exposure time

**Chronic (long-term) fish toxicity**

LC50: No data available  
EC50  
species:  
Exposure time

**Acute (short-term) daphnia toxicity**

LC50: No data available  
EC50  
species:  
Exposure time

**Chronic (long-term) daphnia toxicity**

LC50: No data available  
EC50  
species:

Exposure time

**Acute (short-term) algae toxicity**

LC50: No data available

EC50

species:

Exposure time

**Chronic (long-term) algae toxicity**

LC50: No data available

EC50

species:

Exposure time

12.2 Persistence and degradability

No data available

12.3 Bioaccumulative potential

(o) Partition coefficient: n-octanol/water 2.95 (20°C)

12.4 Mobility in soil

No data available

12.5 Results of PBT assessment

No data available

12.6 Other adverse effects

No data available

---

13. Disposal considerations

13.1 Waste treatment methods

**Appropriate disposal / Product**

Dispose according to legislation. Consult the appropriate local waste disposal expert about waste disposal.

Waste code product No data available

**Appropriate disposal / Package**

13.2 Additional information

No data available

---

14. Transport information

14.1 Land transport (ADR/RID)

UN-No.	No data available
Proper Shipping Name	No data available
Class(es)	No data available
Classification code:	No data available
Packing group	No data available
Hazard label(s)	No data available

14.2 Sea transport (IMDG)

UN-No.	No data available
Proper Shipping Name	No data available
Class(es)	No data available
Classification code:	No data available
Packing group	No data available
Marine pollutant	
Segregation group	

14.3 Air transport (ICAO-TI / IATA-DGR)

UN-No.	No data available
Proper Shipping Name	No data available
Class(es)	No data available
Classification code:	No data available
Packing group	No data available

14.4 Additional information

No data available

---

15. Regulatory information

15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

Water hazard class (WGK)	2
--------------------------	---

15.2 Chemical Safety Assessment

No data available

---

16. Other information

16.1 Relevant R-, H- and EUH-phrases (Number and full text)

---

R10	Flammable.
R20	Harmful by inhalation.
R36/38	Irritating to eyes and skin.

H226	Flammable liquid and vapour.
H332	Harmful if inhaled.
H319	Causes serious eye irritation.
H315	Causes skin irritation.

## 16.2 Additional information

Indication of changes

general update

*The above information describes exclusively the safety requirements of the product and is based on our present-day knowledge. The information is intended to give you advice about the safe handling of the product named in this safety data sheet, for storage, processing, transport and disposal. The information cannot be transferred to other products. In the case of mixing the product with other products or in the case of processing, the information on this safety data sheet is not necessarily valid for the new made-up material.*