


Art.- No.	Bemessungswerte/Ratings/Valeurs assignées			Spannungsfall Voltage drop Chute de tension max [mV]	Schmelzintegral Melting integral Intégral de fusion [A ² s]
	Strom Current Courant	Spannung Voltage Tension	Ausschaltvermögen Breaking capacity Pouvoir de coupure		
520.107	100 mA	250 V	35 A	3000	0,0020
520.108	125 mA			3000	0,0031
520.109	160 mA			3000	0,0051
520.110	200 mA			2000	0,0160
520.111	250 mA			2000	0,0288
520.112	315 mA			2000	0,0496
520.113	400 mA			1500	0,0960
520.114	500 mA			1500	0,1700
520.115	630 mA			500	0,2000
520.116	800 mA			500	0,3200
520.117	1 A			250	0,6000
520.118	1,25 A			250	1,2500
520.119	1,6 A		1500 A	1000	0,2600
520.120	2 A			700	2,0000
520.121	2,5 A			700	3,1250
520.122	3,15 A			600	3,9700
520.123	4 A			600	6,4000
520.124	5 A			500	14,5000
520.125	6,3 A			500	23,8100
520.126	8 A			400	32,0000
520.127	10 A			400	60,0000
520.128	12,5 A			300	78,1300

Aufbau: 100 mA-1,25 A Glasrohr, durchsichtig
1,6-12,5 A Keramikrohr
Kontaktkappen: Messing, vernickelt
Verpackung: 100 St. = 10 x 10 Faltschachteln
1000 St. = Industrieverpackung

Construction: 100 mA-1,25 A Glasstube, transparent
1,6-12,5 A ceramic-tube
Contact caps: Brass, nickel plated
Packing: 100 pcs. = 10 boxes of 10 pieces
1000 pcs. = Industrial boxes

Construction: 100 mA-1,25 A Tube verre, transparent
1,6-12,5 A Tube céramique
Cabochons de contact: Laiton, nickelé
Emballage: 100 pcs. = en 10 boîtes de 10 pièces
1000 pcs. = en emballage industriel



Schmelzzeit-Grenzwerte / Pre-arcing time limits / Temps de fusion limité

Bemessungsstrom Rated current Courant assigné	1,0 I _{rat} min.	1,5 I _{rat} max.	2,75 I _{rat} min. max.	4 I _{rat} min. max.	10 I _{rat} max.
100 mA - 12,5 A	1 h	30 min.	2 ms 100ms	1 ms 50 ms	5 ms