



CONTACTOR RELAY, 2NO+2NC, AC 230 V,
50 HZ, SCREW CONNECTION, SIZE S00

General technical data:		
product brand name		SIRIUS
Product designation		contactor relay
Size of the contactor		S00
Protection class IP / on the front		IP20
Degree of pollution		3
Insulation voltage / with degree of pollution 3 / rated value	V	690
Installation altitude / at a height over sea level / maximum	m	2,000
Ambient temperature		
• during transport	°C	-55 ... +80
• during storage	°C	-55 ... +80
• during operating	°C	-25 ... +60
Contact reliability		one incorrect switching operation of 100 million switching operations (17 V, 1 mA)
Resistance against shock		10g / 5 ms and 5g / 10 ms
Impulse voltage resistance / rated value	kV	6
Reference code		
• according to DIN EN 61346-2		K
• according to DIN 40719 extended according to IEC 204-2 / according to IEC 750		K
• according to DIN EN 81346-2		K

Mechanical operating cycles as operating time		
• of the contactor / typical		30,000,000
• of the contactor with added auxiliary switch block / typical		10,000,000
• of the contactor with added electronics-compatible auxiliary switch block / typical		5,000,000

Control circuit/ Control:		
Voltage type / of control feed voltage		AC
Control supply voltage frequency		
• 1 / rated value	Hz	50
• 2 / rated value	Hz	60
Control supply voltage		
• at 50 Hz / at AC / rated value	V	230
• at 60 Hz / at AC / rated value	V	230
Operating range factor control supply voltage rated value / of the magnet coil		
• at 50 Hz		0.8 ... 1.1
• for AC		
• at 60 Hz		0.85 ... 1.1
• for AC		
Apparent pull-in power / of the solenoid / for AC	V·A	27
Apparent holding power / of the solenoid / for AC	V·A	4.6
Inductive power factor		
• with the pull-in power of the coil		0.8
• with the pull-in power of the coil		0.27

Auxiliary circuit:		
Product extension / auxiliary switch		Yes
Identification number and letter for switching elements		22 E
Contact reliability / of the auxiliary contacts		1 faulty switching per 100 million (17 V, 1 mA)
Number of NC contacts / for auxiliary contacts		2
• delayed switching		0
• instantaneous switching		2
• asynchronous switching		0
• lagging switching		0
Number of NO contacts / for auxiliary contacts		2
• instantaneous switching		2
• delayed switching		0
• asynchronous switching		0
• leading switching		0
Number of changeover contacts		

<ul style="list-style-type: none"> • for auxiliary contacts 		0
<ul style="list-style-type: none"> • of the auxiliary contacts / instantaneous switching 		0
Operating current		
<ul style="list-style-type: none"> • at AC-12 / maximum 	A	10
<ul style="list-style-type: none"> • at AC-15 		
<ul style="list-style-type: none"> • at 230 V / rated value 	A	6
<ul style="list-style-type: none"> • at 400 V / rated value 	A	3
<ul style="list-style-type: none"> • at 500 V / rated value 	A	2
<ul style="list-style-type: none"> • at 690 V / rated value 	A	1
Operating current / with 1 current path		
<ul style="list-style-type: none"> • at DC-12 		
<ul style="list-style-type: none"> • at 24 V / rated value 	A	10
<ul style="list-style-type: none"> • at 110 V / rated value 	A	3
<ul style="list-style-type: none"> • at 220 V / rated value 	A	1
<ul style="list-style-type: none"> • at DC-13 		
<ul style="list-style-type: none"> • at 24 V / rated value 	A	10
<ul style="list-style-type: none"> • at 110 V / rated value 	A	1
<ul style="list-style-type: none"> • at 220 V / rated value 	A	0.27

Short-circuit:

Design of the fuse link / for short-circuit protection of the auxiliary switch / required

fuse gL/gG: 10 A

Installation/ mounting/ dimensions:

mounting position		+/-180° rotation possible on vertical mounting surface; can be tilted forward and backward by +/- 22.5° on vertical mounting surface
Mounting type		screw and snap-on mounting
Width	mm	45
Height	mm	57.5
Depth	mm	72
Distance, to be maintained, to the ranks assembly / sideways	mm	0

Connections/ terminals:

Design of the electrical connection / for auxiliary and control current circuit

screw-type terminals

Type of the connectable conductor cross-section

• for auxiliary contacts

• solid

• finely stranded

• with conductor end processing

• for AWG conductors / for auxiliary contacts

2x (0.5 ... 1.5 mm²), 2x (0.75 ... 2.5 mm²), 2x 4 mm²

2x (0.5 ... 1.5 mm²), 2x (0.75 ... 2.5 mm²)

2x (20 ... 16), 2x (18 ... 14), 1x 12

Certificates/ approvals:

Verification of suitability

CSA / UL / CCC / GL / LRS / BV / DNV / RMRS / RINA

General Product Approval

Functional Safety /
Safety of
Machinery

Declaration of
Conformity



CCC



CSA



UL

[Type Examination](#)



EG-Konf.

Test Certificates

[Special Test
Certificate](#)

[Type Test
Certificates/Test
Report](#)

Shipping Approval



ABS



BUREAU
VERITAS



DNV



GL



LRS



PRS

Shipping Approval

other



RINA



RMRS

[other](#)

[Environmental
Confirmations](#)

Safety related data:

Proportion of dangerous failures

- with high demand rate / according to SN 31920
- with low demand rate / according to SN 31920

%	75
%	40

Protection against electrical shock

finger-safe

T1 value / for proof test interval or service life / according to IEC 61508

a	20
---	----

B10 value / with high demand rate

- according to SN 31920
- note

1,000,000
With 0.3 x Ie

Further information:

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/industrial-controls/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/>

Cax online generator



<http://www.siemens.com/cax>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<http://support.automation.siemens.com/WW/view/en/3RH1122-1AP00/all>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3RH1122-1AP00



last change:

Jul 7, 2014