

EAO – Your Expert Partner for Human Machine Interfaces

61-6441.4077 - Emergency stop switch compact - Actuator

61-6441.4077 - Emergency stop switch compact - Actuator



Attention: The preview is based on a sample product. This can differ from your current configuration.

Attribute

| | |
|----------------------|---|
| Design | raised |
| Front form | round |
| IP front protection | IP66, IP67, IP69K |
| Mounting cut-out | Ø 16 mm |
| Contacts | 1 NC / 1 NO |
| Dimension | Ø 27 mm |
| Front dimension | Ø 27 mm |
| IK Protection | IK06 (cover D40) |
| Type of illumination | non illuminated |
| IP Protection | IP67 front side, according to EN IEC 60529/A1:2010-04 |
| Lens colour | Red |
| Lens illumination | non illuminative |
| Lens material | Plastic |
| Lens shape | mushroom-head |
| Operating Travel | 4.2 mm |
| Switching action | Maintained |
| Terminal | Plug-in terminal |
| Weight | 0.02 kg |

Function

Emergency stop switch


EAO – Your Expert Partner for Human Machine Interfaces

61-6441.4077 - Emergency stop switch compact - Actuator


Dimensions




Mounting cut-outs



Component layouts



Wiring diagrams



Additional information

Application as per DIN EN ISO 13850 and EN 60204-1

Twist to unlock clockwise

Application as per DIN EN ISO 13850 and EN 60204-1

Seal Part No. 61-9900

Anti-twist ring No. 51-910

Fixing nut No. 51-991

Plug-in terminals 2.8 mm x 0.5 mm are solderable without UL certificate

Front plate thickness 1 ... 4 mm with an anti-rotation ring

Front plate thickness 1 ... 6 mm without an anti-rotation ring