



### 1-Piece Fixing Ties with Arrowhead, with Disc, sealed

- for Round holes
- for Oval holes


One-piece fixing ties assembled with a cellular rubber disc bring together a solution for the need to bundle a product whilst at the same time providing a fixing solution especially for the door and tailgate harnesses used for car body applications.

HellermannTyton's one-piece fixing ties combined with the specially designed cellular rubber discs offer a high protection against the ingress of dust and water. Tested according to the IEC 60529 standard the article types T50SOSSFT6.5E-MD and T60SOSSFT62x122-E-MD produced from PA66 heat stabilized material fulfill IP67.

As an additional protection against the loss of the seal disc during transportation, the cellular rubber disc of T50SOSSFT6.5E-MD is welded to the fixing tie by an automatic laser welding machine.



The additional seal protects against the ingress of moisture or dirt.



One piece fixing tie with arrowhead and disc, standard design

#### Material Data

Material	<b>Polyamide 6.6 (PA66)</b>
Operating Temperature	<b>-40 °C to +85 °C Continuous, (+105 °C for 500 h)</b>
Flammability	<b>UL94 V2</b>



#### Material Data

Material	<b>Polyamide 6.6 Heat Stabilised (PA66HS)</b>
Operating Temperature	<b>-40 °C to +105 °C Continuous, (+145 °C for 500 h)</b>
Flammability	<b>UL94 V2</b>



#### Technical Table

Article-No.	Type	Length (L)	Width (W)	Bundle Ø max.	Min. Tensile strength for ties (N)	Disc Ø	Hole Ø	Panel Thickness min.	Panel Thickness max.	Material	Colour
for Round Holes with foam seal											
126-03100	<b>T50SOSSFT6.5E-MD</b>	160	4.6	35.0	225	16.0	6.3-6.7	0.6	1.8	PA66HS	Green (GN)
156-00264	<b>T50SOSSFT6.5E-MD</b>	160	4.6	35.0	225	16.0	6.3-6.7	0.6	1.8	PA66HS	Black (BK)
156-00271	<b>T50SOSSFT6.5-E-MDL</b>	160	4.6	35.0	225	16.0	6.3-6.7	0.6	1.8	PA66HS	Natural (NA)
156-00379	<b>T50XROSSFT6.5EMDL</b>	200	4.6	45.0	200	16.0	6.25-6.75	1.2	2.1	PA66HS	Black (BK)
126-00065	<b>T50SOSSFT6.5-MS-MD</b>	163	4.6	35.0	180	16.0	6.25-6.75	0.7	1.6	PA66HS	Natural (NA)
for Oval Holes with foam seal											
126-00076	<b>T60SOSSFT65x130-E-MD</b>	157	5.5	30.0	300	16.0 x 22.0	6.5x13.0	0.6	2.0	PA66	Natural (NA)
126-00079	<b>T60SOSSFT70x120-E-MD</b>	157	5.5	30.0	300	16.0 x 22.0	7.0x12.0	0.7	2.0	PA66HS	Black (BK)
126-00080	<b>T60SOSSFT62x122-E-MD</b>	157	5.5	30.0	300	16.0 x 22.0	6.5x12.2	0.6	2.0	PA66HS	Black (BK)

All dimensions in mm. Subject to technical changes.