

DATA SHEET

5mm LEDs

Order code	Manufacturer code	Description	
56-0430	L-53LID	L-7113LID 5MM LOW CURRENT RED LED (RC)	

5mm LEDs	Page 1 of 6
The enclosed information is believed to be correct, Information may change ±without noticeqdue to	Revision A
product improvement. Users should ensure that the product is suitable for their use. E. & O. E.	20/02/2007

Sales: 01206 751166 Sales@rapidelec.co.uk Technical: 01206 835555 Tech@rapidelec.co.uk Fax: 01206 751188 www.rapidonline.com



T-1 3/4 (5mm) SOLID STATE LAMP

Part Number: L-7113LID

High Efficiency Red


Features


- LOW POWER CONSUMPTION.
- POPULAR T-1 3/4 DIAMETER PACKAGE.
- GENERAL PURPOSE LEADS.
- RELIABLE AND RUGGED.
- LONG LIFE SOLID STATE RELIABILITY.
- AVAILABLE ON TAPE AND REEL.
- LOW CURRENT IF=2mA OPERATING.
- RoHS COMPLIANT.

Description

The High Efficiency Red source color devices are made with Gallium Arsenide Phosphide on Gallium Phosphide Orange Light Emitting Diode.

Package Dimensions





- 1. All dimensions are in millimeters (inches).
- 2. Tolerance is $\pm 0.25(0.01")$ unless otherwise noted.
- 3. Lead spacing is measured where the leads emerge from the package.4. Specifications are subject to change without notice.





PAGE: 1 OF 5 SPEC NO: DSAC2657 **REV NO: V.7 DATE: JUL/10/2007 APPROVED: WYNEC CHECKED: Allen Liu DRAWN: Y.H.CHEN** ERP: 1101005077

Selection Guide

Part No.	Dice	Lens Type	lv (mc @ 2	,	Viewing Angle [1]
		,	Min.	Тур.	201/2
L-7113LID	High Efficiency Red (GaAsP/GaP)	RED DIFFUSED	0.7	5	30°

- 1. 01/2 is the angle from optical centerline where the luminous intensity is 1/2 the optical centerline value. 2. Luminous intensity/ luminous Flux: +/-15%.

Electrical / Optical Characteristics at TA=25°C

Symbol	Parameter	Device	Тур.	Max.	Units	Test Conditions
λpeak	Peak Wavelength	High Efficiency Red	627		nm	I=2mA
λD [1]	Dominant Wavelength	High Efficiency Red	625		nm	I=2mA
Δλ1/2	Spectral Line Half-width	High Efficiency Red	45		nm	I=2mA
С	Capacitance	High Efficiency Red	15		pF	VF=0V;f=1MHz
VF [2]	Forward Voltage	High Efficiency Red	1.7	2.5	V	I=2mA
IR	Reverse Current	High Efficiency Red		10	uA	VR = 5V


- 1.Wavelength: +/-1nm.
- 2. Forward Voltage: +/-0.1V.

Absolute Maximum Ratings at TA=25°C


Parameter	High Efficiency Red	Units		
Power dissipation	75	mW		
DC Forward Current	30	mA		
Peak Forward Current [1]	160	mA		
Reverse Voltage	5	V		
Operating/Storage Temperature	-40°C To +85°C			
Lead Solder Temperature [2]	260°C For 3 Seconds			
Lead Solder Temperature [3]	260°C For 5 Seconds			


- 1. 1/10 Duty Cycle, 0.1ms Pulse Width.
- 2. 2mm below package base.
 3. 5mm below package base.


SPEC NO: DSAC2657 **REV NO: V.7** DATE: JUL/10/2007 PAGE: 2 OF 5 APPROVED: WYNEC **CHECKED: Allen Liu DRAWN: Y.H.CHEN** ERP: 1101005077





High Efficiency Red L-7113LID












 SPEC NO: DSAC2657
 REV NO: V.7
 DATE: JUL/10/2007
 PAGE: 3 OF 5

 APPROVED: WYNEC
 CHECKED: Allen Liu
 DRAWN: Y.H.CHEN
 ERP: 1101005077

LED MOUNTING METHOD

1. The lead pitch of the LED must match the pitch of the mounting holes on the PCB during component placement. Lead-forming may be required to insure the lead pitch matches the hole pitch. Refer to the figure below for proper lead forming procedures.



Correct mounting method "X" Incorrect mounting method Note 1-2: Do not route PCB trace in the contact area between the leadframe and the PCB to prevent short-circuits.

2. When soldering wire to the LED, use individual heat—shrink tubing to insulate the exposed leads to prevent accidental contact short-circuit. (Fig. 2)





Fig. 2

3. Use stand-offs (Fig. 3) or spacers (Fig. 4) to securely position the LED above the PCB.




SPEC NO: DSAC2657 APPROVED: WYNEC

REV NO: V.7 CHECKED: Allen Liu **DATE: JUL/10/2007** DRAWN: Y.H.CHEN


PAGE: 4 OF 5 ERP: 1101005077

LEAD FORMING PROCEDURES


1. Maintain a minimum of 2mm clearance between the base of the LED lens and the first lead bend. (Fig. 5 and 6)



- 2. Lead forming or bending must be performed before soldering, never during or after Soldering.
- 3. Do not stress the LED lens during lead—forming in order to fractures in the lens epoxy and damage the internal structures.
- 4. During lead forming, use tools or jigs to hold the leads securely so that the bending force will not be transmitted to the LED lens and its internal structures. Do not perform lead forming once the component has been mounted onto the PCB. (Fig. 7)
- 5. Do not bend the leads more than twice. (Fig. 8)



6. After soldering or other high—temperature assembly, allow the LED to cool down to 50°C before applying outside force (Fig. 9). In general, avoid placing excess force on the LED to avoid damage. For any questions please consult with Kingbright representative for proper handling procedures.



PAGE: 5 OF 5

ERP: 1101005077

SPEC NO: DSAC2657 REV NO: V.7 DATE: JUL/10/2007

APPROVED: WYNEC CHECKED: Allen Liu DRAWN: Y.H.CHEN