

Page 1 of 9
Safety data sheet according to Regulation (EC) No 1907/2006, Annex II
Revision date / version: 21.08.2015 / 0007
Replacing version dated / version: 23.10.2012 / 0006
Valid from: 21.08.2015
PDF print date: 24.08.2015
Innenraum-Reiniger 500 mL
Art.: 1547

Safety data sheet according to Regulation (EC) No 1907/2006, Annex II

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1 Product identifier

Innenraum-Reiniger 500 mL
Art.: 1547

1.2 Relevant identified uses of the substance or mixture and uses advised against

Relevant identified uses of the substance or mixture:

Cleaner

Sector of use [SU]:

SU 3 - Industrial uses: Uses of substances as such or in preparations at industrial sites

SU21 - Consumer uses: Private households (=general public = consumers)

SU22 - Professional uses: Public domain (administration, education, entertainment, services, craftsmen)

Chemical product category [PC]:

PC35 - Washing and cleaning products (including solvent based products)

Process category [PROC]:

PROC 7 - Industrial spraying

PROC 8a - Transfer of substance or preparation (charging/discharging) from/to vessels/large containers at non-dedicated facilities

PROC 9 - Transfer of substance or preparation into small containers (dedicated filling line, including weighing)

PROC11 - Non industrial spraying

PROC19 - Hand-mixing with intimate contact and only PPE available

Article Categories [AC]:

AC99 - Not required.

Environmental Release Category [ERC]:

ERC 2 - Formulation of preparations

ERC 4 - Industrial use of processing aids in processes and products, not becoming part of articles

ERC 5 - Industrial use resulting in inclusion into or onto a matrix

ERC 8a - Wide dispersive indoor use of processing aids in open systems

ERC 8c - Wide dispersive indoor use resulting in inclusion into or onto a matrix

ERC 8d - Wide dispersive outdoor use of processing aids in open systems

ERC 8f - Wide dispersive outdoor use resulting in inclusion into or onto a matrix

Uses advised against:

No information available at present.

1.3 Details of the supplier of the safety data sheet

GB

LIQUI MOLY GmbH, Jerg-Wieland-Str. 4, 89081 Ulm-Lehr, Germany
Phone: (+49) 0731-1420-0, Fax: (+49) 0731-1420-88

Qualified person's e-mail address: info@chemical-check.de, k.schnurbusch@chemical-check.de Please DO NOT use for requesting Safety Data Sheets.

1.4 Emergency telephone number

Emergency information services / official advisory body:

Telephone number of the company in case of emergencies:

+49 (0) 700 / 24 112 112 (LMR)

SECTION 2: Hazards identification

2.1 Classification of the substance or mixture

Classification according to Regulation (EC) 1272/2008 (CLP)

GB

Page 2 of 9
 Safety data sheet according to Regulation (EC) No 1907/2006, Annex II
 Revision date / version: 21.08.2015 / 0007
 Replacing version dated / version: 23.10.2012 / 0006
 Valid from: 21.08.2015
 PDF print date: 24.08.2015
 Innenraum-Reiniger 500 mL
 Art.: 1547

The mixture is not classified as dangerous in the terms of the Regulation (EC) 1272/2008 (CLP).

2.2 Label elements

Labeling according to Regulation (EC) 1272/2008 (CLP)

Not applicable

2.3 Other hazards

The mixture does not contain any vPvB substance (vPvB = very persistent, very bioaccumulative) or is not included under XIII of the regulation (EC) 1907/2006.

The mixture does not contain any PBT substance (PBT = persistent, bioaccumulative, toxic) or is not included under XIII of the regulation (EC) 1907/2006.

REGULATION (EC) No 648/2004

perfumes
 2-BROMO-2-NITROPROPANE-1,3-DIOL
 BENZISOTHIAZOLINONE
 METHYLISOTHIAZOLINONE

SECTION 3: Composition/information on ingredients

Gen. Description:

mixture of detergent substances, auxiliary substances

3.1 Substance

n.a.

3.2 Mixture

--	
Registration number (REACH)	--
Index	-
EINECS, ELINCS, NLP	-
CAS	-
content %	
Classification according to Regulation (EC) 1272/2008 (CLP)	---

SECTION 4: First aid measures

4.1 Description of first aid measures

Inhalation

Not required.

Skin contact

Wash in water.

Eye contact

Wash thoroughly for several minutes using copious water. Seek medical help if necessary.

Ingestion

Rinse the mouth thoroughly with water.

Give water to drink.

If applicable:

Medical attention necessary.

4.2 Most important symptoms and effects, both acute and delayed

If applicable delayed symptoms and effects can be found in section 11 and the absorption route in section 4.1.

The following may occur:

Irritation of the eyes

In certain cases, the symptoms of poisoning may only appear after an extended period / after several hours.

4.3 Indication of any immediate medical attention and special treatment needed

n.c.

SECTION 5: Firefighting measures

Safety data sheet according to Regulation (EC) No 1907/2006, Annex II
Revision date / version: 21.08.2015 / 0007
Replacing version dated / version: 23.10.2012 / 0006
Valid from: 21.08.2015
PDF print date: 24.08.2015
Innenraum-Reiniger 500 mL
Art.: 1547

5.1 Extinguishing media

Suitable extinguishing media

Adapt to the nature and extent of fire.

Unsuitable extinguishing media

n.c.

5.2 Special hazards arising from the substance or mixture

In case of fire the following can develop:

Oxides of carbon

5.3 Advice for firefighters

In case of fire and/or explosion do not breathe fumes.

Protective respirator with independent air supply.

Dispose of contaminated extinction water according to official regulations.

SECTION 6: Accidental release measures

6.1 Personal precautions, protective equipment and emergency procedures

Avoid contact with eyes.

If applicable, caution - risk of slipping.

6.2 Environmental precautions

If leakage occurs, dam up.

Resolve leaks if this possible without risk.

Prevent surface and ground-water infiltration, as well as ground penetration.

Do not pour down the drain undiluted.

6.3 Methods and material for containment and cleaning up

Soak up with absorbent material (e.g. universal binding agent, sand, diatomaceous earth, sawdust) and dispose of according to Section 13.

Flush residue using copious water.

6.4 Reference to other sections

For personal protective equipment see Section 8 and for disposal instructions see Section 13.

SECTION 7: Handling and storage

In addition to information given in this section, relevant information can also be found in section 8 and 6.1.

7.1 Precautions for safe handling

7.1.1 General recommendations

Observe directions on label and instructions for use.

7.1.2 Notes on general hygiene measures at the workplace

General hygiene measures for the handling of chemicals are applicable.

Wash hands before breaks and at end of work.

Keep away from food, drink and animal feedingstuffs.

Remove contaminated clothing and protective equipment before entering areas in which food is consumed.

7.2 Conditions for safe storage, including any incompatibilities

Not to be stored in gangways or stair wells.

Store product closed and only in original packing.

Protect from frost.

7.3 Specific end use(s)

No information available at present.

SECTION 8: Exposure controls/personal protection

8.1 Control parameters

8.2 Exposure controls

8.2.1 Appropriate engineering controls

Page 4 of 9
 Safety data sheet according to Regulation (EC) No 1907/2006, Annex II
 Revision date / version: 21.08.2015 / 0007
 Replacing version dated / version: 23.10.2012 / 0006
 Valid from: 21.08.2015
 PDF print date: 24.08.2015
 Innenraum-Reiniger 500 mL
 Art.: 1547

Ensure good ventilation. This can be achieved by local suction or general air extraction.
 If this is insufficient to maintain the concentration under the WEL or AGW values, suitable breathing protection should be worn.
 Applies only if maximum permissible exposure values are listed here.

8.2.2 Individual protection measures, such as personal protective equipment

General hygiene measures for the handling of chemicals are applicable.
 Wash hands before breaks and at end of work.
 Keep away from food, drink and animal feedingstuffs.
 Remove contaminated clothing and protective equipment before entering areas in which food is consumed.

Eye/face protection:
 Tight fitting protective goggles (EN 166) with side protection, with danger of projections.

Skin protection - Hand protection:
 Normally not necessary.

Skin protection - Other:
 Protective working garments (e.g. safety shoes EN ISO 20345, long-sleeved protective working garments).

Respiratory protection:
 Normally not necessary.

Thermal hazards:
 Not applicable

Additional information on hand protection - No tests have been performed.
 In the case of mixtures, the selection has been made according to the knowledge available and the information about the contents.
 Selection of materials derived from glove manufacturer's indications.
 Final selection of glove material must be made taking the breakthrough times, permeation rates and degradation into account.
 Selection of a suitable glove depends not only on the material but also on other quality characteristics and varies from manufacturer to manufacturer.
 In the case of mixtures, the resistance of glove materials cannot be predicted and must therefore be tested before use.
 The exact breakthrough time of the glove material can be requested from the protective glove manufacturer and must be observed.

8.2.3 Environmental exposure controls

No information available at present.

SECTION 9: Physical and chemical properties

9.1 Information on basic physical and chemical properties

Physical state:	Liquid
Colour:	Colourless, Clear
Odour:	Fruity
Odour threshold:	Not determined
pH-value:	6,5 (20°C)
Melting point/freezing point:	Not determined
Initial boiling point and boiling range:	100 °C
Flash point:	n.a.
Evaporation rate:	Not determined
Flammability (solid, gas):	n.a.
Lower explosive limit:	Not determined
Upper explosive limit:	Not determined
Vapour pressure:	23 hPa (20°C)
Vapour density (air = 1):	Not determined
Density:	1,01 g/cm ³ (20°C)
Bulk density:	n.a.
Solubility(ies):	Not determined
Water solubility:	Mixable
Partition coefficient (n-octanol/water):	Not determined
Auto-ignition temperature:	No
Decomposition temperature:	Not determined
Viscosity:	Not determined

(GB)

Page 6 of 9
 Safety data sheet according to Regulation (EC) No 1907/2006, Annex II
 Revision date / version: 21.08.2015 / 0007
 Replacing version dated / version: 23.10.2012 / 0006
 Valid from: 21.08.2015
 PDF print date: 24.08.2015
 Innenraum-Reiniger 500 mL
 Art.: 1547

Toxicity to daphnia:							n.d.a.
Toxicity to algae:							n.d.a.
Persistence and degradability:							The surfactant(s) contained in this mixture complies(comply) with the biodegradability criteria as laid down in Regulation (EC) No.648/2004 on detergents. Data to support this assertion are held at the disposal of the competent authorities of the Member States and will be made available to them, at their direct request or at the request of a detergent manufacturer.
Bioaccumulative potential:							n.d.a.
Mobility in soil:							n.d.a.
Results of PBT and vPvB assessment							n.d.a.
Other adverse effects:							n.d.a.

SECTION 13: Disposal considerations

13.1 Waste treatment methods

For the substance / mixture / residual amounts

EC disposal code no.:

The waste codes are recommendations based on the scheduled use of this product.

Owing to the user's specific conditions for use and disposal, other waste codes may be allocated under certain circumstances. (2014/955/EU)

20 01 30 detergents other than those mentioned in 20 01 29

Recommendation:

Sewage disposal shall be discouraged.

Pay attention to local and national official regulations.

E.g. dispose at suitable refuse site.

Can be disposed of with household rubbish.

For contaminated packing material

Pay attention to local and national official regulations.

Empty container completely.

Dispose of packaging that cannot be cleaned in the same manner as the substance.

Untampered packaging can be recycled.

Recommended cleaner:

Water

SECTION 14: Transport information

General statements

UN number: n.a.

Transport by road/by rail (ADR/RID)

UN proper shipping name:

Transport hazard class(es): n.a.

Packing group: n.a.

Classification code: n.a.

LQ (ADR 2015): n.a.

Environmental hazards: Not applicable

Tunnel restriction code:

Transport by sea (IMDG-code)

GB

Page 7 of 9
 Safety data sheet according to Regulation (EC) No 1907/2006, Annex II
 Revision date / version: 21.08.2015 / 0007
 Replacing version dated / version: 23.10.2012 / 0006
 Valid from: 21.08.2015
 PDF print date: 24.08.2015
 Innenraum-Reiniger 500 mL
 Art.: 1547

UN proper shipping name:
 Transport hazard class(es): n.a.
 Packing group: n.a.
 Marine Pollutant: n.a.
 Environmental hazards: Not applicable

Transport by air (IATA)

UN proper shipping name:
 Transport hazard class(es): n.a.
 Packing group: n.a.
 Environmental hazards: Not applicable

Special precautions for user

Unless specified otherwise, general measures for safe transport must be followed.

Transport in bulk according to Annex II of MARPOL and the IBC Code

Non-dangerous material according to Transport Regulations.

SECTION 15: Regulatory information

15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

National rules/regulation for the compliance with maximum quantities with regard to phosphates and or phosphorous compounds must be observed and complied with.

For classification and labelling see Section 2.

Observe restrictions: n.a.

General hygiene measures for the handling of chemicals are applicable.

Directive 2010/75/EU (VOC): < 0,05 %

15.2 Chemical safety assessment

A chemical safety assessment is not provided for mixtures.

SECTION 16: Other information

Revised sections: 1 - 16

Classification and processes used to derive the classification of the mixture in accordance with the ordinance (EG) 1272/2008 (CLP):

Not applicable

The following phrases represent the posted Hazard Class and Risk Category Code (GHS/CLP) of the product and the constituents (specified in Section 2 and 3).

Any abbreviations and acronyms used in this document:

AC Article Categories
 acc., acc. to according, according to
 ACGIH American Conference of Governmental Industrial Hygienists
 ADR Accord européen relatif au transport international des marchandises Dangereuses par Route (= European Agreement concerning the International Carriage of Dangerous Goods by Road)
 AOEL Acceptable Operator Exposure Level
 AOX Adsorbable organic halogen compounds
 approx. approximately
 Art., Art. no. Article number
 ATE Acute Toxicity Estimate according to Regulation (EC) 1272/2008 (CLP)
 BAM Bundesanstalt für Materialforschung und -prüfung (Federal Institute for Materials Research and Testing, Germany)
 BAuA Bundesanstalt für Arbeitsschutz und Arbeitsmedizin (= Federal Institute for Occupational Health and Safety, Germany)
 BCF Bioconcentration factor
 BGV Berufsgenossenschaftliche Vorschrift (= Accident Prevention Regulation)
 BHT Butylhydroxytoluol (= 2,6-Di-t-butyl-4-methyl-phenol)
 BMGV Biological monitoring guidance value (EH40, UK)
 BOD Biochemical oxygen demand

Page 8 of 9
 Safety data sheet according to Regulation (EC) No 1907/2006, Annex II
 Revision date / version: 21.08.2015 / 0007
 Replacing version dated / version: 23.10.2012 / 0006
 Valid from: 21.08.2015
 PDF print date: 24.08.2015
 Innenraum-Reiniger 500 mL
 Art.: 1547

BSEF Bromine Science and Environmental Forum
 bw body weight
 CAS Chemical Abstracts Service
 CEC Coordinating European Council for the Development of Performance Tests for Fuels, Lubricants and Other Fluids
 CESIO Comité Européen des Agents de Surface et de leurs Intermédiaires Organiques
 CIPAC Collaborative International Pesticides Analytical Council
 CLP Classification, Labelling and Packaging (REGULATION (EC) No 1272/2008 on classification, labelling and packaging of substances and mixtures)
 CMR carcinogenic, mutagenic, reproductive toxic
 COD Chemical oxygen demand
 CTFA Cosmetic, Toiletry, and Fragrance Association
 DMEL Derived Minimum Effect Level
 DNEL Derived No Effect Level
 DOC Dissolved organic carbon
 DT50 Dwell Time - 50% reduction of start concentration
 DVS Deutscher Verband für Schweißen und verwandte Verfahren e.V. (= German Association for Welding and Allied Processes)
 dw dry weight
 e.g. for example (abbreviation of Latin 'exempli gratia'), for instance
 EC European Community
 ECHA European Chemicals Agency
 EEA European Economic Area
 EEC European Economic Community
 EINECS European Inventory of Existing Commercial Chemical Substances
 ELINCS European List of Notified Chemical Substances
 EN European Norms
 EPA United States Environmental Protection Agency (United States of America)
 ERC Environmental Release Categories
 ES Exposure scenario
 etc. et cetera
 EU European Union
 EWC European Waste Catalogue
 Fax. Fax number
 gen. general
 GHS Globally Harmonized System of Classification and Labelling of Chemicals
 GWP Global warming potential
 HET-CAM Hen's Egg Test - Chorionallantoic Membrane
 HGWP Halocarbon Global Warming Potential
 IARC International Agency for Research on Cancer
 IATA International Air Transport Association
 IBC Intermediate Bulk Container
 IBC (Code) International Bulk Chemical (Code)
 IC Inhibitory concentration
 IMDG-code International Maritime Code for Dangerous Goods
 incl. including, inclusive
 IUCLID International Uniform Chemical Information Database
 LC lethal concentration
 LC50 lethal concentration 50 percent kill
 LCLo lowest published lethal concentration
 LD Lethal Dose of a chemical
 LD50 Lethal Dose, 50% kill
 LDLo Lethal Dose Low
 LOAEL Lowest Observed Adverse Effect Level
 LOEC Lowest Observed Effect Concentration
 LOEL Lowest Observed Effect Level
 LQ Limited Quantities
 MARPOL International Convention for the Prevention of Marine Pollution from Ships
 n.a. not applicable
 n.av. not available
 n.c. not checked
 n.d.a. no data available
 NIOSH National Institute of Occupational Safety and Health (United States of America)
 NOAEC No Observed Adverse Effect Concentration
 NOAEL No Observed Adverse Effect Level
 NOEC No Observed Effect Concentration

Page 9 of 9
Safety data sheet according to Regulation (EC) No 1907/2006, Annex II
Revision date / version: 21.08.2015 / 0007
Replacing version dated / version: 23.10.2012 / 0006
Valid from: 21.08.2015
PDF print date: 24.08.2015
Innenraum-Reiniger 500 mL
Art.: 1547

NOEL No Observed Effect Level
ODP Ozone Depletion Potential
OECD Organisation for Economic Co-operation and Development
org. organic
PAH polycyclic aromatic hydrocarbon
PBT persistent, bioaccumulative and toxic
PC Chemical product category
PE Polyethylene
PNEC Predicted No Effect Concentration
POCP Photochemical ozone creation potential
ppm parts per million
PROC Process category
PTFE Polytetrafluorethylene
REACH Registration, Evaluation, Authorisation and Restriction of Chemicals (REGULATION (EC) No 1907/2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals)
REACH-IT List-No. 9xx-xxx-x No. is automatically assigned, e.g. to pre-registrations without a CAS No. or other numerical identifier. List Numbers do not have any legal significance, rather they are purely technical identifiers for processing a submission via REACH-IT.
RID Règlement concernant le transport International ferroviaire de marchandises Dangereuses (= Regulation concerning the International Carriage of Dangerous Goods by Rail)
SADT Self-Accelerating Decomposition Temperature
SAR Structure Activity Relationship
SU Sector of use
SVHC Substances of Very High Concern
Tel. Telephone
ThOD Theoretical oxygen demand
TOC Total organic carbon
TRGS Technische Regeln für Gefahrstoffe (=Technical Regulations for Hazardous Substances)
UN RTDG United Nations Recommendations on the Transport of Dangerous Goods
VbF Verordnung über brennbare Flüssigkeiten (= Regulation for flammable liquids (Austria))
VOC Volatile organic compounds
vPvB very persistent and very bioaccumulative
WEL-TWA, WEL-STEL WEL-TWA = Workplace Exposure Limit - Long-term exposure limit (8-hour TWA (= time weighted average) reference period), WEL-STEL = Workplace Exposure Limit - Short-term exposure limit (15-minute reference period) (EH40, UK).
WHO World Health Organization
wwt wet weight

The statements made here should describe the product with regard to the necessary safety precautions - they are not meant to guarantee definite characteristics - but they are based on our present up-to-date knowledge.
No responsibility.

These statements were made by:

Chemical Check GmbH, Chemical Check Platz 1-7, D-32839 Steinheim, Tel.: +49 5233 94 17 0, Fax: +49 5233 94 17 90

© by Chemical Check GmbH Gefahrstoffberatung. The copying or changing of this document is forbidden except with consent of the Chemical Check GmbH Gefahrstoffberatung.