## **Product information**

# Viscoplus for Oil

### PI 37/07/25/2024



#### **Description**

Modern, mono-functional high-performance additive for stabilizing the viscosity of motor oils. Visco Plus offers outstanding protection against mechanical and therefore permanent shear losses to the oil under extreme running conditions and is effective against the thinning of motor oils due to frequent cold starts.

# Visco-Stabil Mos Stabil

#### **Properties**

- stabilizes loss of viscosity
- optimum lubrication under all operating conditions
- fully compatible with mineral and synthetic oils
- reduces engine noise
- optimum oil pressure under all operating conditions
- reduces oil consumption
- improves the movable seal between piston and cylinder
- reduces wear

#### Technical data

Color / appearance orange clear Density at 20 °C 0,89 g/cm<sup>3</sup>

DIN 51757

Viscosity at 40 °C 299,6 mm<sup>2</sup>/s

**ASTM D7042** 

Flash point 120 °C

**DIN ISO 2592** 

Pour point -15 °C

**DIN ISO 3016** 

Odor characteristic

Form liquid

#### Areas of application

For all cars and commercial vehicles, gasoline and diesel engines in new and used cars.

#### Comment

Not suitable for use on motorbikes with wet clutches!

#### **Application**

Can contents (300 ml) are sufficient for 5 liters of motor oil. After adding to the motor oil, allow the engine to run warm. The product can be added at any time.

#### Available pack sizes

300 ml Can sheet metal 1017

D-F-NL

300 ml Can sheet metal 2502

D-E-P

#### Available pack sizes

300 ml Can sheet metal 2672

D-PL-BG

300 ml Can sheet metal 2807

DK-N-S-FIN

300 ml Can sheet metal 8362

GB-ARAB-F

300 ml Can sheet metal 8377

D-H-RO

300 ml Can sheet metal 8958

GB-GR-I

300 ml Can sheet metal 20916

JΡ

300 ml Can sheet metal 21695

**GB-AUS** 

Our information is based on thorough research and may be considered reliable, although not legally binding.