



Rapid Part Number: 56-9977 Europa Part Number: 2470001

Specifications and dimensions

- Multifunction timer SPCO
- Din rail mounting
- LED indicator for power and run





LED indicator for power and run		15 18 18
Features		
Height	98.8mm	
Width	17.5mm	
Depth	63.5mm	
Weight	0.11Kg	
Cover ingress protection	IP20	
Contact arrangement	1 x C/O	
Contact material	AgNi	
Rated switching voltage	250V AC	
Minimum switching voltage	5V	
Rated load AC1	10A / 250VAC	
Rated load DC1	10A / 24VDC	
Rated voltage coil	12 240V AC/DC	
Rated frequency	48 63 Hz	
Rated power consumption of coil	0.75VA	
Coil resistance at 20°C	38500 W	
Electrical life AC1	> 2x 105	
Mechanical life	> 2 x 107	
Operating temperature	,-20°C to +45°C	
Timing Module		
Functions		
Delay on energisation	E	
Delay on de-energisation	Wu	
Symmetrical recycling	Вр	
0.5s pulse	Т	
Delay off with start contact	R	
Interval with 0.5s pulse	Ws	
Interval ON	Wa	
Time Ranges		
Seconds	1s, 10s	
Minutes	1m, 10m	
Hours	1h, 10h	
Days	1d, 10d	
Setting accuracy	± 5%	
Repeat accuracy	± 0.5%	

## (1) ALL PRODUCTS, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE.

Information provided in data sheets and/or specifications may vary from actual results in different applications and performance may vary over time. All products must be installed according to manufacturers instructions.

Europa House, Airport Way, Luton, Beds, LU2 9NH Tel: 01582 692 440 / Fax: 01582 692 450 e-mail: sales@europacomponents.com website: http://www.europacomponents.com

Page 1 of 1 EPC2128-001