



LV HRC FUSE LINK GL/GG WITH NON-INSULATED GRIP LUGS WITH FRONT INDICATOR SIZE 000, 50A, AC 500V/DC 250V

Similar to image

### Technical data:

product brand name		SETRON
Product designation		LV HRC fuse link
Current / for AC / rated value	A	50
Operating class of the fuse link		gG
Size of the fallback-system / acc. to DIN EN 60269-1		NH000
Supply voltage		
• for AC / rated value	V	500
• for DC	V	250
Switching capacity current		
• in accordance with IEC 60947-2 / rated value	kA	120
• with DC / in accordance with IEC 60947-2 / rated value	kA	25
Design of the fuse link		LV HRC fuse link
Design of an identification indicator		Front indicators
Mounting type		Non-insulated grip lugs
mounting position		Any, preferably vertical
Protection class IP		IP20, with connected conductors
Climatic class		-20 to +50 at 95% relative humidity
Ambient temperature	°C	-5 ... +40

Ambient temperature / during storage / note		Air humidity 90% at 20 °C
Design of the switching contact		Non-corroding, silver-plated
Net weight	g	131
Item designation		
• according to DIN EN 61346-2		F
• according to DIN EN 81346-2		F

#### Certificates/approvals:

##### General Product Approval



CSA



GOST



KEMA



VDE



EG-Konf.

##### Test Certificates

[Special Test Certificate](#)

[Type Test Certificates/Test Report](#)

##### Shipping Approval



GL

##### other

[Environmental Confirmations](#)

##### Declaration of Conformity

#### Further information:

##### Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

##### Industry Mall (Online ordering system)

<https://eb.automation.siemens.com/mall/en/WW/Catalog/Product/3NA3820>

##### Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<http://support.automation.siemens.com/WW/view/en/3NA3820/all>

##### Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)



[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=3NA3820](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NA3820)

##### CAX-Online-Generator

<http://www.siemens.com/cax>

##### Tender specifications

[Datenorm](#) [GAEB81](#) [GAEB83](#) [RTF](#) [TXT](#)



last change:

Jul 7, 2014