
SIEMENS

Product data sheet

3NA3822



LV HRC FUSE LINK GL/GG WITH NON-INSULATED GRIP LUGS WITH FRONT INDICATOR SIZE 000, 63A, AC 500V/DC 250V

Similar to image

Technical data:				
product brand name		SENTRON		
Product designation		LV HRC fuse link		
Current / for AC / rated value	А	63		
Operating class of the fuse link		gG		
Size of the fallback-system / acc. to DIN EN 60269-1		NH000		
Supply voltage				
for AC / rated value	V	500		
• for DC	V	250		
Switching capacity current				
• in accordance with IEC 60947-2 / rated value	kA	120		
• with DC / in accordance with IEC 60947-2 / rated value	kA	25		
Design of the fuse link		LV HRC fuse link		
Design of an identification indicator		Front indicators		
Mounting type		Non-insulated grip lugs		
mounting position		Any, preferably vertical		
Protection class IP		IP20, with connected conductors		
Climatic class		-20 to +50 at 95% relative humidity		
Ambient temperature	°C	-5 +40		

	Air humidity 90% at 20 °C
	Non-corroding, silver-plated
g	131
	F
	F
-	g

Certificates/approvals:

General Product Approval

(SA)	GOST	KEMA		EG-Konf.	
Test Certificates		Shipping Approval	other		
Special Test Certificate	Type Test Certificates/Test Report	G L C	Environmental Confirmations		
Further information:					

Declaration of Conformity

Information- and Downloadcenter (Catalogs, Brochures,...) http://www.siemens.com/lowvoltage/catalogs

Industry Mall (Online ordering system)

https://eb.automation.siemens.com/mall/en/WW/Catalog/Product/3NA3822


Service&Support (Manuals, Certificates, Characteristics, FAQs,...)


http://support.automation.siemens.com/WW/view/en/3NA3822/all

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...) http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NA3822

CAx-Online-Generator http://www.siemens.com/cax

Tender specifications
Datanorm GAEB81 GAEB83 RTF TXT





last change:

Jul 7, 2014